LITE-ON SEMICONDUCTORS

G2045CTFW

TRENCH SCHOTTKY RECTIFIERS

REVERSE VOLTAGE – 45 Volts
FORWARD CURRENT – 20 Amperes

FEATURES

- Trench Schottky technology
- Low power loss, high efficiency
- Low forward drop voltage
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case: ITO-220AB molded plastic
- Case Material: “Green” molding compound, UL flammability classification 94V-0, (No Br. Sb. Cl.) "Halogen-free".
- Terminals: Matte Tin
- Lead Free Finish, RoHS Compliant
- Polarity: As marked on the body
- Weight: 0.05 ounces, 1.558 grams (Approximate)
- Mounting position: Any

ITO-220AB(WB)



ITO-220AB(WB)		
DIM.	MIN.	MAX.
A	14.95	15.95
B	10.00	10.40
C	2.76	3.36
D	8.50	8.80
E	3.30	3.90
F	13.0	13.70
G	1.15	1.70
H	2.40	2.70
I	0.50	0.80
J	0.45	0.70
K	3.00	3.30
L	4.46	4.87
M	2.48	2.80
N	2.50	2.80
P	1.50	1.90
All dimensions in millimeter		

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25℃ ambient temperature unless otherwise specified.

ABSOLUTE RATINGS

PARAMETER	SYMBOL	VALUE	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	45	V
Maximum DC Blocking Voltage	V_{DC}	45	V
Average Rectified Output Current per device @Tc=110℃	I_F	20	A
Non-repetitive Peak Forward Surge Current single half sine-wave tp=8.3ms	I_{FSM}	180	A
Operating junction and Storage temperature range	T_J, T_{STG}	-55 to +150	℃

STATIC ELECTRICAL CHARACTERISTICS

Parameter	Test condition	Symbol	Typ.	Max.	Unit
Maximum Forward Voltage Note(1)	IF=10A @Tj=25℃ IF=10A @Tj=125℃	VF	- 0.45	0.5 -	V
Maximum DC Reverse Current	VR=45V @Tj=25℃ @Tj=125℃	IR	- -	0.5 100	mA mA
Junction Capacitance per element	f=1MHz, VR=4V	Cj	1260	-	pF

THERMAL CHARACTERISTICS

Parameter	SYMBOL	VALUE	UNIT
Typical thermal resistance Junction (Note 2&3)	$R_{\Theta JC}$ $R_{\Theta JL}$ $R_{\Theta JA}$	3 4 15	℃/W

REV. 4, Jan -2017, KTHC126

Note :

(1) 300us Pulse Width, 2% Duty Cycle.
(2) Thermal Resistance Junction to Case, Lead and Ambient.
(3) Device mounted on 72 x 75 x 2 mm Copper plate.

RATING AND CHARACTERISTIC CURVES
G2045CFTW

FIG.1- FORWARD CURRENT DERATING CURVE



FIG.2- MAXIMUM NON-REPETITIVE SURGE CURRENT



FIG.3- TYPICAL JUNCTION CAPACITANCE



FIG.4- TYPICAL FORWARD CHARACTERISTICS



FIG.5- TYPICAL REVERSE CHARACTERISTICS



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.