





P/N LEGEND



A1250	H	XP	N	0	X	NP	N	00	G
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

① Series No.
 ② Connector type: H=Housing
 ③ No. of circuits
 ④ N=Halogen Free
 ⑤ Material: 0=Nylon 66-V0
 ⑥ Color: W=White; B=Black
 ⑦ Plating code: NP=Non-plating
 ⑧ Plating code: N=Non-plating
 ⑨ Option code: 00=Standard
 ⑩ Packing code: G=Bag



SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 125V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Material: Nylon 66,UL94V-0
 Color: White or Black



Circuit No.	Dimensions			Circuit No.	Dimensions		
	A	B	C		A	B	C
02P	1.25	4.25	2.95	12P	13.75	16.75	15.45
03P	2.50	5.50	4.20	13P	15.00	18.00	16.70
04P	3.75	6.75	5.45	14P	16.25	19.25	17.95
05P	5.00	8.00	6.70	15P	17.50	20.50	19.20
06P	6.25	9.25	7.95	16P	18.75	21.75	20.45
07P	7.50	10.50	9.20	17P	20.00	23.00	21.70
08P	8.75	11.75	10.45	18P	21.25	24.25	22.95
09P	10.00	13.00	11.70	19P	22.50	25.50	24.20
10P	11.25	14.25	12.95	19P	22.50	25.50	24.20
11P	12.50	15.50	14.20	20P	23.75	26.75	25.45

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.						
UNIT		SCALE		SHEET		TITLE:				
mm		1 : 1		1 of 1						
DRAWN BY		APPROVED BY		1.25mm PITCH HOUSING						
歐陽小強		謝瑞清								
2008.09.02		2008.09.02								
GENERAL TOLERANCE				DRAW NO. : A1250H-XPXXXXXXXXX						
A3	EN1107040251	2011.07.01	陳錦展					X. X±0.25	ANGLE±	
A2	EN1011230269	2010.11.26	陳錦展					X. XX±0.15		
REV.	DESCRIPTION	DATE	NAME					X. XXX±0.05	REV. A3	