


PCB Relay G5Q

Compact, High Isolation Relay

- Compact single pole relay with high isolation between coil and contacts.
- Ensures a withstand impulse voltage of 8,000V between the coil and contacts.
- Low coil power consumption.
- UL class F coil insulation.
- UL recognized / CSA certified. EN approved.
- Ideal for appliance and HVAC controls
- RoHS Compliant



Ordering Information

To Order: Select the part number and add the desired coil voltage and rating. (e.g., G5Q-14 DC12)

Classification		Enclosure rating	Model
Single contact, class F coil insulation	SPST-NO	Flux protection	G5Q-1A
		Fully-sealed	G5Q-1A4
	SPDT	Flux protection	G5Q-1
		Fully-sealed	G5Q-14

Note: Add “-EU” before the coil voltage to obtain versions with CTI > 250. (e.g., G5Q-1A4-EU DC12)
Specifications for “EU” type differ from standard models. Contact Omron for more details

Specifications

■ Coil Ratings

Rated voltage (V)		Rated coil current (mA)	Coil resistance (Ω)	Pick-up voltage	Drop-out voltage	Maximum voltage	Power consumption (mW)
				Percent of rated voltage			
SPDT	DC 5	80	63	75% max	5% min	190% @ 23°C	400
	DC 9	44.4	202				
	DC 12	33.3	360				
	DC 24	16.7	1440				
SPST-NO	DC 5	40	125	75% max	5% min	190% @ 23°C	200
	DC 9	22.2	405				
	DC 12	16.7	720				
	DC 24	8.3	2880				

- Note:**
1. Rated current and coil resistance are measured at 23°C with a tolerance of ±10%.
 2. The operating characteristics are measured at a coil temperature of 23°C.
 3. The “Maximum voltage” is the maximum voltage that can be applied to the relay coil.

■ Contact Ratings

Item	SPDT	SPST-NO
Rated load (resistive)	10 A at 125 VAC (NO) 3 A at 250 VAC (NO) 3 A at 125 VAC (NO) 5 A at 30 VDC (NO) 3 A at 250 VAC (NC) 3 A at 125 VAC (NC) 3 A at 30 VDC (NC)	10 A at 125 VAC 3 A at 250 VAC 3 A at 125 VAC 5 A at 30 VDC
Contact type	Single	
Contact material	Ag alloy (Cd free)	
Rated carry current	10 A (NO)/3 A (NC)	
Max. switching voltage	277 VAC, 30 VDC	
Max. switching current	AC: 10 A (NO)/3 A (NC) DC: 5 A (NO)/3 A (NC)	
Max. switching capacity	1250 VA, 150 W (NO) 750 VA, 90 W (NC)	
Min. permissible load (120 operations/minute)	10 mA at 5 VDC (P level: $\lambda_{60} = 0.1 \times 10^{-6}$ /operation)	

■ Characteristics

Contact resistance (See note 2.)	100 mΩ max.	
Operate time	10 ms max.	
Release time	5 ms max.	
Insulation resistance (See note 3.)	1,000 mΩ min.	
Dielectric strength	4,000 VAC, 50/60 Hz for 1 min between coil and contacts 1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity	
Impulse withstand voltage	8 kV (1.2 × 50 μs) between coil and contacts	
Vibration resistance	Destruction: 10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude) Malfunction: 10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude)	
Shock resistance	Destruction: 1000 m/s ² (approx. 100G) Malfunction: 100 m/s ² (approx. 10G)	
Life expectancy (See Note 4)	Mechanical	10,000,000 operations (18,000 operations per hour)
	Electrical	NO 50,000 operations: 10 A at 125 VAC resistive load (operations: ON for 1 sec, OFF for 3 sec.) 200,000 operations: 3 A at 125 VAC resistive load (operations: ON for 1 sec, OFF for 1 sec.) 100,000 operations: 3 A at 250 VAC resistive load (operations: ON for 1 sec, OFF for 1 sec.) 100,000 operations: 5 A at 30 VDC resistive load (operations: ON for 1 sec, OFF for 1 sec.) NC 200,000 operations: 3 A at 125 VAC resistive load (operations: ON for 1 sec, OFF for 1 sec.) 100,000 operations: 3 A at 250 VAC resistive load (operations: ON for 1 sec, OFF for 1 sec.) 100,000 operations: 3 A at 30 VDC resistive load (operations: ON for 1 sec, OFF for 1 sec.)
Ambient temperature	Operating & storage	−40°C to 105°C with no icing or condensation
Ambient humidity	Operating & storage	5% to 85%
Weight	Approx. 6.5 g	

Note: 1. The data shown above are initial values.

2. The contact resistance is measured with 1 A applied at 5 VDC using a fall-of-potential method.

3. The insulation resistance was measured with a 500 VDC megohmmeter at the same locations as the dielectric strength was measured.

4. The electrical life data items shown are possible at 23°C

■ Approved Standard

UL Recognized (File No. E41515) / CSA Certified (File No. LR31928) - - Ambient Temp = 40°C


Model	Contact Form	Coil ratings	Contact ratings	Number of test operations
G5Q	SPST-NO (1a) SPDT (1c)	5 to 48 VDC	10 A 250 VAC N.O. only (resistive)	6,000
			10 A 30 VDC N.O. only (resistive)	
			4 A 120 VAC N.O. only (resistive)	100,000
			3 A 250 VAC N.C. only (resistive)	6,000
3 A 30 VDC N.O. only (resistive)				

EC/IEC, VDE (Certified / No.40003467) - - Ambient Temp = 105°C


Model	Contact Form	Coil ratings	Contact ratings	Number of test operations
G5Q	SPST-NO (1a) SPDT (1c)	5, 9, 12, 24 VDC	10 A 250 VAC (cosφ=1)(N.O.) 5 A 30 VDC (0 ms)(N.O.) 3 A 30 VDC (0 ms)(N.C.)	10,000

Engineering Data


Maximum Switching Capacity



Ambient Temperature vs Maximum Coil Voltage






Shock Malfunction



Dimensions

Note: All units are in millimeters unless otherwise indicated.

G5Q-1A G5Q-1A4




* Average value

PCB Mounting Holes


(Bottom View)

Tolerance: ± 0.1 mm






Terminal Arrangement/ Internal Connections

(Bottom View)



(No coil polarity)

G5Q-1 G5Q-14




* Average value

PCB Mounting Holes


(Bottom View)

Tolerance: ± 0.1 mm



Terminal Arrangement/ Internal Connections

(Bottom View)



(No coil polarity)

Precautions

Be sure to read the precautions and information common to all Electromechanical Relays, contained in the Technical User's Guide, "Electromechanical Relays, Technical Information" for correct use.



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.
To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. J155-E-04

11/13

Specifications subject to change without notice

Printed in USA