

DATASHEET

Chip Infrared LED With Right Angle Lens SIR12-21C/TR8



Features

- Small double-end package
- Low forward voltage
- Good spectral matching to Si photo detector
- Package in 8mm tape on 7" diameter reel
- Pb free
- The product itself will remain within RoHS compliant version.

Descriptions

SIR12-21C/TR8 is an infrared emitting diode in miniature SMD package molded in a water clear plastic with right angle lens.

The device is spectrally matched with silicon photodiode and phototransistor.

Applications


- Household Appliances
- Electric Appliances
- Smoke detector
- Floppy disk drive


Device Selection Guide

Part Category	Chip Material	Lens Color	
SIR	GaAlAs	Water clear	





Package Dimensions





For reflow soldering (propose)





Notes: 1.All dimensions are in millimeters

2. Tolerances unless dimensions ±0.1mm

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Units	
Continuous Forward Current	I_{F}	65	mA	
Reverse Voltage	V_R	5	V	
Operating Temperature	T_{opr}	-25 ~ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	T_{stg}	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
Soldering Temperature *1	T_{sol}	260	$^{\circ}\!\mathbb{C}$	
Power Dissipation at(or below)	P_d	110	mW	
25°C Free Air Temperature				

Notes: *1. Soldering time ≤ 5 seconds.



Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Units
Radiant Intensity	Ie	$I_F=20mA$	0.5	0.9		mW /sr
Peak Wavelength	λp	$I_F=20mA$		875		nm
Spectral Bandwidth	Δλ	$I_F=20mA$		80		nm
Forward Voltage	V_{F}	I _F =20mA		1.3	1.6	V
Reverse Current	I_R	V _R =5V			10	μ A
View Angle	2 \theta 1/2	I _F =20mA		160		deg



Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Forward Current





Fig.4 Relative Intensity vs.






Typical Electro-Optical Characteristics Curves

Fig.5 Relative Radiant Intensity vs.

Angular Displacement






Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package, the LEDs should be kept at 30°C or less and 90%RH or less.
 - 2.3 The LEDs should be used within a year.
 - 2.4 After opening the package, the LEDs should be kept at 30° C or less and 60% RH or less.
 - 2.5 The LEDs should be used within 168 hours (7 days) after opening the package.
 - 2.6 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

 Baking treatment: 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.




4. Soldering Iron


Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing


Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Package Dimensions



Carrier Taping Dimensions: (Quantity: 2000PCS/Reel)



Note: The tolerances unless mentioned are ± 0.1 , unit=mm



Label Form Specification



CPN: Customer's Production Number

P/N: Production Number QTY: Packing Quantity

CAT: Ranks«

HUE: Peak Wavelength↓

REF: Reference₽

LOT No: Lot Number↓

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- These specification sheets include materials protected under copyright of EVERLIGHT
 corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's
 consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No. 6-8, Zhonghua Rd., Shulin Dist.,

New Taipei City 23860, Taiwan

Tel: 886-2-2685-6688

Fax: 886-2685-2699, 6897

http://www.everlight.com