



Pivot center 0.18  
 Full position 1  
 Operation limit 1.4min  
 On position 2.20



NOTE:  
 Rating: DC 12V 0.1A  
 Operating Force: 20±10gf  
 Lifetime: 100,000 Cycles

PART NO.
K5-1652UA-01
K5-1652UN-01

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Phosphor Bronze	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—

APPROVALS	DATE	TITLE:
DRAWN J.X.Zhang	2013/9/17	DETECTOR SWITCHS

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ.:
30~12.5 ±0.30 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10	±2°	mm	1:1	1st