

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	JLZ 06/06/16'	~	

NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
  - VOLTAGE RATING:125V.
  - CURRENT RATING:1.5A.
- ENVIRONMENT CHARACTERISTICS:
  - TEMPERATURE: -40°C~+85°C.
- MATERIALS
  - CONTACT MATERIAL: COPPER ALLOY.
  - CONTACT PLATING: SELECTIVE GOLD.
  - INSULATOR MATERIALS: PBT BLACK.
- PRODUCT NUMBER CODE:
 

DS1129-04-X X X X X - X

Shell Type  
S:W/ Shrapnel  
X:W/O Shrapnel





Housing Materials  
P:PBT

Contact Plating  
0:Seclective Gold Flash

Housing Color  
B:Black

No.Of Contacts  
8:8p8c

Connector Type  
S:Socket



PC BOARD LAYOUT  
THICKNESS=1.6mm

GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°
DRAWING TYPE		CUSTOMER	
SCALE		1:1	SHEET 1 OF 1
DRAWING NO.		C-DS1129-04-XXXXX-A	

PROJECTION		TITLE	PCB Jack 8 Positions 1*2 Port W/ Shell 3.56mm WITH LED Type
UNITS	mm	SHEET SIZE	A4
SHEET SIZE	A4	SERIES	DS1129-04 SERIES

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD

6-574-63508787  
Fax:86-574-63510817  
E-mail:sale@connfly.com  
http://www.connfly.com  
Industry Zone KuangYan  
Civi Ningbo China  
P.C:315333