規格承認書

PECIFICATION FOR APPROVAL

客 戶							
CUSTOMER	:						
項目	_						
ITEM	:	压电式无源蜂鸣器 (外部驱动)					
型號	_						
TYPE	:	GPC2316YB-5V2700					
描述	-						
DESCRIPTION	:	ф 23.0 x H16.0 mm	2700Hz	5V	≥100DB	P=15mm	材质 PBT
客戶料號							
CUSTOMER NO.:							
規格書號							
SPECIFICATION NO.:							
版本							
EDITION NO.	:	V1.0					
日 期							
DATE	:	2013-8-27					

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認				
TESTED BY	CHECKED BY	APPROVED BY				

東莞市赢海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認	
ISSUED BY	CHECKED BY	APPROVED BY	
周明	李林	李菲菲	


地址: 廣東省東莞市長安鎮廈邊元灶頭工業區 16-6 號

網址: HTTP://WWW.INGHAI.COM

DONGGUAN INGHAI ELECTRONICS CO.,LTD

Model NO: GPC2316YB-5V2700

A:DIMEMSIONS Unit:mm Tolerance: ± 0.5



B:SPECIFICATIONS


Model NO	GPC2316YB		
Rated Voltage	5Vp-p		
Sound Pressure level(dB)	Min.100dB at10cm/2.7KHZ/24VP-P		
Resonant Frequency	2700±500Hz		
Max. Current Consumption (mA)	Max. 5mA at Rated Voltage		
Capacitance at 1KHz	25000±30%		
Operating Voltage	1∼30 Vp-p		
Operating Temperature	-20 °C ~+70 °C		
Storage Temperature	-30 °C ~+80 °C		
Case material and color	PBT / Black		

Measuring condition


Part shall be measured under a condition (Temperature: $5\sim35^{\circ}$ C, Humidity: $45\%\sim85\%$ R.H., Atmospheric pressure: $860\sim1060h$ Pa) unless the standard condition (Temperature: $25\pm3^{\circ}$ C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860\sim1060h$ Pa) is regulated to measure.

C:Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:



D:Typical Frequency Response Curve



E:Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

1. Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10^{\circ}$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

2. High Temperature Test

The part shall be capable of with standing a storage temperature of +80°C for 96 hours.

3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30 $^{\circ}$ C for 96 hours.

4. Humidity Test

Temperature:+ $40\%\pm3\%$ Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

5. Temperature Shock Test

Temperature: 70° C /1hour \rightarrow 25 $^{\circ}$ C/3hours \rightarrow -30 $^{\circ}$ C/1hour \rightarrow 25 $^{\circ}$ C/3hours (1cycle)

Total cycle: 10 cycles

6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

7. Vibration Test

Vibration:1000cycles /min. Amplitude:1.5mm, Duration: 1 hour in each 3 axes

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.