

TAIWAN TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD

DONGGUAN TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD

承認書 Specification For Approval						
Customer: (客	戶)					
Description:	E品描述) S	MD0603燈珠側	發藍光			
Part number:(產	E品型號) TJ	-S1706SW6T(	GLC6B-A5			
Date: (日)	期)					
Approved By: (約 Prepared By:(我常						
Approval	Check	Design	Sales			
核准	審核	製作	業務			

Customer Service Hotline: **400-676-8616** TEL: 0769-8662 5999 0769-8200 2226 E-MIAL:dg@togialed.com

FAX: 0769-8200 2227 WEB: www.togialed.com TAIWAN TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD



DONGGUAN TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD

#### Features

1.7mm x 0.6mm SMT LED, 1.1mm thickness

Low power consumption

Wide view angle

Package: 4000pcs/reel


**RoHS** Compliant

#### Applications


Ideal for back light and indicator

Various colors and lens types available

### Package outlines



## **Recommend Pad Layout**





Part No.	Emitted color	Dice	Lens color
TJ-S1706SW6TGLC6B-A5	Blue	InGaN	Water transparent

#### Notes:

- 1. All dimensions are in millimeters (inches);
- 2. Tolerances are  $\pm 0.1$ mm (0.004inch) unless otherwise noted.




# Absolute maximum ratings (TA=25°C)


Parameter	Symbol	Value	Unit
Forward current	lf	30	mA
Reverse voltage	Vr	5	V
Power dissipation	Pd	108	mW
Operating temperature	Тор	-40 ~+80	°C
Storage temperature	Tstg	-40 ~+85	°C
Peak pulsing current (1/8 duty f=1kHz)	lfp	125	mA

Electro-optical characteristics (TA=25°C)

Parameter	Test Condition	Symbol	Value			Unit
Farameter			Min	Тур	Max	Onit
Wavelength at peak emission	lf=20mA	λp		465		nm
Spectral half bandwidth	lf=20mA	$\bigtriangleup \lambda$		25		nm
Dominant wavelength	lf=20mA	$\lambda$ d	460		475	nm
Forward voltage	lf=20mA	Vf	2.9		3.5	V
Luminous intensity	lf=20mA	lv	60	120		mcd
Viewing angle at 50% Iv	lf=10mA	<b>2</b> θ <b>1/2</b>		120		Deg
Reverse current	Vr=5V	lr			10	μA




# Optical characteristic curves




Wave Length(nm)

Forward Current vs. Forward Voltage



Forward Current (mA)


#### **Directive Characteristics**





### **Reflow Profile**

■ Reflow Temp/Time



Notes:

- 1.We recommend the reflow temperature 245°C(±5°C).the maximum soldering temperature should be limited to 260°C.
- 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.
- 3.Number of reflow process shall be 2 times or less.
- ■Soldering iron


Basic spec is  $\leq$  5sec when 260  $^\circ\!\mathrm{C}$  . If temperature is higher, time should be shorter

(+10  $^\circ\!\!\mathrm{C}\! \rightarrow$  -1sec ). Power dissipation of iron should be smaller than 20W,


and temperatures should be controllable . Surface temperature of the device should be under 230  $^\circ\!\mathrm{C}\,$  .

■Rework

- 1.Customer must finish rework within 5 sec under 260  $^\circ\!{\rm C}.$
- 2. The head of iron can not touch copper foil
- 3.Twin-head type is preferred.




Avoid rubbing or scraping the resin by any object, during high temperature, for example reflow solder etc.



### Test circuit and handling precautions

Test circuit



- Handling precautions
- 1. Over-current-proof

Customer must apply resistors for protection; otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
- 2.1 It is recommended to store the products in the following conditions: Humidity: 60% R.H. Max.

Temperature : 5℃~30℃(41°F~86°F)

- 2.2 Shelf life in sealed bag: 12 month at <5°C~30°C and <30% R.H. after the package is Opened, the products should be used within a week or they should be keeping to stored at ≦20 R.H. with zip-lock sealed.
- 3. Baking

It is recommended to baking before soldering when the pack is unsealed after 72hrs. The Conditions are as followings:


- 3.1 60 $\pm$ 3°C x(12~24hrs) and <5%RH, taped reel type
- 3.2 100 $\pm$ 3°C x(45min~1hr), bulk type
- 3.3 130 $\pm$ 3°C x(15~30min), bulk type



DONGGUAN TONGJIA OPTOELECTRONICS TECHNOLOGY CO., LTD

# Test items and results of reliability


Туре	Test Item	Test Conditions	Note	Number of Damaged
Environmental Sequence	Temperature Cycle	-20℃ 30min ↑↓ 80℃ 30min	100 cycle	0/22
	Thermal Shock	-20℃ 15min ↑↓ 80℃ 15min	100 cycle	0/22
	High Humidity Heat Cycle 30℃⇔ 65℃ 90%RH 24hrs/1cyc		10 cycle	0/22
	High Temperature Storage Ta=80℃		1000 hrs	0/22
	Humidity Heat Storage	Ta=60 ℃ RH=90%	1000 hrs	0/22
	Low Temperature Storage	Ta=-30℃	1000 hrs	0/22
Operation Sequence	Life Test	Ta=25℃ IF=20mA	1000 hrs	0/22
	High Humidity Heat Life Test	60℃ RH=90% IF=10mA	500 hrs	0/22
	Low Temperature Life Test	Ta=-20℃ IF=20mA	1000 hrs	0/22





# 1706 Series SMD Chip LED Lamps Packaging Specifications


• Feeding Direction













#### • Arrangement of Tape




## Notes:

- 1. Empty component pockets are sealed with top cover tape;
- 2. The maximum number of missing lamps is two;
- 3. The cathode is oriented towards the tape sprocket hole in accordance with ANSI/EIA RS-481 specifications.
- 4. 4,000 pcs/Reel.



## 1706 Series SMD Chip LED Lamps Packaging Specifications

• Packaging specifications



Notes:

Reeled products (numbers of products are 4,000pcs) packed in a seal off moisture-proof bag along with a desiccant one by one, ten moisture-proof bag of maximums (total maximum number of products are 40,000pcs) packed in an inside box (about size: 240x 220x 120mm) and four inside boxes of maximums are put in the outside box (about size: 460mm x 246mm x 250mm) Together with buffer material, and it is packed. (Part No., Lot No., quantity should appear on the label on the moisture-proof bag, part No. and quantity should appear on the label on the cardboard box.) The number of the loading steps of outside box (cardboard box) has it to three steps.