


### Features

- Low forward voltage drop
- High current capability
- High reliability
- High surge current capability
- Plastic material-UL flammability 94V-0

### Mechanical Data

- Case: Molded plastic DO-41
- Terminals: Plated leads solderable per MIL-STD-202, Method 208 guaranteed
- Polarity: Color band denotes cathode end
- Mounting Position: Any
- Making: Type Number
- Lead Free: For RoHS/Lead Free Version



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load


For capacitive load derate current by 20%

Type Number	SYMBOL	SR 120	SR 130	SR 140	SR 145	SR 150	SR 160	SR 180	SR 1100	SR 1150	SR 1200	SR 1250	Unit	
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	20	30	40	45	50	60	80	100	150	200	250	V	
Maximum RMS Voltage	$V_{RMS}$	14	21	28	31.5	35	42	56	70	105	140	175	V	
Maximum DC Blocking Voltage	$V_{DC}$	20	30	40	45	50	60	80	100	150	200	250	V	
Average Rectified Output Current (Note 1) @ $T_L = 90^\circ C$	$I_{F(AV)}$	1.0											A	
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	$I_{FSM}$	30											A	
$I^2t$ Rating for Fusing ( $t < 8.3ms$ )	$I^2t$	3.735											A <sup>2</sup> s	
Forward Voltage @ $I_F = 1.0A$	$V_{FM}$	0.55			0.7		0.85		0.92		0.95		V	
Peak Reverse Current @ $T_A = 25^\circ C$	$I_R$	0.1						0.05						mA
At Rated DC Blocking Voltage @ $T_A = 100^\circ C$		10.0						5.0						
Typical Junction Capacitance (Note 2)	$C_J$	110											pF	
Typical Thermal Resistance Junction to Ambient (Note 1)	$R_{\theta JA}$	80											°C/W	
Operating Temperature Range	$T_J$	-55 to +150											°C	
Storage Temperature Range	$T_{STG}$	-55 to +150											°C	


Note: 1. Leads maintained at ambient temperature at a distance of 9.5mm from the case

2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C


**Fig.1-FORWARD CURRENT DERATING CURVE**




**Fig.2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS**



**Fig.3-MAXIMUM NON-REPETITIVE SURGE CURRENT**



**Fig.4-TYPICAL JUNCTION CAPACITANCE**



## Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from DIYI.
- DIYI reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- DIYI disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- DIYI does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.

DIYI makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify DIYI for any damages resulting from such improper use or sale.
- Since DIYI uses lot number as the tracking base, please provide the lot number for tracking when complaining.