

## SOT-23 Plastic-Encapsulate MOSFETS



### FEATURE

TrenchFET Power MOSFET

### APPLICATIONS

- Load Switch for Portable Devices
- DC/DC Converter

MARKING: 6385



### ■ Maximum ratings ( $T_a=25^{\circ}\text{C}$ unless otherwise noted)

Characteristic 特性參數	Symbol 符號	Rate 額定值	Unit 單位
Drain-Source Voltage 漏極-源極電壓	$BV_{DSS}$	-60	V
Gate- Source Voltage 柵極-源極電壓	$V_{GS}$	$\pm 20$	V
Drain Current (continuous) 漏極電流-連續	$I_D$	-3.5	A
Drain Current (pulsed) 漏極電流-脈沖	$I_{DM}$	-10	A
Total Device Dissipation 總耗散功率 $T_A=25^{\circ}\text{C}$ 環境溫度為 $25^{\circ}\text{C}$	$P_D$	1400	mW
Junction 結溫	$T_J$	150	$^{\circ}\text{C}$
Storage Temperature 儲存溫度	$T_{stg}$	-55to+150	$^{\circ}\text{C}$

## SOT-23 Plastic-Encapsulate MOSFETS




■ Maximum ratings ( $T_a=25^{\circ}\text{C}$  unless otherwise noted)

Characteristic 特性參數	Symbol 符號	Min 最小值	Typ 典型值	Max 最大值	Unit 單位
Drain-Source Breakdown Voltage 漏極-源極擊穿電壓( $I_D = -250\mu\text{A}, V_{GS}=0\text{V}$ )	$BV_{DSS}$	-55	-60	—	V
Gate Threshold Voltage 柵極開啓電壓( $I_D = -250\mu\text{A}, V_{GS}=V_{DS}$ )	$V_{GS(th)}$	-1	—	-3	V
Diode Forward Voltage Drop 內附二極管正向壓降( $I_S = -2\text{A}, V_{GS}=0\text{V}$ )	$V_{SD}$	—	—	-1.2	V
Zero Gate Voltage Drain Current 零柵壓漏極電流( $V_{GS}=0\text{V}, V_{DS} = -60\text{V}$ )	$I_{DSS}$	—	—	-1	$\mu\text{A}$
Gate Body Leakage 柵極漏電流( $V_{GS}=\pm 20\text{V}, V_{DS}=0\text{V}$ )	$I_{GSS}$	—	—	$\pm 100$	nA
Static Drain-Source On-State Resistance 靜態漏源導通電阻( $I_D = -3\text{A}, V_{GS} = -10\text{V}$ )	$R_{DS(ON)}$	—	70	85	$\text{m}\Omega$
Static Drain-Source On-State Resistance 靜態漏源導通電阻( $I_D = -2\text{A}, V_{GS} = -4.5\text{V}$ )	$R_{DS(ON)}$	—	80	120	$\text{m}\Omega$
Input Capacitance 輸入電容 ( $V_{GS}=0\text{V}, V_{DS} = -15\text{V}, f=1\text{MHz}$ )	$C_{ISS}$	—	900	—	pF
Output Capacitance 輸出電容 ( $V_{GS}=0\text{V}, V_{DS} = -15\text{V}, f=1\text{MHz}$ )	$C_{OSS}$	—	100	—	pF
Turn-On Delay Time 開啓延遲時間 ( $V_{DS}=-30\text{V}, I_D=-1\text{A}, R_{GEN}=3\Omega, V_{GS}=-10\text{V}$ )	$t_{d(on)}$	—	38	—	ns
Turn-On Rise Time 開啓上升時間 ( $V_{DS}=-30\text{V}, I_D=-1\text{A}, R_{GEN}=3\Omega, V_{GS}=-10\text{V}$ )	$t_r$	—	18	—	ns
Turn-Off Delay Time 關斷延遲時間 ( $V_{DS}=-30\text{V}, I_D=-1\text{A}, R_{GEN}=3\Omega, V_{GS}=-10\text{V}$ )	$t_{d(off)}$	—	51	—	ns
Turn-On Fall Time 開啓下降時間 ( $V_{DS}=-30\text{V}, I_D=-1\text{A}, R_{GEN}=3\Omega, V_{GS}=-10\text{V}$ )	$t_f$	—	6	—	ns

Pulse Width  $\leq 300 \mu\text{s}$ ; Duty Cycle  $\leq 2.0\%$


**SOT-23 Plastic-Encapsulate MOSFETS**

**SOT-23 Package Outline Dimensions**



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	6°

**SOT-23 Suggested Pad Layout**



- Note:
1. Controlling dimension: in millimeters.
  2. General tolerance:  $\pm 0.05$ mm.
  3. The pad layout is for reference purposes only.