

#### SEMICONDUCTOR

### 400mW SOD-123 SURFACE MOUNT Small Outline Flat Lead Plastic Package High Voltage & High Conductance Fast Switching Diode

#### Absolute Maximum Ratings T<sub>A</sub> = 25°C unless otherwise noted


<b>3</b> - <b>1</b>						
Symbol	Parameter	Value	Units			
PD	Power Dissipation	400	mW			
T <sub>STG</sub>	Storage Temperature Range -65 to +150		°C			
TJ	Operating Junction Temperature +150		°C			
V <sub>RRM</sub>	RM Repetitive Peak Reverse Voltage 250		V			
I <sub>F(AV)</sub>	Average Rectified Forward Current	200	mA			

These ratings are limiting values above which the serviceability of the diode may be impaired.

## Green Product



SOD-123 Flat Lead



#### **Specification Features:**

- Fast Switching Diode
- General Purpose Diodes High Voltage Application Diodes
- Flat Lead SOD-123 Small Outline Plastic Package
- Surface Device Type Mounting
- RoHS Compliant
- Green EMC
- Matte Tin(Sn) Lead Finish
- Band Indicates Cathode

#### **Electrical Characteristics** $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter		Test Condition	Limits		Unit
Symbol			Test Condition	Min	Max	Unit
Bv	Breakdown Voltage	BAV19W	I <sub>R</sub> =100μΑ	120		Volts
		BAV20W		200		Volts
		BAV21W		250		Volts
I <sub>R</sub>	Reverse Leakage Current	BAV19W	V <sub>R</sub> =100V		100	nA
		BAV20W	V <sub>R</sub> =150V		100	nA
		BAV21W	V <sub>R</sub> =200V		100	nA
VF	Forward Voltage		I <sub>F</sub> =100mA		1.0	Volts
			I <sub>F</sub> =200mA		1.25	Volts
T <sub>RR</sub>	Reverse Recovery Time		I <sub>F</sub> =I <sub>R</sub> =30mA			
			R <sub>L</sub> =100Ω		50	nS
			I <sub>RR</sub> =3mA			
С	Capacitance		$V_R=0V$ , f=1 $M_{HZ}$		5.0	pF


#### DEVICE MARKING CODE:

Device Type	Device Marking		
BAV19W	H1		
BAV20W	H2		
BAV21W	H3		




SEMICONDUCTOR

#### **Typical Performance Characteristics**



# Total Capacitance







## 10<sup>6</sup> 10<sup>5</sup> Reverse Current, (nA) 10<sup>4</sup> 125°C 10<sup>3</sup> 75°C 10<sup>2</sup> 10<sup>1</sup> 25°C $10^{0}$ 100 200 0 300 400 500 Reverse Voltage, VR (V)


Reverse Current vs Reverse VoltageReverse

SEMICONDUCTOR



SEMICONDUCTOR

#### Flat Lead SOD-123 Package Outline





## NOTICE

The information presented in this document is for reference only. Tak Cheong reserves the right to make changes without notice for the specification of the products displayed herein.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Tak Cheong Semiconductor Co., Ltd., or anyone on its behalf, assumes no responsibility or liability for any damagers resulting from such improper use of sale.

This publication supersedes & replaces all information reviously supplied. For additional information, please visit our website <u>http://www.takcheong.com</u>, or consult your nearest Tak Cheong's sales office for further assistance.