

PRODUCT SPECIFICATION

新弘智

SPEC. NO: T-0602-058J

DATE: Aug. 7, 2018

CUSTOMER' S PRODUCT NAME:

EMTEK PRODUCT NAME:

CMF2012H4-Series

THIS SPECIFICATION IS:

- FULLY ACCEPTED
- DENIED
- ACCEPTED UNDER THE FOLLOWING CONDITIONS



SIGNATURE: _____

DATE: _____

NAME(PRINT): _____

TITLE: _____

 **EMTEK CO., LTD.**

本文件內容全部或部份,未經兆欣科技股份有限公司同意不得以任何形式複製或其他用途
All rights reserved.This document or parts thereof,may not be reproduced by any means or used in any manner without written permission of EMTEK CO.,LTD.

FACTORY:
39, Chingao Rd., (305)Hsinpu,
Hsinchu Hsien, Taiwan, R. O. C
TEL: 03-5894-433
FAX: 03-5894-523

PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J



1. Scope

This specification applies ferrite Chip common mode filters CMF2012H4-Series to be delivered to user.



2. Product Identification

CMF 2012 H4 - 900 - 2P - T



(1) (2) (3) (4) (5) (6)

- (1) Product name
- (2) Shapes and dimensions
- (3) Shielding Type
- (4) Impedance 【 at 100MHz 】
65min. (90typ.)
- (5) Number of Line
2P:2-Line
- (6) Taping Type

3. Shapes and Dimensions [Dimensions in mm]



A : 2.0 ± 0.2
 B : 1.2 ± 0.2
 C : 1.2 ± 0.2



Drawn by	Checked by	Approved by
Cindy Feb.23.2018	Zheng Feb.23.2018	Su Feb.23.2018

PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4. Electrical Characteristics

4-1 Electrical Spec.


Our Product Part Number	Common-Mode Impedance $Z(\Omega)$ at 100MHz	DC Resistance $R_{dc}(\Omega)$ Max.	Rated Current $I_{dc}(mA)$ Max.	Rated Voltage $V_{dc}(V)$	Cut-off Frequency (GHz)Typ.	Insulation Resistance (M Ω)Min.
CMF2012H4-420-2P-T	42 \pm 25%	0.12	400	20	5.0	10
CMF2012H4-500-2P-T	50 \pm 25%	0.30	400	20	5.0	10
CMF2012H4-600-2P-T	60 \pm 25%	0.31	320	20	4.0	10
CMF2012H4-670-2P-T	67 \pm 25%	0.31	320	20	4.0	10
CMF2012H4-900-2P-T	65min. (90typ.)	0.25	300	20	4.0	10
CMF2012H4-121-2P-T	120 \pm 25%	0.25	300	20	4.0	10

4-2-1 Characteristics(Reference)


CMF2012H4-420-2P-T




CMF2012H4-500-2P-T



CMF2012H4-900-2P-T



CMF2012H4-121-2P-T



PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4-2-2 Insertion loss(Reference)

CMF2012H4-420-2P-T


HDMI Choke Insertion Loss Graphic result

HDMI Choke Common Mode Insertion Loss C1 -(PASS)



CMF2012H4-420-2P-T

HDMI Choke Impedance Graphic result



Parameter Name: HDMI Choke Impedance C1	
Spc Max: 115 Ω	Spc Min: 85 Ω
Max: 101.66 Ohms at 1.3705 ns	Min: 101.00 Ohms at 2.8705 ns
$\Delta\Omega$: 0.66	Avg: 101.33 Ohms
Result: Pass	

PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4-2-2 Insertion loss(Reference)

CMF2012H4-500-2P-T


Choke Insertion Loss Graphic result

USB3 Choke Insertion Loss C1



CMF2012H4-500-2P-T

USB3 Choke Impedance Graphic result



PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4-2-2 Insertion loss(Reference)

CMF2012H4-670-2P-T


HDMI Choke Insertion Loss Graphic result

HDMI Choke Common Mode Insertion Loss C1-(PASS)



CMF2012H4-670-2P-T

HDMI Choke Impedance Graphic result



PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4-2-2 Insertion loss(Reference)

CMF2012H4-900-2P-T


HDMI Cat2 Attenuation (IL) Graphic result

HDMI Cat2 Attenuation (IL) choke



CMF2012H4-900-2P-T

HDMI Cat2 Transition Area Impedance Graphic result



PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J




4-2-2 Insertion loss(Reference)

CMF2012H4-121-2P-T


HDMI Choke Insertion Loss Graphic result

HDMI Choke Common Mode Insertion Loss C1



CMF2012H4-121-2P-T

HDMI Choke Impedance Graphic result



PRODUCT SPECIFICATION

SPEC. NO.


T-0602-058J



4-3 Test Equipment


4-3-1 Impedance

Measured by using Agilent E4991A RF Impedance Analyzer.




4-3-2 DC Resistance

Measured by using Chroma 16502 mill ohm meter.



4-3-3 Insulation Resistance





PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J



5. Reliability Test

Operating temperature : -40 to +105°C		Storage temp and humidity : 20~25°C ,60%RH max.
Item	Specifications	Test conditions
Solder ability	It can be connected on the Recommendation soldering condition.	Apply cream solder to the test circuit board . It is mounted on the recommendation soldering condition.
Terminal strength	The terminal electrode and the ferrite must not be damaged.	Solder a chip to test substrate , and then laterally apply a load 0.5Kg in the arrow direction. 
Strength on pc board bending	The terminal electrode and the ferrite must not be damaged.	Soldering a chip to a test substrate , bend the substrate by 2mm and then return.  <p>Dimensions in mm</p> <p>R10</p> <p>Force</p> <p>length</p> <p>Width side</p>
	Test board : Glass base epoxy multiplayer board pc board pattern. PC board pattern : Recommended PC board pattern.	


PRODUCT SPECIFICATION

SPEC. NO.

T-0602-058J



5. Reliability Test

Item	Specifications	Test conditions
High temperature resistance	Appearance : Ferrite shall not be damaged. Impedance : Within $\pm 20\%$ of the initial value. insulation resistance: $> 10(M\Omega)$ DC resistance : standard value inside.	Temperature : $+105\pm 2^{\circ}C$ Applied voltage : Rated voltage Applied current : Rated current Testing time : 50 ± 12 hours Measurement : After placing for 24 hours min.
Humidity resistance		Temperature : $+85\pm 2^{\circ}C$ Humidity : 90 to 95%RH Applied current : Rated current Applied voltage : Rated voltage Testing time : 500 ± 12 hours Measurement : After placing for 24 hours min.
Thermal cycle		Temperature : $-40^{\circ}C, +105^{\circ}C$ kept stabilized for 30 minutes each. Cycle : 5 cycle Measurement : After placing for 24 hours min. 
Low temperature resistance		Temperature : $-40\pm 2^{\circ}C$ Testing time : 48 ± 12 hours Measurement : After placing for 24 hours min.
Vibration	Appearance : Ferrite shall not be damaged.	Frequency : 10 to 50 Hz Amplitude : 1.52 mm Dimension and times : X ,Y and Z directions for 2 hours each.

PRODUCT SPECIFICATION

SPEC. NO.


T-0602-058J



6. Packaging

The packaging must be done not to receive any damage during transporting and storing


6-1 Tape dimensions



(Dimensions in mm; Tolerance : ± 0.1)

Symbol	W	P	P_0	P_1	A_o	B_o	K_o	t
Dimension	8	4	4	2	1.5	2.25	1.35	0.24


6-2 Reel dimensions



Dimension in mm

Symbol	T
ϕA	$180+0,-3$
ϕB	$60+1,-0$
ϕC	13 ± 0.2
D	2.2 ± 0.5
W	9.0 ± 0.3
t	1.2
R	1

6-3 Tapping figure



PRODUCT SPECIFICATION


SPEC. NO.

T-0602-058J



6-4 Packaging Form

There shall not continuation more than two vacancies of the product.



Material of carrier tape : Polystyrene

Material of cover tape : Polyester


6-5 Cover Tape Peel Strength

The force for tearing off cover tape is 0.05~0.69(N) in the arrow direction at the following conditions:

Temperature : 5 ~ 35°C

Humidity : 45 ~ 85%

Atmospheric pressure : 860 ~ 1060 hpa



6-6 Packing Quantity

φ180 mm reel T type : 2000 pcs./reel

PRODUCT SPECIFICATION

SPEC. NO.


T-0602-058J




7. Recommended Soldering Conditions (Please use this product by reflow soldering)

7-1 Recommended Footprint

Termination Number : Please refer to the equivalent circuit in chapter 3.



7-2 Recommended Reflow Pattern



7-3 Iron Soldering

Use a solder iron of less than 30W when soldering, do not allow the soldering iron tip directly touch the ferrite body outside of terminal electrode.

4 seconds max. at 260°C.

8. Attention in Case of Using

In case of using product, please avoid following matters:

Splashing water or salt water

Dew condenses

Toxic gas (Hydrogen sulfide, Sulfurous acid, Chlorine, Ammonia)

Vibrations or shocks which exceed the specified condition

Please be careful for the stress to this product by board flexure or something after the mounting.

9. Other

Recommended wire wound inductors should be used within 6 months from the time of delivery.