PRODUCT SPECIFICATION

MAME(PRINT):

TITILE:

DATE: Aug.7,2018



SPEC. NO: T-0602-171A

FACTORY:

39,Chingao Rd.,(305)Hsinpu, Hsinchu Hsien,Taiwan,R.O.C

TEL: 03-5894-433 FAX: 03-5894-523

本文件內容全部或部份,未經兆欣科技股份有限公司同意不得以任何形式複製或其他用途 All rights reserved. This document or parts thereof, may not be reproduced by any means or used in any manner witout written permission of EMTEK CO.,LTD.

SPEC. NO.

T-0602-171A



1. Scope


This specification applies ferrite Chip common mode filters CMF4532LC-Series to be delivered to user.

2. Product Identification

<u>CMF</u> 4532 LC - 101 - <u>2P</u> - <u>T</u> (1) (2) (3) (4) (5) (6)

- (1) Product name
- (2) Shapes and dimensions
- (3) Automotive
- (4) Inductance [at 100KHz] 101:100 Ω
- (5) Number of Line 2P:2-Line
- (6) For Customer Design

3. Shapes and Dimensions [Dimensions in mm]



A: $4.5 \pm 0.2 \text{ mm}$ B: $3.2 \pm 0.2 \text{ mm}$ C: $2.7 \pm 0.2 \text{ mm}$ D: $0.25 \pm 0.1 \text{ mm}$ E: 1.2 Typ. mmF: 1.0 Typ. mm

Drawn by	Checked by	Approved by
Jun. 15. 2017	Theray Jun-15-2017	Jan. 15. 2017

T-0602-171A

ROHS

4. Electrical Characterisitics

4-1 Electrical Spec.


Our Product Part Number	Z(Ω) Common Mode Impedance at 10MHz		L(uH) Common Mode Inductance at 100KHz	DCR(Ω) Max.	Idc(mA) Max.	Rated Voltage Vdc (V)Typ.	Withstand Voltage Vdc(V)	Insulation Resistance IR (ΜΩ)Min.
CMF4532LC-110-2P-T	min.	300	(+50%/-30%)	0.6	250	50	125	10
CMF4332LC-110-2P-1	typ.	600	11	0.6	250			
CMF4532LC-220-2P-T	min.	500	(+50%/-30%)	1.0	200	50	125	10
CMF4332LC-220-2P-1	typ.	1200	22	1.0				
CMF4532LC-510-2P-T	min.	1000	(+50%/-30%)	1.0	200	50	125	10
CMF4332LC-310-2F-1	typ.	2800	51	1.0				
CMF4532LC-101-2P-T	min.	2000	(+50%/-30%)	2.0	150	50	125	10
	typ.	5800	100	2.0				
CMF4532LC-201-2P-T	min.		(+50%/-30%)	4.5	100	50	125	10
CIVIT4332LC-201-2F-1	typ.		200	4.3	100			

Storage temp. and humidity : -40 to +85 $^{\circ}\text{C}\,$, 70%RH max


4-2Characteristics(Reference)

4-2-1 Z v.s. Freq.





Frequency (MHz)




T-0602-171A






4-2-1 Z v.s. Freq.







SPEC. NO.


T-0602-171A



4-3 Test Equipment


4-3-1 Inductance

Measured by using Agilent HP4284A Precision LCR Meter.



4-3-2 DC Resistance


Measured by using Chroma 16502 mill ohm meter.




4-3-3 Insulation Resistance

Measured by using Chroma 19073

Measurement voltage: 50v, Measurement time: 60 sec.



SPEC. NO.






5.Reliability Test

Operating temperature : -40 to +125℃		Storage temp and humidity: 20~25℃,60%RH max.				
Item	Specifications	Test conditions				
Board Flex	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 60 sec				
Terminal strength	The chip must not damage the terminal electrode and the ferrite.	Appendix 1 Note(AEC-Q200-006):Force of 1.8 kg for 60 seconds. Test Board				
Solderability	The electrodes shall be at least 95% covered with new solder coating.	Pre-heating: 150 °C, 1min Solder Composition: Sn/3.0Ag/0.5Cu Solder Temperature: 255±5 °C Immersion Time: 4±1sec				
Resistance to Soldering Heat	Appearance:No damage Inductance change shall be within ±20%.	Pre-heating: 150°C , 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 255±5°C Immersion Time: 10±1sec				
Resistance to Solvents	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.				
Mechanical Shock	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Pulse shape:Half-sine waveform Impact acceleration:100g Pulse duration: 6ms Number of shocks: 18 shocks (3 shocks for each face) Orientation:Bottom,top,left,right,front and rear faces				

SPEC. NO.





Item	Specifications	Test conditions				
Vibration	Appearance:No damage	Vibration waveform: Sine waveform				
	Inductance change shall be	Vibration frequency: 10Hz~2000Hz				
	within ±20%.	Vibration acceleration: 5g				
		Sweep rate: 0.764386otcave/minute				
		Duration of test: 12 cycles each of 3 orientations				
		20 minutes for each cycle Vibration axes: X, Y & Z				
High	Appearance:No damage	Temperature: 125±3°C				
Temperature	(for microscope of MEIJI WF10X/22)	Time:1000hrs				
Exposure	Inductance change shall be within ±30%.	Measured after exposure in the room condition for 24hrs				
(Storage)						
Biased	_	Temperature: 85±2°C				
Humidity		Relative Humidity: 85%				
Trainidity		Time: 1000hrs				
		Measured after exposure in the room condition for 24hrs				
		Treasured arter exposure in the room condition for 2 ims				
Operational		Temperature : 125±2°C				
Life		Appliend Current : Rated Current				
		Time :1000±24 hrs				
		Measured after exposure in the room condition for 24 hrs				
T	4	Total evalue 1000 evalue				
Temperature		Total cycles: 1000 cycles				
Cycling		Temperature Cycling Test Conditions: -40 to +125°C				
		Soak Mode Condition: 30 minutes				
Ĺ		Measured after exposure in the room condition for 24hrs				


SPEC. NO.

T-0602-171A



6. Reel Dimension & Tape Dimension


6-1 Reel Dimensions



Unit: mm

A	В	С	D	
13.2±0.5	60±2	13±0.5	180±2	

6-2 Tape Dimensions



Symbol	W	P	Е	F	P2	D	D1	Po	10Po
Dimension	12.00	8.00	1.75	5.50	2.00	1.50	1.50	4.00	40.00
SPEC.	±0.1	±0.1	±0.1	±0.05	±0.05	+0.10 -0.00	±0.1	±0.1	±0.2
Symbol	Ao	Во	Ko	t					_
Dimension	3.57	4.80	2.80	0.30					
SPEC.	±0.1	±0.1	±0.1	±0.05					

SPEC. NO.

T-0602-171A



6-3 Packaging Quantity

500pcs/reel

7. Equivalent Circuit & Recommened Footprint

