

ITEM :

CRYSTAL RESONATORS

TYPE :

NOMINAL FREQUENCY :

32. 768kHz

DT-38

SPEC No. :

1TC125AFNS027

Please acknowledge receipt of this specificaiton by signing and returning a copy to us.

	RECEIPT
DATE	
RECEIVED	(signature) (name)



1. Electrical characteristics (measured at +25±2°C)

(1) Nominal frequency	32.768 kHz
(2) Frequency tolerance	± 5 × 10 ⁻⁶ max.
(3) Loading capacitance	12.5 pF
(4) Equivalent resistance	30 kΩ max. / series
(5) Measurement drive level	$1.0 \pm 0.2 \mu\text{W}$
(6) Turnover temperature	25 ± 5°C
(7) Parabolic curvature constant	-4.0×10^{-8} / °C ² max.
(8) Insulation resistance	Lead to lead 500 MΩ min. at D.C. 100V Lead to case
(9) Operating temperature range	- 10 ~ + 60 °C
(10) Storage temperature range	- 20 ~ + 70 °C
(11) Aging	± 5 × 10 ⁻⁶ max. / year

Manufacturing location	Spec No.
Tianjin	1TC125AFNS044

2. Construction

TITLE

Date

(1) Holder	DT-38		
(2) Dimensions and marking	Refer to Fig-1 and Fig-2.		
3. Other specifications Use of Freon This related product is not used with any 0	DDC CLASS 1.		
TITLE DT-38 TYPE QUARTZ CRYSTAL SPECIFICATION	Remark		
Date	Spec. No.	Rev.	Page
2009/02/09	1TC125AFNS027		1/7
DAIOLINI		DN1 70000	1- 040

4. Dimensions



А	С	Н	к	L
dia.3.1 max.	8.3 max.	1.1 ± 0.2	dia.0.35±0.07	10.0±1.0

_	:~		1
-	1(1	-	
	IM		

(Unit: mm)

5. Marking

The manufacturer's code and manufacturing date should be marked on the surface of the holder as the following diagram shows.



(*) Year : The last digit of the manufactured year Ex) 2009 shall be marked as "9" Month : As shown in the table Ex) Feb. shall be marked as "B"

	Month	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
	Symbol	А	В	С	D	Е	F	G	Н	J	К	L	М
	Fig-2												
LITL D	.E T-38 TYPE Q	UARTZ	CRYST	AL SPEC	CIFICAT	ION	Rema	rk					
Date	;						Spec.	No.				Rev.	Pag
200	9/02/09							1TC12	5AFNS)27			2/7
					DA	ISHINK	J CORP				D	M-Z0002	2:style-010

6. Mechanical endurance

Item	Standard	Condition		
Vibration resistance	f ₀ : ±3×10 ⁻⁶ max.	(1) Vibration30 ~ 120Hz(2) Cycle2 min(3) G force3G(4) Time20 minX,Y,Z Each direction.		
Shock resistance	f ₀ : ±3×10 ⁻⁶ max.	Free drops from 75cm high onto a wooden board (3 cm thickness) Repeat 3 times. Measure 5 min after the test.		
Hermetical sealing	1×10 ⁻⁹ Pa-m ³ /s max.	Testing by Helium leak detector.		
Terminal strength	No visual damage	Bending terminals at +90°, at –90°, at +90°, and finally unbending at 0° 1mm from the bottom of case. One bend is counted as one time, it can be endured up to three times.		
Soldering heat resistance	f ₀ : ±3×10 ⁻⁶ max.	Dipping terminals to 1mm from the bottom of product into the solder pot at +245 \pm 5°C for 3s. Measuring 1h after the test at +25°C.		
Solder ability	90% min.	Terminals solder ability is at a bath temperature of +245±5°C for 3s. (with flux)		

7. Environmental endurance

Item	Standard	Condition
High temperature	f ₀ : ±3×10 ⁻⁶	+70°C × 24h
storage	max.	Measuring 2h after the test at +25°C.
Low temperature	f ₀ : ±3×10 ⁻⁶	-30°C × 24h
storage	max.	Measuring 2h after the test at +25°C.
Moisture	f ₀ : ±3×10 ⁻⁶	+40°C × 24h in 90 % relative humidity.
storage	max.	Measuring 2h after the test at +25°C.

TITLE	Remark		
DT-38 TYPE QUARTZ CRYSTAL SPECIFICATION			
Date	Spec. No.	Rev.	Page
2009/02/09	1TC125AFNS027		3/7
DAISHINKU	U CORP.	DM-Z0002:sty	/le-010

8. Packing

TITLE

Date

8.1. Inner box





9. Inside structure



No	Components	Materials	Finish/Specifications
(1)	Can	Nickel silver	Ni plating
(2)	Crystal blank	SiO ₂	-
(3)	Solder	Sn-Ag-Cu	-
(4)	Shell	42 alloy	Sn plating
(5)	Lead terminal	Kovar	Sn plating

This is a sketch of inside construction.

So the size of this drawing may not match with actual size.

TITLE DT-38 TYPE QUARTZ CRYSTAL SPECIFICATION	Remark		
Date	Spec. No.	Rev.	Page
2009/02/09	1TC125AFNS027		5/7
DAISHINK	U CORP.	DM-Z0002:sty	yle-010

10. User manual for tuning fork type crystal units (cylinder type)

10.1. Shock

Do not add excessive shocks to units, otherwise deterioration or non-oscillation may be caused. Please be careful not to drop the units and operate them in a shock free condition. Please also confirm conditions before applying automatic mounting or changing the condition of use.

10.2. Temperature and humidity

Operation or storage in high-temperature, low-temperature or high-humidity may cause deterioration of the units.

Please operate or store them under condition of normal temperature and normal humidity.

10.3. Solder heat

Solder which shall be melted at +217°C is used inside of these units, and therefore deterioration or non-oscillation may be caused if the units' body temperature reaches +150°C or over. Please use SMD or heat-resistant type units when applying the above temperature. Please be aware of temperature conditions or consult with us when applying flow-soldering. May we also remind you to solder at +280°C max. with 5s max., or at +260°C max. with 10s max. at the leads.

Please do not apply solder to the body of units directly, as it may cause deterioration.

10.4. Mounting

If a horizontal laying position on the circuit board is required, fix the units firmly.

Especially under the vibrating conditions, insert shock absorber between the unit and circuit board or fix the unit with elastic glue (silicon applied) onto the board.

Please do not put the glue on glass part of units.

If a vertical standing position on a circuit board is required it is suggested to keep the unit at least 3mm away from circuit board for DT-38 type and 2mm for DT-26 type.



10.5. Lead cutting and Lead forming

Please keep your lead cutters in good condition, when applying the lead cutting. If forming or reforming the leads, do not add excessive power to the roots of leads or press the sealing areas otherwise the glass may crack and leakages may be caused. Please do not cut or bend the leads within 0.5 mm from the base of the cylinder body.

10.6. Ultrasonic washing and ultrasonic welding

Since mounting by Ultrasonic welding and processing have a possibility of an excessive vibration spreading inside a crystal resonator and becoming the cause of characteristic deterioration and not oscillating, it does not recommend.

Please consult with us if ultrasonic washing is required.

10.7. Drive level

Oscillation in excessive drive level may cause deterioration or non-oscillation. For this product, drive level less than 1.0μ W is recommended. And original characteristics cannot be guaranteed when more than 2.0μ W is supplied.

Thank you very much.

Please do contact us to below if you have any question. Daishinku Corporation R&D Engineering Dept. 179-15 Mizuashi, Noguchi-cho, Kakogawa-city, Hyogo-pref., 675-0194 Japan Tel : +81 (79) 421-7200 Fax : +81 (79) 421-7240

TITLE DT-38 TYPE QUARTZ CRYSTAL SPECIFICATION	Remark			
Date	Spec. No.	Rev.	Page	
2009/02/09	1TC125AFNS027		6/7	
DAISHINK	DAISHINKU CORP.		DM-Z0002:style-010	

Rev. No.	Date	Reason	Contents	Approved	Checked	Drawn
-	2009/02/09		The first edition.	T.N		H.N

REVISION RECORD