


# 10A 250V AC Qualified Type SDDJE Series


Туре			Rocker
Circuit arrangement			DPST
Travel			3.4mm
Operating force			6±3N
Mounting method			Snap-in
Terminal type			For Lead
Frame			Without
Marking (knob)			-, O mark
C-UL-US			10AGP 250V AC
SEMKO			6A/96A 250V~, 10(6)/250~
VDE			6A/96A 250V~, 10(6)/250~
BS			6A/96A 250V~, 10(6)/250~
Ratings satisfying local electrical appliance and material safety law			125V 10A ‡
Operating temperature range			-10℃ to +55℃
Rating		10AGP 250V AC, 6A/96A 250V~	
Electrical	Contact resistance		100mΩ max.
performance	Insulation resistance		500MΩ min. 500V DC
	Voltage proof		2,000V AC for 1 minute
Mechanical performance	Terminal strength		50N for 1 minute (lead terminal) 5N for 1 minute (right-angle terminal)
	Actuator strength	Operating direction	25N
		Perpendicular direction	25N
Durability	Operating life		10,000 cycles 10A 250V AC


Environmental performance	Cold		-20°C 96h
	Dry heat  Damp heat		85℃ 96h
			40℃, 90 to 95%RH 96h
Minimum order unit (pcs.)		Japan	400
		Export	2,000

#### **Dimensions**



# Mounting Hole Reference Size






Direction of insertion


U-shaped Hole		Unit:mm
Thickness of mounting board	Y2	Z
0.75 to 1.1	19.5° <sub>-0.1</sub>	
1.1 to 1.7	19.7° <sub>-0.1</sub>	12.9 <sup>+0.1</sup>
1.7 to 2	19.9° <sub>-0.1</sub>	

Verify the performance under actual product conditions before use.

# Circuit Diagram



# Marking (knob)



### **Packing Specifications**

#### Tray

Number of packages 1 case / Japan (pcs.)		400
	1 case / export packing	2,000
Export package measurements (mm)		411×328×379

#### **Soldering Conditions**

#### **Reference for Hand Soldering**

Soldering temperature	350±10℃
Soldering time	3+1/0s

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. The lead terminals are also used as tab terminals (#187). (Use a positive lock connector type.)
- 3. The lead terminal type can be mounted onto a board. (Manual soldering required.)
- 4. Standard products apply Grade V-2 material (Flame Class). For Grade V-0 type please contact us.
- 5. Please place purchase orders per minimum order unit (integer).
- 6. Products other than those listed in the above chart are also available. Please contact us for details.