
# **G3VM-41GR8/61GR**□/61VR

MOS FET Relays SOP 4-pin, High-current and Low-ON-resistance Type

# MOS FET Relays in SOP4-pin that featuring the low ON resistance and high switching capacity as a mechanical relay.

(Unit: mm, Average)



40-V Relay: Continuous load current of 1 A max.
60-V Relay: Continuous load current of 1.7 A max.

\_\_\_\_\_

Special

SOP 4-pin



• Amusement equipment



**Note:** The actual product is marked differently from the image shown here.

RoHS Compliant


**■**Package

SOP 4-pin

## **■**Application Examples

- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Security equipment
- Industrial equipment
- Power circuit

# ■Model Number Legend



 $\frac{1}{1} \frac{2}{2} \frac{3}{3} \frac{4}{4} \frac{5}{5}$ 

 1. Load Voltage
 2. Contact form
 3. Package

 4: 40 V
 1: 1a (SPST-NO)
 G: SOP 4-pin

 6: 60 V
 V: Special SOP 4-pin

4. Additional function

R: Low ON resistance

5. Other informations

When specifications overlap, serial code is added in the recorded order.

# **Note:** The actual product is marked differently from the image shown here.

# **■**Ordering Information

	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Stick packaging		Tape packaging	
Package					Model	Minimum package quantity	Model	Minimum package quantity
		Surface-mounting Terminals	40 V	1000 mA	G3VM-41GR8	100 pcs.	G3VM-41GR8(TR)	2,500 pcs.
	4-			1000 IIIA	G3VM-61GR1		G3VM-61GR1(TR)	
SOP4	1a (SPST-NO)		60 V	1400 mA 1700 mA	G3VM-61VR	125 pcs.	G3VM-61VR(TR05)	500 pcs.
							G3VM-61VR(TR)	3,000 pcs.
					G3VM-61GR2	100 pcs.	G3VM-61GR2(TR05)	2,500 pcs.

\* The AC peak and DC value are given for the load voltage and continuous load current.

**Note:** To order tape packaging for Relays with surface-mounting terminals, add "(TR)" or "(TR05)" to the end of the model number.

## ■Absolute Maximum Ratings (Ta = 25°C)


	Item	Symbol	G3VM-41GR8	G3VM-61GR1	G3VM-61VR	G3VM-61GR2	Unit	Measurement conditions
	LED forward current	lF	30 50		0	30	mA	
Ħ	LED forward current reduction rate	ΔIF/°C	-0.3		0.5 -0.3		mA/°C	Ta ≥ 25°C
Input	LED reverse voltage	VR	5		6	5	V	
	Connection temperature	TJ	125			°C		
	Load voltage (AC peak/DC)	Voff	40		60		V	
¥	Continuous load current (AC peak/DC)	lo	1000		1400	1700	mA	
Output	ON current reduction rate	Δlo/°C -		-13.3 -14		-17	mA/°C	G3VM-41GR8/61GR1: Ta ≥ 50°C G3VM-61VR/61GR2: Ta ≥ 25°C
	Pulse ON current lop		2	3	4.2	5	Α	t=100 ms, Duty=1/10
	Connection temperature	TJ		12	25		°C	
Dielectric strength between I/O *		V <sub>I</sub> -O	15	00	3750	1500	Vrms	AC for 1 min
Ambient operating temperature		Ta	-40 to +85	-20 to +85	-40 to +110	-40 to +85	°C	With no icing or condensation
Ambient storage temperature		Tstg	-55 to +125	-40 to	+125	-55 to +125	°C	with no iding of condensation
Soldering temperature		_	260			°C	10 s	

<sup>\*</sup> The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

## **■Electrical Characteristics** (Ta = 25°C)

	Item	Symbol		G3VM-41GR8	G3VM-61GR1	G3VM-61VR	G3VM-61GR2	Unit	Measurement conditions
		VF	Minimum	1.18	1.0	1.1	1.18		
	LED forward voltage		Typical	1.33	1.15	1.27	1.33	V	IF=10 mA
			Maximum	1.48	1.3	1.4	1.48		
=	Reverse current	lr	Maximum		10			μΑ	VR=5 V
Input	Capacitance between terminals	Ст	Typical	70	15	7	0	pF	V=0, f=1 MHz
			Typical		1		0.6		G3VM-41GR8/61GR1/61GR2:
	Trigger LED forward current	IFT	Maximum	3			mA	lo=100 mA G3VM-61VR: lo=1400 mA	
	Release LED forward current	IFC	Minimum		0.	.1		mA	Ioff=100 μA
	Maximum resistance with output ON	Ron -	Typical	0.1	0.25	0.13	0.08	Ω	G3VM-61GR2/61VR: IF=5mA, Io= Continuous load current ratings, t<1s
Output			Maximum	0.13	0.7	0.25	0.13		G3VM-41GR8/61GR1: IF=5mA, Io= Continuous load current ratings
	Current leakage when the relay is open	ILEAK	Typical	_	0.2	2	1		G3VM-41GR8: Voff=30 V
			ILEAK	Maximum	1 100 1000	10	nA	G3VM-61GR1/61VR/61GR2: Voff=60 V	
	Capacitance between terminals	Coff	Typical	300	90	100	250	pF	V=0, f=1 MHz
Ca	pacitance between I/O terminals	C <sub>I-O</sub>	Typical	0.8				pF	f=1 MHz, Vs=0 V
Ins	sulation resistance between I/O	Rı-o	Minimum	1000					V <sub>I-O</sub> =500 VDC, RoH≤60%
ter	minals		Typical	108				ΜΩ	VI-0-300 VDO, ⊓011≥00%
Tu	rn-ON time	ton	Typical	1.2	1.4	2	0.7		
Tu	III-ON UIIIG		Maximum	3				ms	IF=5 mA, RL=200 $\Omega$ ,
Tu	rn-OFF time	toff	Typical 0	0.2	0.6	0.1	0.1	1115	VDD=20 V *
Tu	III-OI I uille	LOFF	Maximum	0.5	1		0.5		

#### \* Turn-ON and Turn-OFF Times



## **■**Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.


Item	Symbol		G3VM-41GR8	G3VM-61GR1	G3VM-61VR	G3VM-61GR2	Unit		
Load voltage (AC peak/DC)	VDD	Maximum	32		48	V			
On another LED forward		Maximum		5					
Operating LED forward current	lF	Typical	10		7.5	10			
Carrent		Maximum	20		2	mA			
Continuous load current (AC peak/DC)	lo	Maximum	1000		1400	1300			
Ambient operating	Ta	Minimum	-20						
temperature	l la	Maximum	6	00	100	65	°C		

## **■**Spacing and Insulation


Item	G3VM-□GR□ G3VM-61VR		Unit	
iteiii	Mini	mum	Ollit	
Creepage distances	4.0	5.0		
Clearance distances	4.0	5.0	mm	
Internal isolation thickness	0.1	0.2		

## **■**Engineering Data


# LED forward current vs. Ambient temperature




# Continuous load current vs. Ambient temperature




# LED forward current vs. LED forward voltage




# Continuous load current vs. On-state voltage




# On-state resistance vs. Ambient temperature




Trigger LED forward current vs. Ambient temperature




#### Turn ON, Turn OFF time vs. LED forward current







G3VM-61VR




● Turn ON, Turn OFF time vs. Ambient temperature G3VM-41GR8/61GR1/61GR2




#### G3VM-61VR



# Current leakage vs. Ambient temperature G3VM-41GR8/61GR1/61GR2




#### G3VM-61VR



## ■Appearance / Terminal Arrangement / Internal Connections

#### Appearance

#### SOP (Small Outline Package)




Note: 1. The actual product is marked differently from the image shown here.

Note: 2. "G3VM" does not appear in the model number on the Relay.

Note: 3. The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

# ●Terminal Arrangement/Internal Connections (Top View)




### ■Dimensions (Unit: mm)

SOP (Small Outline Package) SOP 4-pin




## Surface-mounting Terminals

Weight: 0.1 g



#### **Actual Mounting Pad Dimensions**

(Recommended Value, Top View)




Note: The actual product is marked differently from the image shown here.

Special SOP 4-pin \* (G3VM-61VR)




#### **Surface-mounting Terminals**

Weight: 0.1 g



#### **Actual Mounting Pad Dimensions**

(Recommended Value, Top View)



\* The external dimensions are different from those of the standard SOP 4-pin, but the mounting pad dimensions are the same.

Note: The actual product is marked differently from the image shown here.

# **■**Approved Standards

UL recognized **\$1** 

•				
Model	Approved Standards	Contact form	File No.	
G3VM-41GR8 G3VM-61GR1 G3VM-61GR2 G3VM-61VR	UL (recognized)	1a (SPST-NO)	E80555	

## **■**Safety Precautions

• Refer to the Common Precautions for All MOS FET Relays for precautions that apply to all MOS FET Relays.

Please check each region's Terms & Conditions by region website.

## **OMRON Corporation**

Electronic and Mechanical Components Company

#### **Regional Contact**

Americas

https://www.components.omron.com/

Asia-Pacific

https://ecb.omron.com.sg/

Korea

https://www.omron-ecb.co.kr/

Europe

http://components.omron.eu/

China

https://www.ecb.omron.com.cn/

Japan

https://www.omron.co.jp/ecb/

© OMRON Corporation 2018 All Rights Reserved.

In the interest of product improvement, specifications are subject to change without notice.

Cat. No. K304-E1-01 0318(0318)