# **ESD Protection Diode Array,** 5-Line

This 5-line surge protection array is designed for application requiring surge protection capability. It is intended for use in over-transient voltage and ESD sensitive equipment such as cell phones, portables, computers, printers and other applications. This device features a monolithic common anode design which protects five independent lines in a single SOT-563 package.

### **Features**

- Protects up to 5 Lines in a Single SOT-563 Package
- ESD Rating of Class 3B (Exceeding 8 kV) per Human Body Model and Class C (Exceeding 400 V) per Machine Model.
- Compliance with IEC 61000-4-2 (ESD) 15 kV (Air), 8 kV (Contact)
- This is a Pb-Free Device

# **Applications**

- Hand Held Portable Applications
- Serial and Parallel Ports
- Notebooks, Desktops, Servers

# MAXIMUM RATINGS (T<sub>J</sub> = 25°C, unless otherwise specified)

Symbol	Rating	Value	Unit
P <sub>PK</sub> 1	Peak Power Dissipation 8x20 μsec double exponential waveform, (Note 1)		W
TJ	Operating Junction Temperature Range	-40 to 125	°C
T <sub>STG</sub>	Storage Temperature Range		°C
TL	Lead Solder Temperature – Maximum (10 seconds)	260	°C
ESD	Human Body Model (HBM) Machine Model (MM) IEC 61000-4-2 Air (ESD) IEC 61000-4-2 Contact (ESD)	16000 400 15000 8000	٧

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Non-repetitive current pulse per Figure 1.



# ON Semiconductor®

www.onsemi.com

# SOT-563 5-LINE SURGE PROTECTION

### **PIN ASSIGNMENT**



PIN 1. CATHODE

- 2. ANODE
- 3. CATHODE
- 4. CATHODE
- 5. CATHODE
- 6. CATHODE



SOT-563 CASE 463A STYLE 6



**MARKING** 

RN = Specific Device Code

M = Month Code■ Pb-Free Package

(Note: Microdot may be in either location)

# **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
NUP5120X6T1G	SOT-563 (Pb-Free)	4000/Tape & Reel
NUP5120X6T2G	SOT-563 (Pb-Free)	4000/Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

# **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = 25°C, unless otherwise specified)

Parameter	Conditions	Symbol Min Typ		Тур	Max	Unit
Reverse Working Voltage	(Note 2)	$V_{RWM}$		-	5.0	V
Breakdown Voltage	I <sub>T</sub> = 1 mA, (Note 3)	$V_{BR}$	6.2	6.8	7.2	V
Reverse Leakage Current	V <sub>RWM</sub> = 3 V	I <sub>R</sub>	-	0.01	0.5	μΑ
Capacitance	$V_R = 0$ V, f = 1 MHz (Line to GND) $V_R = 2.5$ V, f = 1 MHz (Line to GND)	СЈ	-	54	70	pF

Surge protection devices are normally selected according to the working peak reverse voltage (V<sub>RWM</sub>), which should be equal or greater than the DC or continuous peak operating voltage level.
 V<sub>BR</sub> is measured at pulse test current I<sub>T</sub>.




Figure 1. Power Derating vs. Ambient Temperature




Figure 2. Peak Power vs. Pulse Duration




Figure 3. Peak Current vs. Clamp Voltage




Figure 4. Typical Capacitance vs. Reverse Voltage




Figure 5. Reverse Current vs. Reverse Voltage





Figure 6. Typical Forward Current vs. Forward Voltage

### PACKAGE DIMENSIONS

SOT-563, 6 LEAD CASE 463A **ISSUE G** 



#### NOTES


- DIMENSIONING AND TOLERANCING PER ANSI
- Y14.5M, 1982.
  2. CONTROLLING DIMENSION: MILLIMETERS
- MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH THICKNESS. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF BASE MATERIAL.

	MILLIMETERS			INCHES			
DIM	MIN	NOM	MAX	MIN	NOM	MAX	
Α	0.50	0.55	0.60	0.020	0.021	0.023	
b	0.17	0.22	0.27	0.007	0.009	0.011	
С	0.08	0.12	0.18	0.003	0.005	0.007	
D	1.50	1.60	1.70	0.059	0.062	0.066	
Е	1.10	1.20	1.30	0.043	0.047	0.051	
е	0.5 BSC			(	0.02 BSC		
L	0.10	0.20	0.30	0.004	0.008	0.012	
He	1.50	1 60	1 70	0.059	0.062	0.066	

- STYLE 6: PIN 1. CATHODE 2. ANODE 3. CATHODE

  - 4. CATHODE 5. CATHODE
  - CATHODE

# **SOLDERING FOOTPRINT\***



\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability on semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does on semiconductor assume any individual arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

# **PUBLICATION ORDERING INFORMATION**

# LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative