EVERLIGHT EVERLIGHT ELECTRONICS CO.,LTD.

Technical Data Sheet

Chip LED with Right Angle Lens

12-21/T3D-AQ2S2M/2C

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.

Descriptions

- The 12-21 SMD Taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide

Part No.	Chip		Long Colon	
Part No.	Material	Emitted Color	Lens Color	
12-21/T3D-AQ2S2M/2C	InGaN	Pure White	Yellow Diffused	



Everlight Electronics Co., Ltd. Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006


http://www.everlight.com


Rev. 1


Page: 1 of 12

Prepared by: Zhifang Pan


Package Outline Dimensions








For reflow soldering (propose)





Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd. Device No.: SZDSE-121-T03 http://www.everlight.com

Rev. 1

Page: 2 of 12

Prepared date:20-Sep-2006 Prepared by: Zhifang Pan



Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	
Reverse Voltage	VR	5	V	
Forward Current	IF	25	mA	
Peak Forward Current (Duty 1/10 @1KHz)	IFP	100	mA	
Power Dissipation	Pd	110	mW	
Electrostatic Discharge(HBM)	ESD	150	V	
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\!\mathbb{C}$	
Soldering Temperature	Tsol	Reflow Soldering : 260 °C for 10 sec. Hand Soldering : 350 °C for 3 sec.		

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	90		285	mcd	
Viewing Angle	2 \theta 1/2		130		deg	IF=20mA
Forward Voltage	VF	2.75		3.95	V	
Reverse Current	Ir			50	μ A	V _R =5V

Notes:

1. Tolerance of Luminous Intensity ±10%

2.Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 3 of 12

Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan



Bin Range Of Luminous Intensity & Forward Voltage

Symbol	Bin Code	Min.	Max.	Unit	Condition
	Q2	90.0	112		
	R1	112	140		
Iv	R2	140	180	mcd	IF=20mA
	S 1	180	225		
	S2	225	285		
VF	5	2.75	3.05		
	6	3.05	3.35	V	
	7	3.35	3.65		I _F =20mA
	8	3.65	3.95		

Notes:

1.Tolerance of Luminous Intensity ±10%

2.Tolerance of Forward Voltage ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 4 of 12 Device No.: SZDSE-121-T03

Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan



Chromaticity Coordinates Specifications for Bin Grading

Groups	Bin Code	CIE_x	CIE_y	Condition
	1	0.274	0.226	
		0.274	0.258	
		0.294	0.286	
		0.294	0.254	
		0.274	0.258	
	2	0.274	0.291	
	2	0.294	0.319	
		0.294	0.286	
		0.294	0.254	
	2	0.294	0.286	
	3	0.314	0.315	
A		0.314	0.282	I 20 A
A	4	0.294	0.286	IF=20mA
		0.294	0.319	
		0.314	0.347	
		0.314	0.315	
	5	0.314	0.282	
		0.314	0.315	
		0.334	0.343	
		0.334	0.311	
	6	0.314	0.315	
		0.314	0.347	
		0.334	0.376	
		0.334	0.343	


Notes:

- 1.The C.I.E. 1931 chromaticity diagram (Tolerance ±0.01).
- 2. The products are sensitive to static electricity and care must be fully taken when handling products.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 5 of 12

Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan

CIE Chromaticity Diagram




Everlight Electronics Co., Ltd. Device No.: SZDSE-121-T03 http://www.everlight.com Prepared date:20-Sep-2006 Rev. 1


Page: 6 of 12

Prepared by: Zhifang Pan

Typical Electro-Optical Characteristics Curves




CAT: Luminous Intensity Rank HUE: Chromaticity Coordinates REF: Forward Voltage Rank



MADE IN TAIWAN


Reel Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm


Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 8 of 12 Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd.

Device No.: SZDSE-121-T03

http://www.everlight.com

Prepared date: 20-Sep-2006

Rev. 1

Page: 9 of 12

Prepared by: Zhifang Pan



Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	$H: +100^{\circ}\mathbb{C}$ 15min $\int 5 \text{ min}$ $L: -40^{\circ}\mathbb{C}$ 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	$H: +100^{\circ}\mathbb{C}$ 5min $\int 10 \sec$ $L: -10^{\circ}\mathbb{C}$ 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°℃	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°€	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C / 85%RH	1000 Hrs.	22 PCS.	0/1

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 10 of 12

Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan

Precautions For Use


1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

2. Storage

- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 1 year under 30 deg C or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

 Baking treatment: 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 11 of 12

Device No.: SZDSE-121-T03 Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C

Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 1 Page: 12 of 12 Device No.: SZDSE-121-T03

Prepared date: 20-Sep-2006 Prepared by: Zhifang Pan