


DATASHEET


Infrared Remote Control Receiver Module IRM-66XXM3 Series



Pin Configuration

- 1. OUT
- 2. GND
- 3. V_{CC}

Block Diagram



Features

- · High protection ability against EMI
- · Circular lens for improved reception characteristics
- · Available for various carrier frequencies
- · Min burst length: 8 cycles
- · Min gap length: 12 cycles
- Low operating voltage and low power consumption
- · High immunity against ambient light
- · High immunity against TFT and PDP backlight
- · Long reception range
- High sensitivity
- · Pb free and RoHS compliant

Description

The IRM-66xxM3 devices are mini DIP type infrared receivers which have been developed and designed by using the latest IC technology.

The PIN diode and preamplifier are assembled onto a lead frame and molded into a black epoxy package which operates as an IR filter. The demodulated output signal can directly be decoded by a microprocessor.

Copyright © 2013, Everlight All Rights Reserved. Release Date: 19/2/2014 Issue No: DMO-0000251 Rev:2

1

www.everlight.com

Release Date:2014-03-10 10:57:26.0

Expired Period: Forever




Applications

- AV equipment such as TV, VCR, DVD, CD, MD, etc.
- CATV set top boxes
- Multi-media Equipment
- Other devices using IR remote control

IRM-66XXM3 Series Datasheet

Application Circuit



The RC Filter must be connected as close as possible to Vcc and GND pins.

Parts Table

Model No.	Carrier Frequency		
IRM-6636M3	36 kHz		
IRM-6638M3	38 kHz		

Revision

Release Date:2014-03-10 10:57:26.0

Expired Period: Forever

: 2 正式發行 LifecyclePhase: Approved



Absolute Maximum Ratings (T_a=25°C)

Parameter	Symbol	Rating	Unit
Supply Voltage	Vcc	6	V
Operating Temperature	Topr	-20 ~ +80	
Storage Temperature	Tstg	-40 ~ +85	
Soldering Temperature *1	Tsol	260	

 $^{^{\}star 1}$ 4mm from mold body for less than 5 seconds

Electro-Optical Characteristics (Ta=25 , Vcc=3V)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Current consumption	Icc		0.4	0.6	mA	No input signal
Supply voltage	V_{CC}	2.7	-	5.5	V	
Peak wavelength	λ_{p}		940		nm	
Decention range	L ₀	14			— m See chapter deg ,Test method'	
Reception range	L ₄₅	6				See chanter
Half angle(horizontal)	ϕ_{h}		±50			
Half angle(vertical)	ϕ_{v}		±50			
High level pulse width	Тн	450		750	μs Test signal	Test signal according to
Low level pulse width	T _L	450		750	μs	figure 1
High level output voltage	V_{OH}	Vcc-0.4			V	
Low level output voltage	V_{OL}		0.2	0.5	V	I _{SINK} 2mA
Internal pull up resistor	R_{PU}	85	100	115	kΩ	

<u>ح</u>

www.everlight.com

Expired Period: Forever

Revision : 2 Release Date:2014-03-10 10:57:26.0

Copyright © 2013, Everlight All Rights Reserved. Release Date : 19/2/2014 Issue No: DMO-0000251 Rev:2

LifecyclePhase: Approved



Test method

The specified electro-optical characteristics are valid under the following conditions.

- 1. Measurement environment
 - A place without extreme light reflections.
- 2. External light

The environment contains an ordinary, white fluorescent lamp without high frequency modulation. The color temperature is 2856K and the illumination at the IR receiver is less than 10 Lux (Ev 10Lux).


3. Standard transmitter

The test transmitter is calibrated by using the circuit shown in figure 2. The radiation intensity of the transmitter is adjusted until **Vo=400mVp-p.** Both, the test transmitter and the photo diode, have a peak wavelength of 940nm. The photo diode for calibration is PD438B (λp=940nm, Vr=5V).

4. The measurement system is shown in Fig.-3

Fig.-1 Transmitter Wave Form








Fig.-2 standard transmitter calibration





Fig.-3 Measuring System


Release Date: 2014-03-10 10:57:26.0


Expired Period: Forever







Typical Electro-Optical Characteristic Curves












Fig.8 Relative Sensitivity vs. Carrier Frequency


www.everlight.com Copyright © 2013, Everlight All Rights Reserved. Release Date : 19/2/2014 Issue No: DMO-0000251 Rev:2

Revision : 2 Release Date:2014-03-10 10:57:26.0 LifecyclePhase: **Expired Period: Forever**



Package Dimensions

(Dimensions in mm)



Notes:

Tolerances unless mentioned ±0.3mm. Unit: mm

Revision


Release Date:2014-03-10 10:57:26.0



Code information

Protocol	Suitable	Protocol	Suitable
JVC	Yes	RCA	No
Matsushita	Yes	Sharp	Yes
Mitsubishi	No	Sony 12 Bit	Yes
NEC	Yes	Sony 15 Bit	No
RC5	Yes	Sony 20 Bit	No
RC6	Yes	Toshiba	Yes
RCMM	No	XMP-1	Yes
RCS-80	No	Continuous Code	No

Device Marking



Notes

- 1 denotes Year code
- 2 denotes Month code
- 3 denotes Device number
- 4 denotes Carrier frequency

Packing Quantity

1500 pcs / Box

10 Boxes / Carton

Revision

Copyright © 2013, Everlight All Rights Reserved. Release Date : 19/2/2014 Issue No: DMO-0000251 Rev:2

www.everlight.com

Release Date:2014-03-10 10:57:26.0

Expired Period: Forever

Revision : 2 LifecyclePhase: Approved



DISCLAIMER

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without the specific consent of EVERLIGHT.

LifecyclePhase:

Release Date: 2014-03-10 10:57:26.0

www.everlight.com

Expired Period: Forever

Copyright © 2013, Everlight All Rights Reserved. Release Date: 19/2/2014 Issue No: DMO-0000251 Rev:2