Switch-mode Power Rectifier 150 V, 10 A

Features and Benefits

- Low Forward Voltage
- Low Power Loss/High Efficiency
- High Surge Capability
- 10 A Total (5 A Per Diode Leg)
- Guard-Ring for Stress Protection
- This is a Pb–Free Device

Applications

- Power Supply Output Rectification
- Power Management
- Instrumentation

Mechanical Characteristics:

- Case: Epoxy, Molded
- Epoxy Meets UL 94 V-0 @ 0.125 in
- Weight (Approximately): 1.9 Grams
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260°C Max. for 10 Seconds

MAXIMUM RATINGS


Please See the Table on the Following Page




ON Semiconductor®


www.onsemi.com

SCHOTTKY BARRIER RECTIFIER 10 AMPERES, 150 VOLTS



MARKING DIAGRAM





ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

MAXIMUM RATINGS (Per Diode Leg)

Rating		nbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _F	RRM RWM /R	150	V
	ELEG) I _F evice)	(AV)	5 10	А
Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60		SM	150	А
Operating Junction Temperature (Note 1)	-	Tj	-20 to +150	°C
Storage Temperature		stg	-65 to +150	°C
Voltage Rate of Change (Rated V _R)		v/dt	10000	V/µs
ESD Ratings: Machine Mod Human Body Mode	-		> 400 > 8000	V

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient: $dP_D/dT_J < 1/R_{\theta JA}$.

THERMAL CHARACTERISTICS

	Rating	Symbol	Value	Unit
Maximum Thermal Resistance	 Junction-to-Case 	$R_{ extsf{ heta}JC}$	2.5	°C/W

ELECTRICAL CHARACTERISTICS (Per Diode Leg)


Rating	Symbol	Тур	Max	Unit
Maximum Instantaneous Forward Voltage (Note 2) (I _F = 5 A, T _C = 25°C) (I _F = 5 A, T _C = 125°C)	VF	0.85 0.63	0.69	V
$\begin{array}{l} \mbox{Maximum Instantaneous Reverse Current (Note 2)} \\ (Rated DC Voltage, T_C = 25^{\circ}C) \\ (Rated DC Voltage, T_C = 125^{\circ}C) \end{array}$	i _R		45 20	μA mA


2. Pulse Test: Pulse Width = 300 μ s, Duty Cycle \leq 2.0%.

DEVICE ORDERING INFORMATION

Device Order Number	Package Type	Shipping [†]
MBRF10H150CTG	TO-220FP (Pb-Free)	50 Units / Rail

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.









Figure 8. Thermal Response Junction-to-Case for MBRF10H150CTG

PACKAGE DIMENSIONS

TO-220 FULLPACK, 3-LEAD CASE 221AH ISSUE F



FULLPAK is a trademark of Semiconductor Components Industries, LLC.

ON Semiconductor and the use are gistered trademarks of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries. SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at tww.onsemi.com/site/pdt/Patent–Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application. Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regardin

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81–3–5817–1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative