

## JST20xxH Series 20A TRIACS

### DESCRIPTION:

High current density due to double mesa technology, glass passivation, guaranteed maximum junction temperature 150° C.


JST20xxH series triacs are suitable for general purpose AC switching. They can be used as an ON/OFF function in applications such as static relays, washing machine, soymlik maker, flush toilet, hair drier, induction motor starting circuits...or for phase control operation light dimmers, motor speed controllers.

JST2035H -JST2050H are 3 quadrants triacs. They are specially recommended for use on inductive loads.

JST20xxHxA series are full pack plastic e, they provide a 2500V RMS isolation voltage from all three terminals to external heat sink.

### MAIN FEATURES

| Symbol                             | Value     | Unit |
|------------------------------------|-----------|------|
| I <sub>T</sub> (RMS)               | 20        | A    |
| V <sub>DRM</sub> /V <sub>RRM</sub> | 600 / 800 | V    |
| V <sub>TM</sub>                    | 1.5       | V    |



### ABSOLUTE MAXIMUM RATINGS

| Parameter  | Symbol                      | Value                 | Unit             |
|--|-----------------------------|-----------------------|------------------|
| Storage junction temperature range   | T <sub>stg</sub>            | -40 to +150           | °C               |
| Operating junction temperature range   | T <sub>j</sub>              | -40 to +150           | °C               |
| Repetitive Peak Off-state Voltage (T <sub>j</sub> =25°C)   | V <sub>DRM</sub>            | 600                   | V                |
| Repetitive Peak Reverse Voltage (T <sub>j</sub> =25°C)   |                             | 800                   |                  |
| Non repetitive Surge Peak Off-state Voltage (tp=10ms, T <sub>j</sub> =25°C)  | V <sub>D<sub>SM</sub></sub> | V <sub>DRM</sub> +100 | V                |
| Non repetitive Peak Reverse Voltage (tp=10ms, T <sub>j</sub> =25°C)  | V <sub>R<sub>SM</sub></sub> | V <sub>RRM</sub> +100 |                  |
| RMS on-state current (full sine wave)  | I <sub>T</sub> (RMS)        | 20                    | A                |
| TO-220A T <sub>c</sub> =95°C   |                             |                       |                  |
| TO-220B T <sub>c</sub> =110°C  |                             |                       |                  |
| Non repetitive surge peak on-state current (full cycle, T <sub>j</sub> =25°C)  | I <sub>T<sub>SM</sub></sub> | 190                   | A                |
| f=50Hz, t=20ms   |                             | 200                   |                  |
| I <sup>2</sup> t Value for fusing  | I <sup>2</sup> t            | 340                   | A <sup>2</sup> s |
| Critical rate of rise of on-state current (I <sub>G</sub> =2×I <sub>GT</sub> , tr≤100ns, f=120Hz, T <sub>j</sub> =150°C) | dI/dt                       | 50                    | A/μs             |
| Peak gate current (tp=20us, T <sub>j</sub> =150°C)   | I <sub>GM</sub>             | 4                     | A                |
| Peak Gate Power Dissipation (tp=20us, T <sub>j</sub> =150°C)   | P <sub>GM</sub>             | 10                    | W                |
| Average gate power dissipation (T <sub>j</sub> =150°C)   | P <sub>G(AV)</sub>          | 1                     | W                |

ELECTRICAL CHARACTERISTICS( $T_j=25^\circ\text{C}$  unless otherwise specified)

| Symbol          | Test Condition  | Quadrant |      | Limits  |         | Unit             |
|-----------------|---|----------|------|---------|---------|------------------|
|                 |   |          |      | JST2035 | JST2050 |                  |
| I <sub>GT</sub> | $V_D=12\text{V}$ $R_L=33\Omega$                               | I-II-III | MAX. | 35      | 50      | mA               |
| V <sub>GT</sub> |   | I-II-III | MAX. | 1.3     |         | V                |
| V <sub>GD</sub> | $V_D=V_{DRM}$ $R_L=3.3\text{K}\Omega$ $T_j=125^\circ\text{C}$ | I-II-III | MIN. | 0.2     |         | V                |
| I <sub>L</sub>  | $I_G=1.2I_{GT}$   | I-III    | MAX. | 55      | 70      | mA               |
|                 |   | II       | MAX. | 80      | 100     | mA               |
| I <sub>H</sub>  | $I_T=100\text{mA}$  |          | MAX. | 40      | 55      | mA               |
| dV/dt           | $V_D=67\%V_{DRM}$ gate open $T_j=125^\circ\text{C}$           |          | MIN. | 500     | 1000    | V/ $\mu\text{s}$ |
| (dI/dt)c        | Without snubber $T_j=125^\circ\text{C}$                       |          | MIN. | 13      | 22      | A/ms             |


## STATIC CHARACTERISTICS

| Symbol                               | Parameter                                  |                       | Value(MAX.)          | Unit          |
|--------------------------------------|--|-----------------------|----------------------|---------------|
| V <sub>TM</sub>                      | $I_{TM}=35\text{A}$ , $t_p=380\mu\text{s}$ |                       | T <sub>j</sub> =25°C | 1.5           |
| I <sub>DRM</sub><br>I <sub>RRM</sub> | $V_D=V_{DRM}$ $V_R=V_{RRM}$                | T <sub>j</sub> =25°C  | 10                   | $\mu\text{A}$ |
|                                      |  | T <sub>j</sub> =150°C | 5                    | mA            |


## THERMAL RESISTANCES

| Symbol               | Parameter                                |         | Value | Unit |
|----------------------|--|---------|-------|------|
| R <sub>th(j-c)</sub> | Junction to Case(AC)                     | TO-220A | 1.7   | °C/W |
|                      |  | TO-220B | 0.8   |      |
| R <sub>th(j-a)</sub> | Junction to ambient ( $S=1\text{cm}^2$ ) |         | 60    | °C/W |


## ORDERING INFORMATION



## PACKAGE MECHANICAL DATA



| Ref. | Dimensions  |      |      |        |       |       |
|------|-------------|------|------|--------|-------|-------|
|      | Millimeters |      |      | Inches |       |       |
|      | Min.        | Typ. | Max. | Min.   | Typ.  | Max.  |
| A    | 4.4         |      | 4.6  | 0.173  |       | 1.181 |
| B    | 0.61        |      | 0.88 | 0.024  |       | 0.034 |
| C    | 0.46        |      | 0.70 | 0.018  |       | 0.027 |
| C2   | 1.23        |      | 1.32 | 0.048  |       | 0.051 |
| C3   | 2.4         |      | 2.72 | 0.094  |       | 0.107 |
| D    | 8.6         |      | 9.7  | 0.338  |       | 0.382 |
| E    | 9.8         |      | 10.4 | 0.386  |       | 0.409 |
| F    | 6.55        |      | 6.95 | 0.258  |       | 0.274 |
| G    |             | 2.54 |      |        | 0.1   |       |
| H    | 28.0        |      | 29.8 | 11.0   |       | 11.7  |
| L1   |             | 3.75 |      |        | 0.147 |       |
| L2   | 1.14        |      | 1.7  | 0.044  |       | 0.066 |
| L3   | 2.65        |      | 2.95 | 0.104  |       | 0.116 |
| V1   |             | 45°  |      |        | 40°   |       |



| Ref. | Dimensions  |      |      |        |       |       |
|------|-------------|------|------|--------|-------|-------|
|      | Millimeters |      |      | Inches |       |       |
|      | Min.        | Typ. | Max. | Min.   | Typ.  | Max.  |
| A    | 4.4         |      | 4.6  | 0.173  |       | 1.181 |
| B    | 0.61        |      | 0.88 | 0.024  |       | 0.034 |
| C    | 0.46        |      | 0.70 | 0.018  |       | 0.027 |
| C2   | 1.21        |      | 1.32 | 0.048  |       | 0.051 |
| C3   | 2.4         |      | 2.72 | 0.094  |       | 0.107 |
| D    | 8.6         |      | 9.7  | 0.338  |       | 0.382 |
| E    | 9.6         |      | 10.4 | 0.378  |       | 0.409 |
| F    | 6.2         |      | 6.6  | 0.244  |       | 0.259 |
| G    |             | 2.54 |      |        | 0.1   |       |
| H    | 28.0        |      | 29.8 | 11.0   |       | 11.7  |
| L1   |             | 3.71 |      |        | 0.146 |       |
| L2   | 1.14        |      | 1.7  | 0.044  |       | 0.066 |
| L3   | 2.65        |      | 2.95 | 0.104  |       | 0.116 |
| V1   |             | 45°  |      |        | 40°   |       |

FIG.1: Maximum power dissipation versus RMS on-state current(full cycle)




FIG.3: On-state characteristics (maximum values)




FIG.5: Non-repetitive surge peak on-state current for a sinusoidal pulse with width  $t_p < 10\text{ms}$ , and corresponding value of  $I^2t$ .




FIG.2: RMS on-state current versus case temperature(full cycle)




FIG.4: Surge peak on-state current versus number of cycles.




FIG.6: Relative variation of gate trigger current,holding current and latching current versus junction temperature(typical values).

