

Surface Mount Type

Series : **ZC** Type : **V**

High temperature Lead-Free reflow



Features

- Endurance: 4000 h at 125 °C (High temperature / Long life)
- Low ESR and high ripple current (85 % over, Lower ESR than current V-TP)
- High-withstand voltage (25 V.DC to 80 V.DC), Low LC (0.01 CV or 3 μA)
- Equivalent to conductive polymer type aluminum electrolytic capacitor (There are little characteristics change by temperature and frequency)
- Vibration-proof product is available upon request. New lineup of φ6.3 product. (φ6.3 mm and larger)
- AEC-Q200 compliant
- RoHS directive compliant

Specifications

Size code	C	D	D8	F	G
Category temp. range	-55 °C to +125 °C				
Rated voltage range	25 V.DC to 50 V.DC	25 V.DC to 63 V.DC		25 V.DC to 80 V.DC	
Nominal cap.range	10 μF to 33 μF	10 μF to 56 μF	22 μF to 100 μF	22 μF to 220 μF	33 μF to 330 μF
Capacitance tolerance	±20 % (120 Hz/+20 °C)				
DC leakage current	I ≤ 0.01 CV or 3 (μA) After 2 minutes (whichever is greater)				
Dissipation factor (tan δ)	Please see the attached standard products list				
Endurance 1	125 °C, 4000 h, apply the rated ripple current without exceeding the rated voltage				
	Capacitance change	Within ±30% of the initial value			
	tan δ	≤ 200 % of the initial limit			
	E. S. R.	≤ 200 % of the initial limit			
Endurance 2	125 °C, 3000 h, apply the rated ripple current without exceeding the rated voltage				
	Capacitance change	Within ±30% of the initial value			
	tan δ	≤ 200 % of the initial limit			
	E. S. R.	≤ 300 % of the initial limit			
Shelf life	After storage for 1000 hours at +125 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)				
	85 °C, 85 % to 90 %, 2000 h, rated voltage applied				
Damp heat (Load)	85 °C, 85 % to 90 %, 2000 h, rated voltage applied				
	Capacitance change	Within ±30% of the initial value			
	tan δ	≤ 200 % of the initial limit			
	E. S. R.	≤ 200 % of the initial limit			
Resistance to soldering heat	After reflow soldering and then being stabilized at +20 °C, capacitors shall meet the following limits.				
	Capacitance change	Within ±10% of the initial value			
	tan δ	Within the initial limit			
	DC leakage current	Within the initial limit			

Marking Dimensions (not to scale)

Example : 25 V.DC 33 μF Marking color : BLACK

Rated voltage mark

E	25 V.DC	J	63 V.DC
V	35 V.DC	K	80 V.DC
H	50 V.DC		

() Reference size (Unit : mm)

Size code	D	L	A, B	H	I	W	P	K
C	5.0	5.8±0.3	5.3	6.5 max.	2.2	0.65±0.1	1.5	0.35 ^{+0.15} _{-0.20}
D	6.3	5.8±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 ^{+0.15} _{-0.20}
D8	6.3	7.7±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 ^{+0.15} _{-0.20}
F	8.0	10.2±0.3	8.3	10.0 max.	3.4	0.90±0.2	3.1	0.70±0.2
G	10.0	10.2±0.3	10.3	12.0 max.	3.5	0.90±0.2	4.6	0.70±0.2

· The dimensions of the vibration-proof products, please refer to the page of the mounting specification.

Standard products

Endurance 1 : 125 °C 4000 h
Endurance 2 : 125 °C 3000 h

Rated voltage (V.DC)	Capacitance (±20 %) (μF)	Case size (mm)		Size code	Specification				Part number		Min. packaging qty
		φD	L		Ripple current (100 kHz) (+125 °C) (mA r.m.s.)	ESR (100 kHz) (+20 °C) (mΩ)	tan δ (120 Hz) (+20 °C)	Standard Product	Vibration-proof product	Taping (pcs)	
											Endurance 1
25	33	5	5.8	C	550	–	80	0.14	EEHZC1E330R	–	1000
	56	6.3	5.8	D	900	–	50	0.14	EEHZC1E560P	NEW EEHZC1E560V	1000
	100	6.3	7.7	D8	1400	–	30	0.14	EEHZC1E101XP	NEW EEHZC1E101XV	900
	220	8	10.2	F	1600	1900	27	0.14	EEHZC1E221P	EEHZC1E221V	500
	330	10	10.2	G	2000	2900	20	0.14	EEHZC1E331P	EEHZC1E331V	500
35	22	5	5.8	C	550	–	100	0.12	EEHZC1V220R	–	1000
	47	6.3	5.8	D	900	–	60	0.12	EEHZC1V470P	NEW EEHZC1V470V	1000
	68	6.3	7.7	D8	1400	–	35	0.12	EEHZC1V680XP	NEW EEHZC1V680XV	900
	150	8	10.2	F	1600	1900	27	0.12	EEHZC1V151P	EEHZC1V151V	500
	270	10	10.2	G	2000	2800	20	0.12	EEHZC1V271P	EEHZC1V271V	500
50	10	5	5.8	C	500	–	120	0.10	EEHZC1H100R	–	1000
	22	6.3	5.8	D	750	–	80	0.10	EEHZC1H220P	NEW EEHZC1H220V	1000
	33	6.3	7.7	D8	1100	–	40	0.10	EEHZC1H330XP	NEW EEHZC1H330XV	900
	68	8	10.2	F	1250	–	30	0.10	EEHZC1H680P	EEHZC1H680V	500
	100	10	10.2	G	1600	–	28	0.10	EEHZC1H101P	EEHZC1H101V	500
	120	10	10.2	G	1600	–	28	0.10	EEHZC1H121P	EEHZC1H121V	500
63	10	6.3	5.8	D	700	–	120	0.08	EEHZC1J100P	NEW EEHZC1J100V	1000
	22	6.3	7.7	D8	900	–	80	0.08	EEHZC1J220XP	NEW EEHZC1J220XV	900
	33	8	10.2	F	1100	–	40	0.08	EEHZC1J330P	EEHZC1J330V	500
	56	10	10.2	G	1400	–	30	0.08	EEHZC1J560P	EEHZC1J560V	500
	NEW 68	10	10.2	G	1400	–	30	0.08	EEHZC1J680P	EEHZC1J680V	500
80	NEW 82	10	10.2	G	1400	–	30	0.08	EEHZC1J820P	EEHZC1J820V	500
	22	8	10.2	F	1050	–	45	0.08	EEHZC1K220P	EEHZC1K220V	500
	33	10	10.2	G	1360	–	36	0.08	EEHZC1K330P	EEHZC1K330V	500
	47	10	10.2	G	1360	–	36	0.08	EEHZC1K470P	EEHZC1K470V	500

· Please refer to the page of "Reflow profile" and "The taping dimensions".

Frequency correction factor for ripple current

Rated capacitance	Frequency	100 Hz ≤ f < 200 Hz	200 Hz ≤ f < 300 Hz	300 Hz ≤ f < 500 Hz	500 Hz ≤ f < 1 kHz
C < 47 μF	Correction factor	0.10	0.10	0.15	0.20
47 μF ≤ C < 150 μF		0.15	0.20	0.25	0.30
150 μF ≤ C		0.15	0.25	0.25	0.30
Rated capacitance	Frequency	1 kHz ≤ f < 2 kHz	2 kHz ≤ f < 3 kHz	3 kHz ≤ f < 5 kHz	5 kHz ≤ f < 10 kHz
C < 47 μF	Correction factor	0.30	0.40	0.45	0.50
47 μF ≤ C < 150 μF		0.40	0.45	0.55	0.60
150 μF ≤ C		0.45	0.50	0.60	0.65
Rated capacitance	Frequency	10 kHz ≤ f < 15 kHz	15 kHz ≤ f < 20 kHz	20 kHz ≤ f < 30 kHz	30 kHz ≤ f < 40 kHz
C < 47 μF	Correction factor	0.60	0.65	0.70	0.75
47 μF ≤ C < 150 μF		0.70	0.75	0.80	0.80
150 μF ≤ C		0.75	0.80	0.85	0.85
Rated capacitance	Frequency	40 kHz ≤ f < 50 kHz	50 kHz ≤ f < 100 kHz	100 kHz ≤ f < 500 kHz	500 kHz ≤ f
C < 47 μF	Correction factor	0.80	0.85	1.00	1.05
47 μF ≤ C < 150 μF		0.85	0.90	1.00	1.00
150 μF ≤ C		0.85	0.90	1.00	1.00

After endurance ESR (100 kHz, –40 °C)

Size	φ5×5.8	φ6.3×5.8	φ6.3×7.7	φ8×10.2	φ10×10.2
ESR (Ω)	2.0	1.4	0.8	0.4	0.3

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.