

M HF ROHS


Surface Mount 2-Electrode Gas Discharge Tube (GDT)

UN1206 Series

Description

Gas discharge Tubes (GDT) are classical components for protecting the installations of the telecommunications. It is essential that IT and telecommunications systems -with their high-grade but sensitive electronic circuits - be protected by arresters.

The 1206 series GDT offers high surge ratings in a miniature package. It's designed for surface mounting on PCB with small size 3.2x1.6x1.6mm. Low insertion loss is perfectly suited to broadband equipment applications. The capacitance does not vary with voltage, and will not cause operational problems with ADSL2+, where capacitance variation across Tip and Ring is undesirable. These devices are extremely robust and are able to divert a 500A pulse in a miniature package 1206 without destruction.



Schematic Symbol



Agency Approvals

AGENCY	AGENCY FILE NUMBER
A	E341061

Product Characteristics

Materials	Dull Tin-plated
Product Marking	Without
Storage and Operational Temperature	-40 to +90°C
Weight	~30mg
Climatic category (IEC 60068-1)	40/ 90/ 21

Features

- u Non-Radioactive
- **RoHS** compliant u
- Ultra low capacitance (<0.5pF) u
- UL recognized u
- Excellent response to fast rising transients u
- 0.5KA surge capability tested with 8/20µs u pulse as defined by IEC 61000-4-5
- Square Outline u

Applications

- u Communication equipment
- CATV equipment u
- u Test equipment
- Data lines u
- u Power supplies
- Telecom SLIC protection u
- Broadband equipment u
- ADSL equipment, including ADSL2+ u
- **XDSL** equipment u
- u Satellite and CATV equipment
- u General telecom equipment
- ESD protection u

SOCAY Electronics Co., Ltd.

1/4


www.socay.com




Surface Mount 2-Electrode Gas Discharge Tube (GDT)

UN1206 Series

Device Dimensions (Unit: mm)





Recommended pad outline

Electrical Characteristics

Part Number	DC Spark-over Voltage	Maximum Impulse Spark-over Voltage		Minimum Insulation Resistance	Maximum Capacitance	Arc Voltage	Nominal Impulse Discharge Current	Impulse Discharge Voltage
	@100V/S	@100V/µs	@1KV/µs		@1MHz	@0.2A	@8/20µs ±5 times	@10/700µs
UN1206-150ASMD	150V±30%	≤600V	≤700V	1 GΩ (at 50V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-200ASMD	200V±30%	≤650V	≤750V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-230ASMD	230V±30%	≤650V	≤750V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-300ASMD	300V±30%	≤700V	≤800V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-350ASMD	350V±30%	≤750V	≤850V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-400ASMD	400V±30%	≤850V	≤950V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-420ASMD	420V±30%	≤850V	≤950V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-470ASMD	470V±30%	≤950V	≤1050V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
UN1206-400ASMD+	>400V	≤850V	≤1050V	1 GΩ (at 100V DC)	<0.5pF	~10V	0.5KA	4KV
Notes: 1). Terms in accordance with ITU-T K.12 and GB/T 9043-2008 2). At delivery AQL 0.65 level II , DIN ISO 2859								



HF Rohs W


Surface Mount 2-Electrode Gas Discharge Tube (GDT)

UN1206 Series

Electrical Rating

Item	Test Condition / Description	Requirement
DC Spark-over Voltage	The voltage is measured with a slowly rate of rise dv / dt=100V/s	
Impulse Spark-over Voltage	The maximum impulse spark-over voltage is measured with a rise time of dv / dt=100V//µs or 1KV/µs	
Insulation Resistance	The resistance of gas tube shall be measured each terminal each other terminal, please see above spec.	
Capacitance	The capacitance of gas tube shall be measured each terminal to each other terminal. Test frequency :1MHz	
Nominal Impulse Discharge Current	The maximum current applying a waveform of 8/20µs that can be applied across the terminals of the gas tube. One hour after the test is completed, re-testing of the DC spark-over voltage does not exceed ±40% of the nominal DC spark-over voltage. Dwell time between pulses is 3 minutes.	

Recommended soldering profile



Reflow Condition		Pb - Free assembly	
	-Temperature Min (T _{s(min)})	150°C	
Pre Heat	-Temperature Max (T _{s(max)})	200°C	
	- Time (min to max) (t _s)	60 -180 Seconds	
Average ramp up rate (Liquidus Temp T_L) to peak		3°C/second max	
T _{S(max)} to TL - Ramp-up Rate		5°C/second max	
Reflow	- Temperature (T _L) (Liquidus)	217°C	
Kenow	- Time (min to max) (t _s)	60 -150 Seconds	
Peak Temperature (T _P)		260 +0/-5°C	
Time within 5°C of actual peak Temperature (t _p)		10 - 30 Seconds	
Ramp-dow	n Rate	6°C/second max	
Time 25°C to peak Temperature (T _P)		8 minutes Max	
Do not exceed		260°C	

SOCAY Electronics Co., Ltd.





HF Rohs N

Surface Mount 2-Electrode Gas Discharge Tube (GDT)

UN1206 Series

Part Numbering





Caution	e and	warni	ane

- $\textbf{u} \quad \text{Gas discharge tubes (GDT) must not be operated directly in power supply networks.}$
- u Gas discharge tubes (GDT) may become hot in case of longer periods of current stress (danger of burning).
- Gas discharge tubes (GDT) may be used only within their specified values. In the event of overload, the head contacts may fail or the component may be destroyed.

Part Number

UN1206-XXXASMD

u Damaged Gas discharge tubes (GDT) must not be re-used.

SOCAY Electronics	Co.,	Ltd.
-------------------	------	------

www.socay.com

Quantity

2500

Description

12mm Tape & 7" Reel