



- NOTES:
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. TERM. NOS. FOR REFERENCE ONLY.
 4. RATING: 50VDC, 50mA
 - ▲ 5. OPERATING FORCE: 160 ± 50 gms
 6. TRAVEL: 0.25 mm ±0.2/-0.1mm
 7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
 8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
 9. SILVER CONTACTS
 - ▲ 10. PACKAGING: TAPE AND REEL, 750 PCS. PER REEL
 11. ▲ DENOTES CRITICAL PARAMETER
 12. 2002/95/EC (ROHS) COMPLIANT



B	20881	Reel Qty was 700	11/14/12	rc
A	20798	NEW RELEASE	10/01/12	rc
REV	PCR NO	DESCRIPTION	DATE	BY

TITLE TL3301EF160QG				
SCALE	DATE	DR	DWG	REV
4:1	10/1/2012	rc	P010663	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED