

# Specification for Approval

**Date:** 2017/05/28

**Customer :** 深圳台慶

**TAI-TECH P/N:** AHP201610TF-SERIES

**CUSTOMER P/N:** \_\_\_\_\_

**DESCRIPTION:** \_\_\_\_\_

**QUANTITY:** \_\_\_\_\_ pcs

|                            |  |  |
|----------------------------|--|--|
| <b>REMARK:</b>             |  |  |
|                            |  |  |
| Customer Approval Feedback |  |  |
|                            |  |  |

西北臺慶科技股份有限公司  
**TAI-TECH Advanced Electronics Co., Ltd**

西北臺慶科技股份有限公司  
 TAI-TECH Advanced Electronics Co., Ltd  
 Headquarter:  
 NO.1 YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI,  
 TAO-YUAN HSIEN, TAIWAN, R.O.C.  
 TEL: +886-3-4641148 FAX: +886-3-4643565  
 http://www.tai-tech.com.tw  
 E-mail: sales@tai-tech.com.tw

東莞臺慶精密電子有限公司  
 DONGGUAN TAI-TECH ADVANCED ELECTRONICS CO., LTD  
 JITIGANG MANAGEMENT DISTRICT, HUANGJIANG, DONGGUAN,  
 GUANGDONG, CHINA  
 TEL: +86-769-3365488 FAX: +86-769-3366896  
 E-mail: twnwe@pub.dgnet.gd.cn

Office:  
 金亨國際有限公司  
 KAMHENG INTERNATIONAL LIMITED  
 TEL: +86-852-25772033 FAX: +86-852-28817778

臺慶精密電子(昆山)有限公司  
 TAI-TECH ADVANCED ELECTRONICS(KUNSHAN) CO., LTD  
 SHINWHA ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN,  
 JIANG-SU, CHINA  
 TEL: +86-512-57619396 FAX: +86-512-57619688  
 E-mail: hui@tai-tech.com.tw

Office:  
 北欣國際有限公司  
 NORTH STAR INTERNATIONAL LIMITED  
 TEL: +86-512-57619396 FAX: +86-512-57619688

Sales Dep.

| APPROVED             | CHECKED              |
|----------------------|----------------------|
| 鄧永浩<br>Yong-hao Deng | 鄧永浩<br>Yong-hao Deng |

R&D Center

| APPROVED        | CHECKED          | DRAWN            |
|-----------------|------------------|------------------|
| 楊祥忠<br>MikeYang | 詹偉特<br>Jack Chan | 林宜瀟<br>Beryl Lin |



# Power Inductor


**AHP201610TF-SERIES**

## 1. Features

1. This specification applies Low Profile Power Inductor.
2. 100% Lead(Pb) & Halogen-Free and RoHS compliant.




## 2. Dimension



| Series      | A(mm)         | B(mm)         | C(mm)  | D(mm)     | E(mm)     |
|-------------|---------------|---------------|--------|-----------|-----------|
| AHP201610TF | 2.0 -0.1/+0.2 | 1.6 -0.1/+0.2 | 1.0Max | 0.60 ref. | 0.80 ref. |

Units: mm

## 3. Part Numbering



A: Series

B: Dimension

C: Lead Free

D: Inductance

E: Inductance Tolerance

Material

R24=0.24uH

M=±20%








## 4. Specification

| TAI-TECH Part Number | Inductance (uH) | Tolerance (%) | DCR (Ω) typ. | DCR (Ω) Max. | I sat (A) typ. | I sat (A) Max. | I rms (A) typ | I rms (A) MAX |
|----------------------|-----------------|---------------|--------------|--------------|----------------|----------------|---------------|---------------|
| AHP201610TF-R24M-1   | 0.24            | ±20           | 0.026        | 0.032        | 6.80           | 5.90           | 4.20          | 3.70          |
| AHP201610TF-R33M-1   | 0.33            | ±20           | 0.032        | 0.038        | 6.00           | 5.50           | 4.0           | 3.60          |
| AHP201610TF-R47M-1   | 0.47            | ±20           | 0.035        | 0.044        | 5.20           | 4.30           | 3.60          | 3.20          |
| AHP201610TF-R68M-1   | 0.68            | ±20           | 0.056        | 0.064        | 4.20           | 3.60           | 2.90          | 2.60          |
| AHP201610TF-1R0M-1   | 1.00            | ±20           | 0.070        | 0.085        | 3.10           | 2.70           | 2.45          | 2.20          |
| AHP201610TF-1R5M-1   | 1.50            | ±20           | 0.105        | 0.125        | 2.90           | 2.60           | 2.30          | 2.00          |
| AHP201610TF-2R2M-1   | 2.2             | ±20           | 0.140        | 0.170        | 2.20           | 1.90           | 1.85          | 1.65          |

Note:



1. Test frequency : L : 1MHz /1.0V

2. Isat : Based on inductance change ( $\Delta L/L0 : \leq -30\%$ ) @ ambient temp. 25°C3. Irms : Based on temperature rise ( $\Delta T : 40^\circ\text{C}$ .) Max



### 5. Material List

| No. | Description | Specification              |
|-----|-------------|----------------------------|
| a.  | Core        | Metal Magnetic Core        |
| b.  | Coating     | Epoxy with Magnetic powder |
| c.  | Termination | Tin (Pb Free)              |
| d.  | Wire        | Enameled Copper Wire       |



Appearance of exposed wire tolerance limit:

1. Width direction ( dimension a ) : Acceptable when  $a \leq w/2$   
Nonconforming when  $a > w/2$
2. Length direction ( dimension b ) : Dimension b is not specified.
3. The total area of exposed wire occurring to each sides is not greater than 50% of coating resin area, and is acceptable.

### 6. Reliability and Test Condition

| Item                                    | Performance   | Test Condition  |                  |  |  |                       |                           |            |                     |   |
|---|---|---|------------------|--|--|-----------------------|---------------------------|------------|---------------------|---|
| Operating Temperature                   | -40~+125°C  |   |                  |  |  |                       |                           |            |                     |   |
| Storage Temperature (on board)          |   |   |                  |  |  |                       |                           |            |                     |   |
| <b>Electrical Performance Test</b>      |   |   |                  |  |  |                       |                           |            |                     |   |
| Inductance L                            | Refer to standard electrical characteristic list  | Agilent-4291, Agilent-4287  |                  |  |  |                       |                           |            |                     |   |
| DC Resistance                           |   | Agilent-4338  |                  |  |  |                       |                           |            |                     |   |
| Rated Current                           | Base on temp. rise & $\Delta L/L0A \leq 30\%$ .   | Saturation DC Current (Isat) will cause L0 to drop approximately $\Delta L(\%)$ .   |                  |  |  |                       |                           |            |                     |   |
| Temperature Rise Test                   | $\Delta T$ 40°C Max   | Heat Rated Current (Irms) will cause the coil temperature rise approximately $\Delta T(°C)$ without core loss.<br>1. Applied the allowed DC current.<br>2. Temperature measured by digital surface thermometer  |                  |  |  |                       |                           |            |                     |   |
| <b>Mechanical Performance Test</b>      |   |   |                  |  |  |                       |                           |            |                     |   |
| Solder Heat Resistance                  | Appearance : No damage.<br>Inductance : within $\pm 10\%$ of initial value<br>RDC : within $\pm 15\%$ of initial value and shall not exceed the specification value | <table border="1"> <thead> <tr> <th>Temperature (°C)</th> <th>Time (s)</th> <th>Temperature ramp/immersion and emersion rate</th> <th>Number of heat cycles</th> </tr> </thead> <tbody> <tr> <td>260 <math>\pm</math>5 (solder temp)</td> <td>10 <math>\pm</math>1</td> <td>25mm/s <math>\pm</math>6 mm/s</td> <td>1</td> </tr> </tbody> </table> | Temperature (°C) | Time (s)                                     | Temperature ramp/immersion and emersion rate | Number of heat cycles | 260 $\pm$ 5 (solder temp) | 10 $\pm$ 1 | 25mm/s $\pm$ 6 mm/s | 1 |
|   |   | Temperature (°C)  | Time (s)         | Temperature ramp/immersion and emersion rate | Number of heat cycles                        |                       |                           |            |                     |   |
| 260 $\pm$ 5 (solder temp)               | 10 $\pm$ 1  | 25mm/s $\pm$ 6 mm/s   | 1                |  |  |                       |                           |            |                     |   |
| Depth: completely cover the termination |   |   |                  |  |  |                       |                           |            |                     |   |

| Item                     | Performance   | Test Condition  |
|--------------------------|---|---|
| Solderability Test       | More than 95% of terminal electrode should be covered with solder.              | Preheat: 150°C, 60sec. °<br>Solder: Sn99.5%-Cu0.5% °<br>Temperature: 245±5°C °<br>Flux for lead free: Rosin. 9.5% °<br>Dip time: 4±1sec °<br>Depth: completely cover the termination  |
| <b>Reliability Test</b>  |   |   |
| Life Test                |   | Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles)<br>Temperature : 85±2°C<br>Applied current : rated current<br>Duration : 1000±12hrs<br>Measured at room temperature after placing for 24±2 hrs  |
| Thermal shock            | Appearance : No damage.<br>Inductance : within±10% of initial value             | Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles)<br>Step1 : -40±2°C 30±5min<br>Step2 : 25±2°C ≤0.5min<br>Step3 : 105±2°C 30±5min<br>Number of cycles : 500<br>Measured at room temperature after placing for 24±2 hrs                            |
| Humidity Resistance Test | RDC : within ±15% of initial value and shall not exceed the specification value | Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles)<br>Humidity : 85±2% R.H,<br>Temperature : 85°C ±2°C<br>Duration : 1000hrs Min. with 100% rated current<br>Measured at room temperature after placing for 24±2 hrs                               |
| Vibration Test           |   | Preconditioning: Run through IR reflow for 2 times. (IPC/JEDEC J-STD-020D Classification Reflow Profiles)<br>Oscillation Frequency: 10~2K~10Hz for 20 minutes<br>Equipment : Vibration checker<br>Total Amplitude: 1.52mm±10%<br>Testing Time : 12 hours (20 minutes, 12 cycles each of 3 orientations) ° |

## 7. Soldering and Mounting

### 7-1. Soldering

Mildly activated rosin fluxes are preferred. TAI-TECH terminations are suitable for all wave and re-flow soldering systems. If hand soldering cannot be avoided, the preferred technique is the utilization of hot air soldering tools.

#### 7-1.1 Solder re-flow:

Recommended temperature profiles for re-flow soldering in Figure 1.

#### 7-1.2 Soldering Iron(Figure 2):

Products attachment with a soldering iron is discouraged due to the inherent process control limitations. In the event that a soldering iron must be employed the following precautions are recommended.

- Preheat circuit and products to 150°C
- Never contact the ceramic with the iron tip
- Use a 20 watt soldering iron with tip diameter of 1.0mm
- 355°C tip temperature (max)
- 1.0mm tip diameter (max)
- Limit soldering time to 4~5 sec.






Fig.1



Iron Soldering times: 1 times max.

Fig.2


### 7-2. Recommended PC Board Pattern



| L(mm) | G(mm) | H(mm) |
|-------|-------|-------|
| 2.3   | 0.7   | 1.7   |


## 8. Packaging Information

### 8-1. Reel Dimension



| Type   | A(mm)   | B(mm)   | C(mm)  | D(mm) |
|--------|---------|---------|--------|-------|
| 7"x8mm | 8.4±1.0 | 50 min. | 13±0.8 | 178±2 |

### 8-2. Tape Dimension / 8mm




| Series | Size   | Bo(mm)  | Ao(mm)  | Ko(mm)   | P(mm)   | t(mm)     |
|--------|--------|---------|---------|----------|---------|-----------|
| AHP    | 201610 | 2.5±0.1 | 2.0±0.1 | 1.40±0.1 | 4.0±0.1 | 0.23±0.05 |

### 8-3. Packaging Quantity

|             |        |
|-------------|--------|
| Chip size   | 201610 |
| Chip / Reel | 2000   |

### 8-4. Tearing Off Force



The force for tearing off cover tape is 15 to 80 grams in the arrow direction under the following conditions.

| Room Temp. (°C) | Room Humidity (%) | Room atm (hPa) | Tearing Speed mm/min |
|-----------------|-------------------|----------------|----------------------|
| 5~35            | 45~85             | 860~1060       | 300                  |

#### Application Notice

- Storage Conditions(component level)
  - To maintain the solderability of terminal electrodes:
    1. TAI-TECH products meet IPC/JEDEC J-STD-020D standard-MSL, level 1.
    2. Temperature and humidity conditions: Less than 40°C and 60% RH.
    3. Recommended products should be used within 12 months form the time of delivery.
    4. The packaging material should be kept where no chlorine or sulfur exists in the air.
- Transportation
  1. Products should be handled with care to avoid damage or contamination from perspiration and skin oils.
  2. The use of tweezers or vacuum pick up is strongly recommended for individual components.
  3. Bulk handling should ensure that abrasion and mechanical shock are minimized.