Is Now Part of

ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at
www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

February 2015

FDMC6686P

P-Channel PowerTrench® MOSFET

-20 V, -56 A, 4 mΩ

Features

- Max $r_{DS(on)}$ = 4 mΩ at V_{GS} = -4.5 V, I_D = -18 A
- Max $r_{DS(on)}$ = 5.7 mΩ at V_{GS} = -2.5 V, I_D = -16 A
- Max $r_{DS(on)}$ =11.5 mΩ at V_{GS} = -1.8 V, I_D = -11 A
- High performance trench technology for extremely low $r_{DS(on)}$
- High power and current handling capability in a widely used surface mount package
- Lead-free and RoHS Compliant

General Description

This P-Channel MOSFET is produced using Fairchild Semiconductor's advanced PowerTrench® process that has been optimized for $r_{DS(ON)}$, switching performance and ruggedness.

Applications

- Load Switch
- Battery Management
- Power Management
- Reverse Polarity Protection



Top



Bottom



Power 33

MOSFET Maximum Ratings T_A = 25 °C unless otherwise noted

Symbol	Parameter			Ratings	Units
V_{DS}	Drain to Source Voltage			-20	V
V_{GS}	Gate to Source Voltage			±8	V
I_D	Drain Current -Continuous	T_C = 25 °C		-56	A
	-Continuous	T_A = 25 °C	(Note 1a)	-18	
	-Pulsed		(Note 3)	-377	
P_D	Power Dissipation	T_C = 25 °C		40	W
	Power Dissipation	T_A = 25 °C	(Note 1a)	2.3	
T_J, T_{STG}	Operating and Storage Junction Temperature Range			-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case		3.1	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	(Note 1a)	53	

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMC6686P	FDMC6686P	Power 33	13 "	12 mm	3000 units

Electrical Characteristics T_J = 25 °C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain to Source Breakdown Voltage	I_D = -250 μA, V_{GS} = 0 V	-20			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I_D = -250 μA, referenced to 25 °C		-15		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS} = -16 V, V_{GS} = 0 V			-1	μA
I_{GSS}	Gate to Source Leakage Current	V_{GS} = ±8 V, V_{DS} = 0 V			±100	nA
On Characteristics						
$V_{GS(th)}$	Gate to Source Threshold Voltage	V_{GS} = V_{DS}, I_D = -250 μA	-0.4	-0.75	-1	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = -250 μA, referenced to 25 °C		3		mV/°C
$r_{DS(on)}$	Static Drain to Source On Resistance	V_{GS} = -4.5 V, I_D = -18 A		3.3	4	mΩ
		V_{GS} = -2.5 V, I_D = -16 A		4.1	5.7	
		V_{GS} = -1.8 V, I_D = -11 A		6	11.5	
		V_{GS} = -4.5 V, I_D = -18 A, T_J = 125 °C		4.3	6.5	
g_{FS}	Forward Transconductance	V_{DS} = -5 V, I_D = -18 A		116		S
Dynamic Characteristics						
C_{iss}	Input Capacitance	V_{DS} = -10 V, V_{GS} = 0 V, f = 1 MHz		8800	13200	pF
C_{oss}	Output Capacitance			1520	2280	pF
C_{rss}	Reverse Transfer Capacitance			1340	2010	pF
R_g	Gate Resistance			6.2		Ω
Switching Characteristics						
$t_{d(on)}$	Turn-On Delay Time	V_{DD} = -10 V, I_D = -18 A, V_{GS} = -4.5 V, R_{GEN} = 6 Ω		25	40	ns
t_r	Rise Time			77	122	ns
$t_{d(off)}$	Turn-Off Delay Time			317	506	ns
t_f	Fall Time			178	285	ns
Q_g	Total Gate Charge	V_{DD} = -10 V, I_D = -18 A, V_{GS} = -4.5 V		87	122	nC
Q_{gs}	Gate to Source Charge			14		nC
Q_{gd}	Gate to Drain “Miller” Charge			24		nC
Drain-Source Diode Characteristics						
V_{SD}	Source to Drain Diode Forward Voltage	V_{GS} = 0 V, I_S = -18 A (Note 2)		-0.7	-1.2	V
		V_{GS} = 0 V, I_S = -2 A (Note 2)		-0.6	-1.2	
t_{rr}	Reverse Recovery Time	I_F = -18 A, di/dt = 100 A/μs		38	61	ns
Q_{rr}	Reverse Recovery Charge			24	39	nC

NOTES:

1. $R_{\theta JA}$ is determined with the device mounted on a 1 in^2 pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. $R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



a. 53 °C/W when mounted on a 1 in^2 pad of 2 oz copper.



b. 125 °C/W when mounted on a minimum pad of 2 oz copper.

2. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.
3. Pulse Id refers to Forward Bias Safe Operation Area.

Typical Characteristics T_J = 25 °C unless otherwise noted



Figure 1. On-Region Characteristics



Figure 2. Normalized On-Resistance vs Drain Current and Gate Voltage



Figure 3. Normalized On-Resistance vs Junction Temperature



Figure 4. On-Resistance vs Gate to Source Voltage



Figure 5. Transfer Characteristics



Figure 6. Source to Drain Diode Forward Voltage vs Source Current

Typical Characteristics T_J = 25 °C unless otherwise noted



Figure 7. Gate Charge Characteristics



Figure 8. Capacitance vs Drain to Source Voltage



Figure 9. Maximum Continuous Drain Current vs Case Temperature



Figure 10. Forward Bias Safe Operating Area



Figure 11. Single Pulse Maximum Power Dissipation

Typical Characteristics T_J = 25 °C unless otherwise noted



Figure 12. Junction-to-Case Transient Thermal Response Curve







LAND PATTERN
RECOMMENDATION





DETAIL A
SCALE: 2X

NOTES: UNLESS OTHERWISE SPECIFIED

A) PACKAGE STANDARD REFERENCE: JEDEC MO-240, ISSUE A, VAR. BA,
B) ALL DIMENSIONS ARE IN MILLIMETERS.
C) DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH. MOLD FLASH OR BURRS DOES NOT EXCEED 0.10MM.
D) DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.
E) DRAWING FILE NAME: MKT-PQFN08SREV1

FAIRCHILD™

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative