




FEATURES:


- ✧ 300 Watts peak pulse power per line ($t_P=8/20\mu s$)
- ✧ Protects four I/O lines
- ✧ Low clamping voltage
- ✧ Low operating voltage
- ✧ Low capacitance: 1.6pF typical
- ✧ ROHS compliant



SOT23-6L

MAIN APPLICATIONS

- ✧ USB power and data line protection
- ✧ Digital video interface (DVI)
- ✧ Notebook computers
- ✧ Video graphics cards
- ✧ Monitors and flat panel displays
- ✧ 10/100/1000 ethernet
- ✧ SIM ports
- ✧ ATM interfaces




PROTECTION SOLUTION TO MEET

- ✧ IEC61000-4-2 (ESD) $\pm 30kV$ (air), $\pm 30kV$ (contact)
- ✧ IEC61000-4-4 (EFT) 40A (5/50ns)
- ✧ IEC61000-4-5 (Lightning) 15A (8/20 μs)

MECHANICAL CHARACTERISTICS

- ✧ JEDEC SOT23-6L package
- ✧ Molding compound flammability rating : UL 94V-0
- ✧ Quantity per reel : 3, 000pcs
- ✧ Lead finish : lead free
- ✧ Marking code: 5UB

PIN Configuration



Circuit Diagram

ABSOLUTE MAXIMUM RATINGS ($T_A=25^\circ\text{C}$, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak pulse power dissipation on 8/20 μs waveform	P_{PP}	300	W
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V_{ESD}	+/- 30 +/- 30	kV
Lead soldering temperature	T_L	260 (10 sec.)	$^\circ\text{C}$
Operating junction temperature range	T_J	-55 to +125	$^\circ\text{C}$
Storage temperature range	T_{STG}	-55 to +150	$^\circ\text{C}$

ELECTRICAL CHARACTERISTICS ($T_A=25^\circ\text{C}$)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse working voltage	V_{RWM}				5.0	V
Reverse breakdown voltage	V_{BR}	$I_T = 1\text{mA}$	6.0			V
Reverse leakage current	I_R	$V_{RWM} = 5\text{V}$ pin5 to pin2			5	μA
Forward voltage	V_F	$I_T=10\text{mA}$		1.2		V
Clamping voltage (I/O pin to Ground)	V_C	$I_{PP} = 15\text{A}$, $t_p = 8/20\mu\text{s}$		22	24.8	V
Junction capacitance	C_J	$V_{RWM} = 0\text{V}$, $f = 1\text{MHz}$ Any I/O pin to Ground		3		pF
		$V_{RWM} = 0\text{V}$, $f = 1\text{MHz}$ Between I/O pins		1.6		



RATINGS AND V-I CHARACTERISTICS CURVES ($T_A=25^\circ\text{C}$, unless otherwise noted)**FIG.1:V- I curve characteristics
(Uni-directional)****FIG.2: Pulse waveform (8/20μs)**

FIG.3: Pulse derating curve






FIG.4: ESD clamping (8KV contact)



PACKAGE MECHANICAL DATA



Symbol	Millimeter		Inches	
	Min	Max	Min	Max
A	0.90	1.45	0.035	0.057
A1	0.00	0.15	0.000	0.006
A2	0.45	0.65	0.017	0.026
B	0.35	0.50	0.010	0.020
C	0.08	0.20	0.003	0.007
D	2.80	3.00	0.110	0.122
e	0.69	1.02	0.032	0.043
E1	1.50	1.75	0.060	0.069
E	2.80BSC		0.110BSC	
L1	0.35	0.60	0.013	0.024
L	0.60		0.024	
X	0.60		0.024	
Y	1.10		0.043	
P	3.60		0.141	
P1	1.40		0.055	
P2	2.50		0.098	
P3	0.95		0.037	

Information furnished in this document is believed to be accurate and reliable. However, Jiangsu JieJie Microelectronics Co.,Ltd assumes no responsibility for the consequences of use without consideration for such information nor use beyond it.

Information mentioned in this document is subject to change without notice, apart from that when an agreement is signed, Jiangsu JieJie complies with the agreement.

Products and information provided in this document have no infringement of patents. Jiangsu JieJie assumes no responsibility for any infringement of other rights of third parties which may result from the use of such products and information.

This document is the second version which is made in 15-Apr.-2017. This document supersedes and replaces all information previously supplied.



is a registered trademark of Jiangsu JieJie Microelectronics Co.,Ltd.

Copyright ©2017 Jiangsu JieJie Microelectronics Co.,Ltd. Printed All rights reserved.