



Ordering Information & Specifications

Part No.	Wire Range	Insulation O.D.	Material	Finish	Qty/Reel
A1254-GPE	AWG#28-#32	0.90mm(max)	Phosphor Bronze	Gold-flash	10,000pcs
A1254-GPE-G4	AWG#28-#32	0.90mm(max)	Phosphor Bronze	Gold-plated 5u"	10,000pcs
A1254-GPE-G5	AWG#28-#32	0.90mm(max)	Phosphor Bronze	Gold-plated 3u"	10,000pcs
A1254-TPE	AWG#28-#32	0.90mm(max)	Phosphor Bronze	Tin-plated	10,000pcs
A1254-TPE-01	AWG#28-#32	0.90mm(max)	Phosphor Bronze	Tin-plated	10,000pcs

Note: Stamping before Tin-plated or Gold-plated

REV.	DESCRIPTION	DATE	NAME
C3	EN1612070001	2016.12.06	賴永強
C2	EN1609200001	2016.09.10	任運宏
C1	EN1406270001	2014.07.01	唐勝風
C0	EN1104130096	2011.07.15	陳敏
B5	EN1009270244	2010.09.24	陳錦展

燦達電子工業股份有限公司
 JOINT TECH ELECTRONIC IND. CO., LTD.

TITLE:
 1.25mm PITCH
 CRIMP TERMINAL

DRAW NO.:
 A1254-XX
 REV. C3