


10A 250V AC Qualified Type SDDJE Series

Туре		Rocker	
Circuit arrangement		SPST	
Travel		3.4mm	
Operating force		3±2N	
Mounting method		Snap-in	
Terminal type		For Lead	
Frame		Without	
Marking (knob)		I, O mark	
C-UL-US		10AGP 250V AC	
SEMKO			6A/96A 250V~, 10(6)/250~
VDE			6A/96A 250V~, 10(6)/250~
BS			6A/96A 250V~, 10(6)/250~
Ratings satisfying law	local electrical applianc	e and material safety	125V 10A ‡
Operating temperature range		-10℃ to +55℃	
Rating			10AGP 250V AC, 6A/96A 250V~
Electrical performance	Contact resistance		100mΩ max.
performance	Insulation resistance		500MΩ min. 500V DC
	Voltage proof		2,000V AC for 1 minute
Mechanical performance	Terminal strength		50N for 1 minute (lead terminal) 5N for 1 minute (right-angle terminal)
	Actuator strength	Operating direction	25N
		Perpendicular direction	25N
Durability	Operating life		10,000 cycles 10A 250V AC

SDDJE Series - Basic information


Environmental performance	Cold		-20℃ 96h
	Dry heat		85℃ 96h
	Damp heat		40℃, 90 to 95%RH 96h
Minimum order unit (pcs.)		Japan	400
		Export	2,000


Dimensions



Mounting Hole Reference Size

Square-shaped Hole		Unit:mm	
Thickness of mounting board	Y1	z	
0.75 to 1.25	19.2 [°] -0.1	12.9 ^{+0.1}	
1.25 to 2.00	19.4 [°] -0.1	12.30	







U-shaped Hole		Unit:mm
Thickness of mounting board	Y2	z
0.75 to 1.1	19.5 [°] -0.1	
1.1 to 1.7	19.7 [°] –0.1	12.9 ^{+0.1}
1.7 to 2	19.9° _{-0.1}	

Verify the performance under actual product conditions before use.

Circuit Diagram



Marking (knob)



Packing Specifications

Tray

Number of packages 1 case / Japan (pcs.)	400
1 case / export packing	2,000
Export package measurements (mm)	411×328×379

Soldering Conditions

Reference for Hand Soldering

Soldering temperature	350±10℃
Soldering time	3+1/0s

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. The lead terminals are also used as tab terminals (#187). (Use a positive lock connector type.)
- 3. The lead terminal type can be mounted onto a board. (Manual soldering required.)
- 4. Standard products apply Grade V-2 material (Flame Class). For Grade V-0 type please contact us.
- 5. Please place purchase orders per minimum order unit (integer).
- 6. Products other than those listed in the above chart are also available. Please contact us for details.