


N-Channel Enhancement Mode MOSFET

Feature Description

- 30V/62A
- $R_{DS(ON)} = 4.5\text{m}\Omega(\text{typ.})$ @ $V_{GS} = 10\text{V}$
- $R_{DS(ON)} = 6.0\text{m}\Omega(\text{typ.})$ @ $V_{GS} = 4.5\text{V}$
- 100% Avalanche Tested
- Reliable and Rugged
- Halogen Free and Green Devices Available
(RoHS Compliant)




Pin Description

TO-252-2L TO-251-3L TO-251-3S

Applications

- Switching Application
- Power Management for DC/DC
- Battery Protection



N-Channel MOSFET

Ordering and Marking Information

 D HY1603 YYXXXJWW G	 U HY1603 YYXXXJWW G	 V HY1603 YYXXXJWW G	Package Code D: TO-252-2L U: TO-251-3L V: TO-251-3S
Date Code YYYY WW	Assembly Material G: Halogen Free		

Note: HUAYI lead-free products contain molding compounds/die attach materials and 100% matte tin plate Termination finish; which are fully compliant with RoHS. HUAYI lead-free products meet or exceed the lead-Free requirements of IPC/JEDEC J-STD-020 for MSL classification at lead-free peak reflow temperature. HUAYI defines "Green" to mean lead-free (RoHS compliant) and halogen free (Br or Cl does not exceed 900ppm by weight in homogeneous material and total of Br and Cl does not exceed 1500ppm by weight).

HUAYI reserves the right to make changes, corrections, enhancements, modifications, and improvements to this product and/or to this document at any time without notice.

HY1603D/U/V

Absolute Maximum Ratings

Symbol	Parameter	Rating	Unit	
Common Ratings (T_c=25°C Unless Otherwise Noted)				
V _{DSS}	Drain-Source Voltage	30	V	
V _{GSS}	Gate-Source Voltage	±20	V	
T _J	Maximum Junction Temperature	150	°C	
T _{STG}	Storage Temperature Range	-55 to 150	°C	
I _S	Source Current-Continuous(Body Diode)	T _c =25°C	62	A
Mounted on Large Heat Sink				
I _{DM}	Pulsed Drain Current *	T _c =25°C	248	A
I _D	Continuous Drain Current	T _c =25°C	62	A
		T _c =100°C	39	A
P _D	Maximum Power Dissipation	T _c =25°C	36	W
		T _c =100°C	14.3	W
R _{θJC}	Thermal Resistance, Junction-to-Case	3.5	°C/W	
R _{θJA}	Thermal Resistance, Junction-to-Ambient **	110	°C/W	
E _{AS}	Single Pulsed-Avalanche Energy ***	L=0.3mH	132	mJ

Note: * Repetitive rating; pulse width limited by max. junction temperature.

** Surface mounted on FR-4 board.

*** Limited by T_{jmax}, starting T_j=25°C, L = 0.3mH, R_G= 25Ω, V_{GS}=10V.

Electrical Characteristics (T_c =25°C Unless Otherwise Noted)

Symbol	Parameter	Test Conditions	HY1603			Unit
			Min	Typ.	Max	
Static Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _{DS} =250μA	30	-	-	V
I _{DSS}	Drain-to-Source Leakage Current	V _{DS} =20V, V _{GS} =0V	-	-	1	μA
		T _J =55°C	-	-	30	μA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _{DS} =250μA	1	1.4	2	V
I _{GSS}	Gate-Source Leakage Current	V _{GS} =±20V, V _{DS} =0V	-	-	±100	nA
R _{DSD(ON)*}	Drain-Source On-State Resistance	V _{GS} =10V, I _{DS} =31A	-	4.5	5.5	mΩ
		V _{GS} =4.5V, I _{DS} =31A	-	6.0	8.0	
Diode Characteristics						
V _{SD*}	Diode Forward Voltage	I _{SD} =31A, V _{GS} =0V	-	0.8	1.1	V
t _{rr}	Reverse Recovery Time	I _{SD} =31A, dI _{SD} /dt=100A/μs	-	21	-	ns
Q _{rr}	Reverse Recovery Charge		-	13	-	nC

Electrical Characteristics (Cont.) ($T_c = 25^\circ\text{C}$ Unless Otherwise Noted)

Symbol	Parameter	Test Conditions	HY1603			Unit
			Min	Typ.	Max	
Dynamic Characteristics						
R_G	Gate Resistance	$V_{GS}=0V, V_{DS}=0V$, Frequency=1.0MHz	-	1.4	-	Ω
C_{iss}	Input Capacitance	$V_{GS}=0V$, $V_{DS}=25V$, Frequency=1.0MHz	-	2082	-	pF
C_{oss}	Output Capacitance		-	140	-	
C_{rss}	Reverse Transfer Capacitance		-	78	-	
$t_{d(ON)}$	Turn-on Delay Time	$V_{DD}=25V, R_G=3.3\Omega$, $I_{DS}=31A, V_{GS}=10V$	-	15	-	ns
T_r	Turn-on Rise Time		-	13	-	
$t_{d(OFF)}$	Turn-off Delay Time		-	39	-	
T_f	Turn-off Fall Time		-	10	-	
Gate Charge Characteristics						
Q_g	Total Gate Charge	$V_{DS}=24V, V_{GS}=10V$, $I_D=31A$	-	52.8	-	nC
Q_{gs}	Gate-Source Charge		-	4.4	-	
Q_{gd}	Gate-Drain Charge		-	10.3	-	

Note: *Pulse test, pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$

Typical Operating Characteristics

Figure 1: Power Dissipation




Figure 2: Drain Current




Figure 3: Safe Operation Area




Figure 4: Thermal Transient Impedance




Figure 5: Output Characteristics





Figure 6: Drain-Source On Resistance



Typical Operating Characteristics(Cont.)

Figure 7: On-Resistance vs. Temperature




Figure 8: Source-Drain Diode Forward




Figure 9: Capacitance Characteristics









Figure 10: Gate Charge Characteristics





Avalanche Test Circuit



Switching Time Test Circuit



Gate Charge Test Circuit




Device Per Unit

Package Type	Unit	Quantity
TO-252-2L	Tube	75
TO-252-2L	Reel	2500
TO-251-3L	Tube	75
TO-251-3S	Tube	75

Package Information


TO-252-2L



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.40
A1	0.00	-	0.20
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.50
c	0.43	0.53	0.63
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.80
E1	4.63	-	-
e	2.286BSC		
H	9.40	10.10	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L2	0.51BSC		
L3	0.88	-	1.28
L4	-	-	1.00
L5	1.65	1.80	1.95
θ	0°	-	8°


TO-251-3L



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.40
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b2	0.00	0.04	0.10
b2'	0.00	0.04	0.10
b3	5.20	5.33	5.50
c	0.43	0.53	0.63
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.80
E1	4.63	-	-
e	2.286BSC		
H	16.22	16.52	16.82
L1	9.15	9.40	9.65
L3	0.88	1.02	1.28
L5	1.65	1.80	1.95


TO-251-3S



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.40
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.50
c	0.43	0.53	0.63
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.80
E1	4.63	-	-
e	2.286BSC		
H	10.00	11.22	11.44
L1	3.90	4.10	4.30
L3	0.88	1.02	1.28
L5	1.65	1.80	1.95

Classification Profile



Classification Reflow Profiles

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T_{smin})	100 °C	150 °C
Temperature max (T_{smax})	150 °C	200 °C
Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T_{smax} to T_p)	3 °C/second max.	3°C/second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time at liquidous (t_L)	60-150 seconds	60-150 seconds
Peak package body Temperature (T_p)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t_p)** within 5°C of the specified classification temperature (T_c)	20** seconds	30** seconds
Average ramp-down rate (T_p to T_{smax})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.

*Tolerance for peak profile Temperature (T_p) is defined as a supplier minimum and a user maximum.
 ** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Table 1.SnPb Eutectic Process – Classification Temperatures (Tc)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2.Pb-free Process – Classification Temperatures (Tc)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ ≥2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

Reliability Test Program

Test item	Method	Description
SOLDERABILITY	JESD-22, B102	5 Sec, 245°C
HOLT	JESD-22, A108	168 Hrs /500 Hrs /1000 Hrs, Bias @ 150°C
PCT	JESD-22, A102	96 Hrs, 100%RH, 2atm, 121°C
TCT	JESD-22, A104	500 Cycles, -55°C~150°C

Customer Service

Worldwide Sales and Service: sales@hymexa.com

Technical Support: Technology@hymexa.com

Huayi Microelectronics Co., Ltd.

No.8928,Shangji Road,Economic and Technological Development Zone,Xi'an,China

TEL: (86-029) 86685706

FAX: (86-029) 86685705

E-mail: sales@hymexa.com

Web net: www.hymexa.com