


Description

LPN1010C use advanced FSMOS™ technology to provide low $R_{DS(on)}$, low gate charge, fast switching and excellent avalanche characteristics. This device is specially designed to get better ruggedness and suitable to use in Synchronous-rectification applications.

| | |
|--------------------------------|--------------|
| ◆ $V_{DS,min}$ | 100V |
| ◆ $I_{D,pulse}$ | 210A |
| ◆ $R_{DS(ON),max}@V_{GS}=10V$ | 10m Ω |
| ◆ $R_{DS(ON),max}@V_{GS}=4.5V$ | 14m Ω |
| ◆ Q_g | 72nC |

Schematic and Package Information



Schematic Diagram

Pin Assignment Top View

Ordering Information

| Package | Units/Tube | Tubes/Inner Box | Units/Inner Box | Inner Box/Carton Box | Units/Carton Box |
|---------|------------|-----------------|-----------------|----------------------|------------------|
| TO220 | 50 | 20 | 1000 | 6 | 6000 |

Product Information

| Product | Package | Pb Free | RoHS | Halogen Free |
|----------|---------|---------|------|--------------|
| LPN1010C | TO220 | yes | yes | yes |

Absolute Maximum Rating at $T_j=25^\circ\text{C}$ unless otherwise noted

| Parameter | Symbol | Value | Unit |
|--|----------------|------------|------------------|
| Drain source voltage | V_{DS} | 100 | V |
| Gate source voltage | V_{GS} | ± 20 | V |
| Continuous drain current ¹⁾ | I_D | 70 | A |
| Pulsed drain current ²⁾ | $I_{D,pulse}$ | 210 | A |
| Power dissipation ³⁾ | P_D | 330 | W |
| Single pulsed avalanche energy ⁵⁾ | E_{AS} | 100 | mJ |
| Operation and storage temperature | T_{stg}, T_j | -55 to 150 | $^\circ\text{C}$ |

Thermal Characteristics

| Parameter | Symbol | Value | Unit |
|--|-----------------|-------|---------------------------|
| Thermal resistance, junction-case | $R_{\theta JC}$ | 0.38 | $^\circ\text{C}/\text{W}$ |
| Thermal resistance, junction-ambient ⁴⁾ | $R_{\theta JA}$ | 62.5 | $^\circ\text{C}/\text{W}$ |

Electrical Characteristics at $T_j=25^\circ\text{C}$ unless otherwise specified

| Parameter | Symbol | Min. | Typ. | Max. | Unit | Test condition |
|----------------------------------|---------------------|------|------|------|------------------|--|
| Drain-source breakdown voltage | BV_{DSS} | 100 | | | V | $V_{GS}=0\text{V}, I_D=250\mu\text{A}$ |
| Gate threshold voltage | $V_{GS(\text{th})}$ | 1.0 | | 2.5 | V | $V_{DS}=V_{GS}, I_D=250\mu\text{A}$ |
| Drain-source on-state resistance | $R_{DS(\text{ON})}$ | | | 10.0 | $\text{m}\Omega$ | $V_{GS}=10\text{V}, I_D=10\text{A}$ |
| Drain-source on-state resistance | $R_{DS(\text{ON})}$ | | | 14.0 | $\text{m}\Omega$ | $V_{GS}=4.5\text{V}, I_D=10\text{A}$ |
| Gate-source leakage current | I_{GSS} | | | 100 | nA | $V_{GS}=20\text{V}$ |
| | | | | -100 | | $V_{GS}=-20\text{V}$ |
| Drain-source leakage current | I_{DS} | | | 1 | μA | $V_{DS}=100\text{V}, V_{GS}=0\text{V}$ |

Dynamic Characteristics

| Parameter | Symbol | Min. | Typ. | Max. | Unit | Test condition |
|------------------------------|--------------|------|--------|------|------|--|
| Input capacitance | C_{iss} | | 3888.5 | | pF | $V_{GS}=0\text{V}, V_{DS}=100\text{V}, f=1\text{MHz}$ |
| Output capacitance | C_{oss} | | 273.7 | | pF | |
| Reverse transfer capacitance | C_{rss} | | 5 | | pF | |
| Turn-on delay time | $T_{d(on)}$ | | 49.6 | | nS | $V_{GS}=10\text{V}, V_{DS}=50\text{V}, R_G=25\Omega, I_D=12\text{A}$ |
| Rise time | t_r | | 52.5 | | nS | |
| Turn-off delay time | $T_{d(off)}$ | | 390 | | nS | |
| Fall time | t_f | | 55.2 | | nS | |

Gate Charge Characteristics

| Parameter | Symbol | Min. | Typ. | Max. | Unit | Test condition |
|----------------------|---------------|------|------|------|------|--|
| Total gate charge | Q_g | | 72 | | nC | $I_D=12\text{A}, V_{DS}=50\text{V}, V_{GS}=10\text{V}$ |
| Gate-source charge | Q_{gs} | | 8.9 | | nC | |
| Gate-drain charge | Q_{gd} | | 18.8 | | nC | |
| Gate plateau voltage | $V_{plateau}$ | | 3.2 | | V | |

Body Diode Characteristics

| Parameter | Symbol | Min. | Typ. | Max. | Unit | Test condition |
|-------------------------------|------------------|------|------|------|------|--|
| Diode forward current | I _S | | | 70 | A | V _{GS} <V _{th} |
| Pulsed source current | I _{SP} | | | 210 | A | |
| Diode forward voltage | V _{SD} | | | 1.3 | V | I _S =20A, V _{GS} =0V |
| Reverse recovery time | t _{rr} | | 66.8 | | nS | I _S =12A, di/dt=100A/uS |
| Reverse recovery charge | Q _{rr} | | 139 | | nC | |
| Peak reverse recovery current | I _{rrm} | | 3.5 | | A | |

Note

- 1) Calculated continuous current based on maximum allowable junction temperature.
- 2) Repetitive rating; pulse width limited by max. junction temperature.
- 3) Pd is based on max. junction temperature, using junction-case thermal resistance.
- 4) The value of R_{θJA} is measured with the device mounted on 1 in 2 FR-4 board with 2oz. Copper, in a still air environment with T_a=25°C.
- 5) V_{DD}=50V, R_G=25 Ω, L=0.3mH, starting T_j=25°C



深圳市芯茂微电子有限公司

LANDP SHENZHEN CHIP HOPE MICRO-ELECTRONICS LTD

LPN1010C

Enhancement Mode N-Channel Power MOSFET

Electrical Characteristics Diagrams




Figure 1, Typ. Output characteristics

Figure 2, Typ. Transfer characteristics




Figure 3, Typ. capacitances

Figure 4, Typ. gate charge




Figure 5, Drain-source breakdown voltage

Figure 6, Drain-source on-state resistance



深圳市芯茂微电子有限公司

LANDP SHENZHEN CHIP HOPE MICRO-ELECTRONICS LTD

LPN1010C

Enhancement Mode N-Channel Power MOSFET




Figure 7, Forward characteristics of body diode




Figure 8, Drain-source on-state resistance




Figure 9, Safe operation area $T_C=25^{\circ}\text{C}$



深圳市芯茂微电子有限公司

LANDP SHENZHEN CHIP HOPE MICRO-ELECTRONICS LTD

LPN1010C

Enhancement Mode N-Channel Power MOSFET

Test circuits and waveforms




Figure 1, Gate charge test circuit &waveform




Figure 2, Switching time test circuit & waveforms




Figure 3, Unclamped inductive switching (UIS) test circuit & waveforms




Figure 4, Diode reverse recovery test circuit & waveforms




深圳市芯茂微电子有限公司

LANDP SHENZHEN CHIP HOPE MICRO-ELECTRONICS LTD

LPN1010C

Enhancement Mode N-Channel Power MOSFET

Package Information



| Symbol | Min | Nom | Max |
|--------|----------|-------|-------|
| A | 4.37 | 4.57 | 4.77 |
| A1 | 1.25 | 1.30 | 1.45 |
| A2 | 2.20 | 2.40 | 2.60 |
| b | 0.70 | 0.80 | 0.95 |
| b2 | 1.17 | 1.27 | 1.47 |
| c | 0.40 | 0.50 | 0.65 |
| D | 15.10 | 15.60 | 16.10 |
| D1 | 8.80 | 9.10 | 9.40 |
| D2 | 5.50 | - | - |
| E | 9.70 | 10.00 | 10.30 |
| E3 | 7.00 | - | - |
| e | 2.54 BSC | | |
| e1 | 5.08 BSC | | |
| H1 | 6.25 | 6.50 | 6.85 |
| L | 12.75 | 13.50 | 13.80 |
| L1 | - | 3.10 | 3.40 |
| ΦP | 3.40 | 3.60 | 3.80 |
| Q | 2.60 | 2.80 | 3.00 |