
# EVERLIGHT

# DATASHEET

# SMD • B 11-22/R6BHC-A31/2T



# Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Multi-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

# Description

- The 11-22 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

# Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

# **Device Selection Guide**

Code	Chip Materials	Emitted Color	Resin Color
R6	AlGaInP	Brilliant Red	Water Clear
ВН	InGan	Blue	<ul> <li>Water Clear</li> </ul>

# Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Code	Rating	Unit
Reverse Voltage	V <sub>R</sub>		5	V
E		R6	25	
Forward Current	I <sub>F</sub>	ВН	20	— mA
Peak Forward Current		R6	60	
(Duty 1/10 @1KHz)	I <sub>FP</sub>	ВН	100	— mA
E		R6	60	
Power Dissipation	Pd	BH	75	— mW
Electrostatic Discharge	ESD <sub>HBM</sub>	R6	2000	V
		BH	150	
Operating Temperature	T <sub>opr</sub>		-40 ~ +85	°C
Storage Temperature	Tstg		-40 ~ +90	°C
Soldering Temperature	Tsol		Reflow Soldering : 26 Hand Soldering : 350	

# Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Code	Min.	Тур.	Max.	Unit	Condition
		R6	140		360	– mcd	
Luminous Intensity	lv	ВН	225		360	mea	_
Viewing Angle	<b>2θ</b> <sub>1/2</sub>			60		deg	_
Deck Weyder sth	λp	R6		632		- nm	_
Peak Wavelength	Χр	ВН		468			
Dominant	λd	R6	621.0		631.0	– nm	IF=20mA
Wavelength	Λŭ	ВН	464.5		474.5	1111	
Spectrum Radiation	Δλ	R6		20		– nm	
Bandwidth		ВН		25			
Forward Valtage	V	R6	1.7	2.0	2.4	- V	
Forward Voltage	V <sub>F</sub>	ВН	2.7	3.3	3.7	v	
	1-	R6			10	– μΑ	V <sub>R</sub> =5V
Reverse Current	I <sub>R</sub>	BH			50	μν	v R <b>-</b> J V

Note:

1.Tolerance of Luminous Intensity: ±11%

2. Tolerance of Dominant Wavelength ±1nm

# Bin Range of Luminous Intensity R6


R6				
Bin Code	Min.	Max.	Unit	Condition
R2	140	180		
S1	180	225		I <sub>F</sub> =20mA
S2	225	285	mcd	
T1	285	360		
вн				
Bin Code	Min.	Max.	Unit	Condition
<u></u>	225	285		
S2	225			
T1	285	360	mcd	I <sub>F</sub> =20mA
T1		360	mcd	I <sub>F</sub> =20mA
⊤1 Bin Range Of R6	285	360	mcd	I <sub>F</sub> =20mA Condition
⊤1 Bin Range Of R6	285 Dom. Wavelengt	360 h	Unit	Condition
T1 <b>Bin Range Of</b> <b>R6</b> Bin Code	285 Dom. Wavelengti Min.	360 h Max.		
T1 Bin Range Of R6 Bin Code FF1 FF2	285 Dom. Wavelengt Min. 621	360 h Max. 626	Unit	Condition
T1 Bin Range Of R6 Bin Code FF1 FF2 BH	285 Dom. Wavelengt Min. 621	360 h Max. 626	Unit	Condition
T1 Bin Range Of R6 Bin Code FF1 FF2 BH	285 Dom. Wavelengt Min. 621 626	360 h Max. 626 631	Unit	Condition I <sub>F</sub> =20mA
T1 Bin Range Of R6 Bin Code FF1 FF2 BH Bin Code A9	285 Dom. Wavelengt Min. 621 626 Min.	360 h Max. 626 631 Max.	Unit Unit Unit	Condition I <sub>F</sub> =20mA Condition
T1 Bin Range Of R6 Bin Code FF1 FF2 BH Bin Code	285 Dom. Wavelengt Min. 621 626 Min. 464.5	360 h Max. 626 631 Max. 467.5	Unit	Condition I <sub>F</sub> =20mA

Note:


1.Tolerance of Luminous Intensity: ±11%


2. Tolerance of Dominant Wavelength ±1nm

# Typical Electro-Optical Characteristics Curves R6




# Typical Electro-Optical Characteristics Curves BH








# **Package Dimension**




Note: Tolerances unless mentioned ±0.1mm. Unit = mm

# Moisture Resistant Packing Materials Label Explanation



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number


# **Reel Dimensions**



Note: The tolerances unless mentioned is  $\pm 0.1$  mm ,Unit = mm



# Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel





### **Precautions For Use**

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big

current change ( Burn out will happen ).

2. Storage

2.1 Do not open moisture proof bag before the products are ready to use.

2.2 After opening the package: The LEDs should be kept at  $30^{\circ}$ C or less and 60%RH or less.


2.3 The LEDs should be used within 168 hours (7days) after opening the package .

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment :  $60\pm5^{\circ}$ C for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile




3.4 After soldering, do not warp the circuit board.

### 4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $350^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

### 5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





# **Application Restrictions**

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.



# DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

