
1. Scope

This specification apply for SLH0704S102MTT of power inductors

2. Appearance

2-1.Dimensions(mm)

2-2.Recommended Land



A	7.3 ± 0.2 mm			
В	4.5mm MAX			
С	2.7 mm REF			
D	2.0 mm REF			
Е	5.4 mm REF			
F	1.6 mm REF			
G	2.2 mm REF			
Н	4.8 mm REF			
I	7.8 mm REF			

3. Coils Specification

3-1. Connection (Bottom View)



"S" is winding start

3-2. Turns and Wire

Terminal	S-F	
Turns	Winding Turns are approx	
Wire	0.10mm*1P G1 P180&2UEW-H	

^{*} Winding Turns are approx.

Font size: Width 2.9*High1.6(Black) Song

^{*} Dimension without tolerance is approx.



3-3. Electronical characteristics

Item	Specifications	Measuring Conditions	Measuring Instrument
Inductance	1.0mH ± 20% Within	1KHz/0.25V	TH2816B
D.C.R	5.0 Ω MAX	25℃	VR131
※ Iast	0.25 A MAX	1KHz/0.25V	TH2816B&VR7210

^{*} This indicates the value of current when the inductance is 25% lower than its initial value at D.C superposition or D.C current when temperature rise $\Delta T=40^{\circ}$ C whichever is lower .(Ta=20°C)

4. General Characteristics

4-1. Storage Temperature range : -40 $^{\circ}$ C $\sim +105 ^{\circ}$ C

4-2. Operating temperature range: -40° C $\sim +105^{\circ}$ C (Including coil's self temperature rise)

4-3. External appearance : No external defects can be found in the visual inspection.

4-4. Electrode strength : No electrode detachment should be found when the device is

pushed in two directions of X and Y with the forceof 5.0N for 10±2 seconds after soldering


between copper plate and the electrodes.(Refer to figure at right)

4-5. Vibration test : Inductance deviation is within $\pm 3.0\%$ after 1 hour sweeping vibration

in each three directions, namely, forward and backward, up and down, right and left. The frequency is $10\sim55\sim10$ Hz and the amplitude of

1 minute cycle is 1.5mm PP.


4-6. Recommended reflow condition:





4-7. Humidity test: Inductance deviation is within $\pm 5.0\%$ after 96 ± 4 hours test under the condition of relative humidity of 90 \sim 95% and temperature of 40 ± 2 °C, and 1 hour storage under room ambient conditions after the device is wiped with dry cloth.

5. Construction and materials




No.	Part name	Material	Remark
1	Drum Core	Ni-Zn Ferrite Core	
2	Wire	Polyurethane enameled copper wire	
3	Ring Core	Ni-Zn Ferrite Core	
4	Adhesive	Epoxy Resin	
⑤ Electrode		Cu+Sn plating	


Rev.01 Page 3 of 5 www.Sunltech.com



6. TAPE DIMENSIONS:




W	16.00±0.30	Р	12.00±0.10	A0	7.90±0.10	В0	7.90±0.10
E	1.75±0.10	PO	4.00±0.10	T	0.40±0.05	D1	Ø1.50 ^{+0.10}
KC	4.80±0.10	P2	2.00±0.10	F	7.50±0.10	DO	Ø1.50±0.10



Rev.01 Page 4 of 5 www.Sunltech.com

7. TAPE REEL DIMENSIONS:



单位:毫米

Туре	A	В	С	G	N	T
16mm	330	21 ± 0.8	13 ± 0.4	16.4	100	20.4

PACKAGING QUANTITY: 1000 PCS /REEL

Rev.01 Page 5 of 5 www.Sunltech.com