


Wire Wound SMD Power Inductors – ASWPA Series

Operating temperature range: -40°C~+125°C (Including self-heating)



FEATURES

- Magnetic-resin shielded construction reduces buzz noise to ultra-low levels
- Metallization on ferrite core results in excellent shock resistance and damage-free durability
- Closed magnetic circuit design reduces leakage flux and Electro Magnetic Interference (EMI)
- 30% higher current rating than conventional inductors of equal size
- AEC-Q200D verified

APPLICATIONS

- Infotainment system
- LED Lighting
- Airbag
- Power supply system except for power engine or chassis and safety system

PRODUCT IDENTIFICATION

ASWPA 4035 S 1R0 N T □□□

① ② ③ ④ ⑤ ⑥ ⑦

① Type	
ASWPA	Wire Wound SMD Power Inductor

② (L×W×H) [mm]	
External Dimensions (L×W×H) [mm]	
4035	4.0×4.0×3.5
6055	6.0×6.0×5.5
8050	8.0×8.0×5.0

③ Feature Type	
S	Standard

④ Nominal Inductance	
Example	Nominal Value
1R0	1.0μH
100	10μH

⑥ Packing	
T	Tape Carrier Package

⑤ Inductance Tolerance	
M	±20%
N	±30%

⑦ Design Code	
□□□	Standard product is blank

SHAPE AND DIMENSIONS

Fig.1






Fig.2



Recommended Land Pattern



Unit: mm

Series	Shape	A	B	C	D	E	F	a Typ.	b Typ.	c Typ.
ASWPA4035S	Fig.1	4.0±0.2	4.0±0.2	3.5 Max.	3.3±0.2	0.95±0.2	2.1±0.2	1.9	1.1	3.7
ASWPA6055S	Fig.1	6.0±0.3	6.0±0.3	5.5 Max.	4.9±0.3	1.55±0.3	2.9±0.3	2.8	1.7	5.7
ASWPA8050S	Fig.2	8.0±0.3	8.0±0.3	5.0 Max.	6.3±0.3	2.00±0.3	4.0±0.3	3.8	2.2	7.5

SPECIFICATIONS

ASWPA4035S Series

Part Number	Inductance	DC Resistance		Self-resonant Frequency	Saturation Current		Heat Rating Current	
	@100kHz,1V	Max.	Typ.	Min.	Max.	Typ.	Max.	Typ.
Units	μH	Ω		MHz	A		A	
Symbol	L	DCR		S.R.F	Isat		I _{rms}	
ASWPA4035S1R0MT	1.0±20%	0.024	0.020	76	6.30	6.90	3.85	4.50
ASWPA4035S1R2MT	1.2±20%	0.028	0.023	70	6.05	6.70	3.60	4.20
ASWPA4035S1R5MT	1.5±20%	0.032	0.027	62	5.45	6.05	3.30	3.90
ASWPA4035S2R2MT	2.2±20%	0.040	0.033	52	4.35	4.80	3.00	3.50
ASWPA4035S3R3MT	3.3±20%	0.058	0.048	38	3.50	3.80	2.50	2.90
ASWPA4035S4R7MT	4.7±20%	0.082	0.068	31	3.00	3.30	2.10	2.45
ASWPA4035S6R8MT	6.8±20%	0.101	0.084	24	2.50	2.80	1.90	2.20
ASWPA4035S8R2MT	8.2±20%	0.108	0.090	26	2.10	2.40	1.80	2.10
ASWPA4035S100MT	10±20%	0.140	0.120	21	2.05	2.30	1.55	1.85
ASWPA4035S150MT	15±20%	0.230	0.190	16	1.65	1.80	1.25	1.45
ASWPA4035S220MT	22±20%	0.290	0.240	10	1.30	1.40	1.10	1.30

SPECIFICATIONS

ASWPA4035S Series

Part Number	Inductance @100kHz,1V	DC Resistance		Self-resonant Frequency Min.	Saturation Current		Heat Rating Current	
		Max.	Typ.		Max.	Typ.	Max.	Typ.
Units	μH	Ω		MHz	A		A	
Symbol	L	DCR		S.R.F	Isat		Irms	
ASWPA4035S330MT	33±20%	0.420	0.350	10	1.10	1.20	0.90	1.05
ASWPA4035S470MT	47±20%	0.590	0.490	8.4	0.95	1.00	0.75	0.90
ASWPA4035S680MT	68±20%	1.090	0.910	7.0	0.75	0.85	0.55	0.65
ASWPA4035S101MT	100±20%	1.380	1.150	5.6	0.65	0.75	0.45	0.55
ASWPA4035S151MT	150±20%	2.280	1.900	4.0	0.55	0.60	0.35	0.45

ASWPA6055S Series

Part Number	Inductance @100kHz,1V	DC Resistance		Self-resonant Frequency Min.	Saturation Current		Heat Rating Current	
		Max.	Typ.		Max.	Typ.	Max.	Typ.
Units	μH	Ω		MHz	A		A	
Symbol	L	DCR		S.R.F	Isat		Irms	
ASWPA6055S3R3MT	3.3±20%	0.026	0.022	32	6.00	6.60	3.95	4.60
ASWPA6055S4R7MT	4.7±20%	0.031	0.026	24	4.90	5.50	3.60	4.25
ASWPA6055S6R8MT	6.8±20%	0.034	0.028	20	3.90	4.30	3.50	4.10
ASWPA6055S8R2MT	8.2±20%	0.049	0.041	21	3.90	4.30	2.90	3.40
ASWPA6055S100MT	10±20%	0.054	0.045	15	3.45	3.85	2.70	3.20
ASWPA6055S150MT	15±20%	0.074	0.062	12	2.50	2.70	2.35	2.75
ASWPA6055S220MT	22±20%	0.100	0.083	10	2.25	2.55	2.00	2.35
ASWPA6055S330MT	33±20%	0.170	0.142	7.8	1.65	1.80	1.55	1.80
ASWPA6055S470MT	47±20%	0.252	0.210	6.4	1.60	1.80	1.25	1.50
ASWPA6055S680MT	68±20%	0.353	0.294	6.4	1.25	1.45	1.00	1.25
ASWPA6055S101MT	100±20%	0.434	0.362	4.2	1.05	1.20	0.95	1.10
ASWPA6055S151MT	150±20%	0.686	0.572	4.2	0.90	1.00	0.75	0.90
ASWPA6055S221MT	220±20%	1.036	0.863	3.5	0.70	0.80	0.60	0.70
ASWPA6055S331MT	330±20%	1.603	1.336	2.8	0.57	0.63	0.50	0.60

ASWPA8050S Series

Part Number	Inductance @100kHz,1V	DC Resistance		Self-resonant Frequency Min.	Saturation Current		Heat Rating Current	
		Max.	Typ.		Max.	Typ.	Max.	Typ.
Units	μH	Ω		MHz	A		A	
Symbol	L	DCR		S.R.F	Isat		Irms	
ASWPA8050S1R0MT	1.0±20%	0.010	0.008	89	9.8	14.0	6.30	6.90
ASWPA8050S1R5MT	1.5±20%	0.013	0.010	67	8.1	11.0	5.65	6.20
ASWPA8050S2R2MT	2.2±20%	0.016	0.012	41	7.1	8.0	5.15	5.60
ASWPA8050S3R3MT	3.3±20%	0.022	0.017	27	6.5	7.0	4.40	4.80
ASWPA8050S4R7MT	4.7±20%	0.025	0.019	24	5.9	6.5	4.10	4.50
ASWPA8050S6R8MT	6.8±20%	0.031	0.024	20	5.5	6.2	3.60	4.00
ASWPA8050S8R2MT	8.2±20%	0.035	0.029	19.4	5.0	5.8	3.40	3.80
ASWPA8050S100MT	10±20%	0.038	0.032	15	4.9	5.6	3.20	3.60
ASWPA8050S150MT	15±20%	0.060	0.050	12	3.95	4.50	2.55	2.90
ASWPA8050S220MT	22±20%	0.087	0.073	9.5	3.25	3.70	2.25	2.50
ASWPA8050S330MT	33±20%	0.121	0.101	7.8	2.70	3.10	1.80	2.00
ASWPA8050S470MT	47±20%	0.173	0.144	6.4	2.30	2.60	1.50	1.70
ASWPA8050S680MT	68±20%	0.245	0.204	4.9	1.75	2.05	1.25	1.40



Specifications subject to change without notice. Please check our website for latest information. Revised 2017/10/15

Sunlord Industrial Park, Dafuyuan Industrial Zone, Guanlan, Shenzhen, China 518110 Tel: 0086-755-29832660 Fax: 0086-755-82269029 E-Mail: sunlord@sunlordinc.com

SPECIFICATIONS

ASWPA8050S Series

Part Number	Inductance	DC Resistance		Self-resonant Frequency	Saturation Current		Heat Rating Current	
	@100kHz,1V	Max.	Typ.	Min.	Max.	Typ.	Max.	Typ.
Units	μH	Ω		MHz	A		A	
Symbol	L	DCR		S.R.F	Isat		Irms	
ASWPA8050S101MT	100±20%	0.317	0.264	4.2	1.50	1.70	1.10	1.25
ASWPA8050S151MT	150±20%	0.423	0.353	3.5	1.10	1.20	0.95	1.00
ASWPA8050S221MT	220±20%	0.743	0.619	3.5	0.85	0.94	0.70	0.80
ASWPA8050S331MT	330±20%	1.097	0.914	2.8	0.68	0.75	0.60	0.65

Note: ※ 1: Rated current: Isat (max.) or Irms (max.), whichever is smaller;

※ 2: Saturation Current: *Max. Value*, DC current at which the inductance drops less than 20% from its value without current; *Typ. Value*, DC current at which the inductance drops 30% from its value without current;

※ 3: Heat Rating Current: DC current that causes the temperature rise (ΔT) from 20°C ambient. For *Max. Value*, $\Delta T < 40^\circ\text{C}$; For *Typ. Value*, ΔT is approximate 40°C.

The part temperature (ambient + temp. rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application