



CUSTOMER DRAWING

① CONN. MWP06M



② F/H MWP06M(2/1)



— 주 기 —

1. MARKING 및 CAV. NO는 당사 규정에 의하여 각인 할 것.
2. 상대 MATCHING CONNECTOR : CONN. MWP RECEPT.
3. ASSY 부품
  - 1) FRONT HOLDER : PH811-06120
  - 2) TERMINAL

적용 전선(SQ)	PART NAME	PART NO.
AV,AVS,AVSS 0.3~0.5 / AVX,AEX 0.5	MWP-M-S	MT091-27050
AV,AVS,AVSS,AVX,AEX 0.85~2	MWP-M-M	MT091-27250
AV,AVS,AVSS 0.3~0.5 / AVX,AEX0.5	MWP-M-S-Au	MT091-27060
AV,AVS,AVSS,AVX,AEX 0.85~2	MWP-M-M-Au	MT091-27260

3) WIRE SEAL

적용 전선(SQ)	PART NAME	PART NO.
AV,AVS 0.3 / AVSS 0.3~0.85	W/S MWP-0.3	RS220-01100
AV 0.5,AVSS1.25/AVS,AVX,AEX0.5~0.85	W/S MWP-SS	RS220-04100
AV 0.85,AVS 1.25	W/S MWP-S	RS220-02100
AVS,AVSS 2.0 /AV,AVX,AEX 1.25~2.0	W/S MWP-W	RS220-03100
막음SEAL용 PIN	MWP S/P	PZ001-08011

4. 본 부품은 방수형 CONNECTOR임.

K.K.L	90.07.01	-	△	신 규	L.S.J
승인	DATE	NOTE NO.	SYM	ALTERATION	담당

②	F/H MWP06M-GY	PH811-06120	GRAY	P.A			
①	CONN. MWP06M-B	PH801-06020	BLACK	P.B.T			
NO.	PART NAME	PART NO.	COLOR	MATERIAL			
	A	1/1(2/1)	K.H.J	L.S.J			
	THIRD ANGLE PROJECTION	TOLERANCE	SCALE	DESIGN	DRAWN	CHECKED	APPROVED

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	150MAX	200MAX	200VR	ANGLE
A	±0.2	±0.3	±0.5	±0.8	±1.0	±1.4	±30'

**KUM** 케이유엠