

**MVG(MV)-BP Series**

• 85°C 2,000Hrs assured.

- Vertical SMD type.
- Bi-polarized.
- For LED MT / TV.
- RoHS compliant.
- Halogen-free capacitors are also available.

**BDS(MVK)-BP Series**

• 105°C 1,000Hrs assured.

- Vertical SMD type.
- Bi-polarized.
- Wide Temperature Range.
- For LED MT / TV.
- RoHS compliant.
- Halogen-free capacitors are also available.

Solvent-proof



MV


MVG(MV)  
-BPBDS(MVK)  
-BP

Bi-polarized

Wide Temp.

**SPECIFICATIONS**

Item	Characteristics					
Series Name	MVG(MV)-BP			BDS(MVK)-BP		
Rated Voltage Range	4 ~ 50 V <sub>DC</sub>			6.3 ~ 50 V <sub>DC</sub>		
Operating Temperature Range	-40 ~ +85°C			-40 ~ +105°C		
Capacitance Tolerance	±20%(M)			(at 20°C, 120Hz)		
Leakage Current (In both directions)	I=0.05CV(μA) or 10μA, whichever is greater. Where, I:Max. Leakage current(μA), C:Nominal capacitance(μF), V:Rated voltage(V <sub>DC</sub> ) (at 20°C, after 2 minutes)					
Dissipation Factor(Tanδ)	Rated Voltage(V <sub>DC</sub> )	4	6.3	10	16	25
	MV-BP	0.45	0.32	0.26	0.24	0.22
	MVK-BP	-	0.35	0.26	0.24	0.20
	(at 20°C, 120Hz)					
Temperature Characteristics (Max. Impedance ratio)	Rated Voltage(V <sub>DC</sub> )	4	6.3	10	16	25
	Z(-25°C)/Z(20°C)	7	4	3	2	2
	Z(-40°C)/Z(20°C)	15	10	8	6	4
	(at 120Hz)					
Load Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage is applied with the following conditions with its polarization reversed every 250 hours.					
	Series Name	MVG(MV)-BP			BDS(MVK)-BP	
	Test time & temperature	2,000 hours at 85°C			1,000 hours at 105°C	
	Capacitance change	≤±20% of the initial value			≤±30% of the initial value	
	Tanδ	≤200% of the initial specified value			≤300% of the initial specified value	
	Leakage current	≤The initial specified value			≤The initial specified value	
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 500 hours at 85°C(MVG(MV)-BP) or 105°C(BDS(MVK)-BP) without voltage applied. The rated voltage shall be applied to the capacitors for a minimum of 30 minutes, at least 24 hours and not more than 48 hours before the measurements.					
	Series Name	MVG(MV)-BP			BDS(MVK)-BP	
	Capacitance change	≤±15% of the initial value			≤±25% of the initial value	
	Tanδ	≤150% of the initial specified value			≤200% of the initial specified value	
	Leakage current	≤The initial specified value			≤The initial specified value	
Others	Satisfied characteristics KS C IEC 60384-4					

**MVG(MV)-BP/  
BDS(MVK)-BP Series**
**PART NUMBERING SYSTEM**



# SURFACE MOUNT ALUMINUM ELECTROLYTIC CAPACITORS

## DIMENSIONS OF MVG(MV)-BP, BDS(MVK)-BP Series

Unit(mm)

DIMENSIONS		MARKING																																																								
<b>Recommended solder land on PC board</b>																																																										
<p>Note 1 : 6.3WV is marked by 6V.</p> <table border="1"> <thead> <tr> <th>Case code</th> <th><math>\phi D</math></th> <th>L</th> <th>A</th> <th>B</th> <th>C</th> <th>W</th> <th>P</th> <th>a</th> <th>b</th> <th>c</th> </tr> </thead> <tbody> <tr> <td>D55</td> <td>4</td> <td>5.2</td> <td>4.3</td> <td>4.3</td> <td>5.1</td> <td>0.5~0.8</td> <td>1.0</td> <td>1.0</td> <td>2.6</td> <td>1.6</td> </tr> <tr> <td>E55</td> <td>5</td> <td>5.2</td> <td>5.3</td> <td>5.3</td> <td>5.9</td> <td>0.5~0.8</td> <td>1.4</td> <td>1.4</td> <td>3.0</td> <td>1.6</td> </tr> <tr> <td>F55</td> <td>6.3</td> <td>5.2</td> <td>6.6</td> <td>6.6</td> <td>7.2</td> <td>0.5~0.8</td> <td>1.9</td> <td>1.9</td> <td>3.5</td> <td>1.6</td> </tr> <tr> <td>F60</td> <td>6.3</td> <td>5.7</td> <td>6.6</td> <td>6.6</td> <td>7.2</td> <td>0.5~0.8</td> <td>1.9</td> <td>1.9</td> <td>3.5</td> <td>1.6</td> </tr> </tbody> </table> <p>■ : Solder land on PC board</p>				Case code	$\phi D$	L	A	B	C	W	P	a	b	c	D55	4	5.2	4.3	4.3	5.1	0.5~0.8	1.0	1.0	2.6	1.6	E55	5	5.2	5.3	5.3	5.9	0.5~0.8	1.4	1.4	3.0	1.6	F55	6.3	5.2	6.6	6.6	7.2	0.5~0.8	1.9	1.9	3.5	1.6	F60	6.3	5.7	6.6	6.6	7.2	0.5~0.8	1.9	1.9	3.5	1.6
Case code	$\phi D$	L	A	B	C	W	P	a	b	c																																																
D55	4	5.2	4.3	4.3	5.1	0.5~0.8	1.0	1.0	2.6	1.6																																																
E55	5	5.2	5.3	5.3	5.9	0.5~0.8	1.4	1.4	3.0	1.6																																																
F55	6.3	5.2	6.6	6.6	7.2	0.5~0.8	1.9	1.9	3.5	1.6																																																
F60	6.3	5.7	6.6	6.6	7.2	0.5~0.8	1.9	1.9	3.5	1.6																																																

## RATINGS OF MVG(MV)-BP, BDS(MVK)-BP Series

### MVG(MV)-BP

$\mu F \backslash V_{DC}$	4	6.3	10	16	25	35	50
1.0 (1.5)							D55 5.5
2.2							D55 6.5
3.3							E55 9
4.7 (6.8)				D55 11		E55 13	E55 11
10 (15)		D55 13		E55 18		E55 21	F55 17
22	D55 14		E55 21		F55 24		
33		E55 23		F55 28			
47			F55 33				
			F55 36				

↑      ↑  
  Case code      Rated Ripple Current(mArms/ 85°C, 120Hz)

### BDS(MVK)-BP

$\mu F \backslash V_{DC}$	6.3	10	16	25	35	50
1.0 (1.5)						D55 5.3
2.2						D55 7.2
3.3						E55 9.0
4.7 (6.8)			D55 10		E55 14	E55 12
10 (15)	D55 12		E55 18		F60 23	F60 16
22	E55 23		F60 32			F60 20
33		F60 35				
47	F60 39					

↑      ↑  
  Case code      Rated Ripple Current (mA rms/105°C, 120Hz)

Note : → Use next higher voltage part.  
Parenthesized capacitance is not standard part.