

APPROVAL SHEET

To :

Customer P/N :

UDE P/N : RU1-161A9WGF

Description : RJ45 Tab up over USB 2.0 stack
Through Hole
10/100/1000 Base-T
Contact Area : 30 μ " Gold
LED:L-Green/Orange; R-Yellow



Spec No. Update Date
RU1156-00 2010/9/27

Approved	Checked	Prepared









湧德電子 股份有限公司
UDE Corp.

11F-1, No.58, Tongde 11th St., Taoyuan City, Taoyuan County (330), Taiwan
桃園縣桃園市(330)同德十一街58號11F之1
TEL:+886-3-3568600 FAX:+886-3-3560611
<http://www.ude-corp.com/>

1. MECHANICAL DIMENSION

1.1 Product Dimension


General Tolerance : X.X : ± 0.25
 X.XX : ± 0.13
 X.XXX : ± 0.08




1.2 Recommended PCB Layout

Component Side of Board

All dimension tolerance are $\pm 0.05\text{mm}$ unless otherwise specified




1.3 Standard RJ45 Plug Specification



- All dimensions follow :
 FCC subpart F, 68,500, Figure (C)(2)(i) & (C)(2)(ii) & (C)(3)(i)
 IEC 60603-7
- All plugs must be meeting the requirements of plug Go & No-Go gauge.
 Gauge follow : FCC subpart F, 68,500, Figure (C)(4)(i) & (C)(5)(i)
- There must be no damage to Housing and Locking Latch.
- There must be no nicks and cuts in cable.
- Durability : 750 cycles generally

1.4 Standard USB 2.0 Plug Specification



- All dimensions follow : Universal Serial Bus Specification 2.0 (April 27,2000)

Figure 6-9. USB Series A Plug Interface Drawing

2. REQUIREMENTS

2.1 Design and Construction

Product shall be of design, construction and physical dimensions specified on applicable.

2.2 Material

2.2.1 Terminal Parts (Underplating : 30 μ " min. Nickel overall)

2.2.1.1 RJ Terminal : PH. Bronze, Thickness=0.30mm

Finish : Contact Area : 30 μ " Gold

2.2.1.2 USB Terminal : PH. Bronze, Thickness=0.25mm

Finish : Contact Area : 30 μ " Gold

Solder Tail : 100 μ " min. Tin

2.2.1.3 Input Terminal : Brass, Thickness=0.35mm

Finish : 100 μ " min. Tin

2.2.1.4 Case Terminal : Brass, Thickness=0.30mm

Finish : 100 μ " min. Tin

2.2.2 Plastic Parts <UL94V-0>

2.2.2.1 Housing : Thermoplastic, Black

2.2.2.2 Case : Thermoplastic, Black

2.2.2.3 Spacer : Thermoplastic, Black

2.2.3 Shield Parts

2.2.3.1 Front Shield : Stainless, Thickness=0.25mm, unplating

2.2.3.2 Back Shield : Stainless, Thickness=0.20mm, Pre-soldering

2.2.3.3 USB Kink : Brass, Thickness=0.25mm

Finish : 100 μ " min. Tin over 30 μ " min. Nickel overall

2.3 Operating and Storage Temperature

Operating Temperature : 0°C to +70°C

Storage Temperature : -40°C to +85°C

2.4 RJ45 specifications

Insulation Resistance 500MΩ min.

Insertion force with the latch depressed 22N max

Removal force with the latch depressed 44N max

Locking Force of Plug Latch : 50N min. @ 60+/-5 sec

Durability : 2500 cycles

2.5 USB 2.0 specifications

Insulation Resistance 1000MΩ min.

Dielectric Withstanding Voltage : 500Vac @1min

Insertion force : 35N max

Removal force : 10N min

Durability : 1500 cycles

2.6 Performance and Test Description




Product is designed to meet electrical, mechanical and environmental performance requirements specified in below table. All tests are performed at ambient environmental conditions per MIL-STD-1344A and EIA-364 unless otherwise specified.

2.7 Packaging and Packing

All parts shall be packaged and packed to protect against physical damage, corrosion and deterioration during shipment and storage.

3. ELECTRICAL CHARACTERISTICS

3.1 Schematic



Emitting Color	λ_p (nm)	$V_f @ I_f=20mA$	$I_r @ V_r=5V$
Green	565	1.7 ~2.6 V	10µA max.
Yellow	585	1.7 ~2.6 V	10µA max.
Orange	610	1.7 ~2.6 V	10µA max.

3.2 Transmitter filter & Receiver filter

Type : Balance low pass 100Ω impedance

Insertion loss : 1~100 MHz -1.0dB max.

100~125 MHz -1.2dB max.

Return loss : 1~30 MHz -18dB min. load 100Ω

30~60MHz -16dB min. load 100Ω

60~80MHz -12dB min. load 100Ω

80~100MHz -10dB min. load 100Ω

3.3 Common Mode Rejection

@ 1~100 MHz -30dB min.

3.4 Cross Talk

@ 1~100 MHz -30dB min.

3.5 Inductance @ 100KHz, 0.1V, 8mA DC BIAS

Input(R2-R3), Input(R4-R5), Input(R6-R7), Input(R8-R9): 350 μH min.

3.6 HiPot Test

Input(R2-R3) To Output(C1-C2) : 1500Vac 60s or 2250Vdc 60s

Input(R4-R5) To Output(C3-C6) : 1500Vac 60s or 2250Vdc 60s

Input(R6-R7) To Output(C4-C5) : 1500Vac 60s or 2250Vdc 60s

Input(R8-R9) To Output(C7-C8) : 1500Vac 60s or 2250Vdc 60s

4. ORDER INFORMATION

R U 1 - 1 6 1A 9WG F
 A B C D

A. LED Code :

L-Green/Orange; R-Yellow. <Refer to Schematic of LED>

B. Mechanical Code :

w/ UDE Logo, w/o Spring

C. Schematics Code :

9WG : 9WG circuit

D. Plating Code :

Underplating	30 μ " min. Nickel overall	
Solder Tail	100 μ " min. Bright Tin	100 μ " min. Matted Tin
Contact Area	A : Gold Flash	1 : Gold Flash
	C : 6 μ " gold	6 : 6 μ " gold
	B : 10 μ " gold	
	D : 15 μ " gold	2 : 15 μ " gold
	<u>F : 30μ" gold</u>	3 : 30 μ " gold
G : 50 μ " gold	4 : 50 μ " gold	

5. DIPPING TEMPERATURE PROFILE

Note :

The measuring point for the specified temperature shall be on the soldered part of the lead.

