

# DATA SHEET

CURRENT SENSOR-LOW TCR

**PE1206-series**

5%,1%

size 1206

RoHS Compliant & Halogen Free



**SCOPE**

This specification describes PE1206 current sensor – low TCR chip resistors with lead-free terminations.

**APPLICATIONS**

- Power supplies
- Consumer(Mobile 、 PNDs 、 ...)
- Laptop
- HDDs

**FEATURES**

- Products with lead free terminations meet RoHS requirements.
- High component and equipment reliability with high power rating.
- Low resistance and narrow tolerance can suitable for current detection.
- Low thermal EMF(<1uV/°C).
- Low inductance <0.5uH (10MHz).

**ORDERING INFORMATION - GLOBAL PART NUMBER**

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient of resistance, taping reel, resistance value.

PE1206    X    X    X    XX    XXXX    Z  
 (1)    (2)    (3)    (4)    (5)    (6)

**(1) TOLERANCE**

F = ±1%  
 J = ±5%

**(2) PACKAGING TYPE**

K = Embossed taping reel

**(3) TEMPERATURE COEFFICIENT OF RESISTANCE**

F= ±100ppm/°C  
 M= ±75ppm/°C  
 E= ±50ppm/°C

**(4) TAPING REEL**

07 = 7 inch dia. Reel & Power Rating 0.25W  
 7W = 7 inch dia. Reel & Power Rating 0.5W  
 47 = 7 inch dia. Reel & Power Rating 1W

**(5) RESISTANCE VALUE**

0R003 (3mΩ) ~ 0R3 (300mΩ)

**(6) DEFAULT CODE**

Letter Z is system default code for order only<sup>(NOTE)</sup>

**ORDERING EXAMPLE**


The ordering code for a PE1206 1W chip resistor, TC100 value 0.01 Ω (10mΩ) with ±1% tolerance, supplied in 7-inch tape reel with 4Kpcs quantify is:  
 PE1206FKF470R01Z.

**NOTE**

1. All our RSMD products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process".
2. On customized label, "LFP" or specific symbol can be printed.

**MARKING**

PE1206




4 digits

The “R” is used as a decimal point; the other 3 digits are significant.

**OUTLINES**

For dimension, please refer to Table 1



**DIMENSIONS**

Table 1

TYPE	PE1206
L (mm)	3.20±0.20
W (mm)	1.60±0.20
H (mm)	0.60±0.15
l1 (mm) - 3mΩ	1.30±0.20
l1 (mm) - 4mΩ	1.20±0.20
l1 (mm) - 5mΩ ~ 8 mΩ	1.15±0.20
l1 (mm) - ≥ 9 mΩ	0.58±0.20

**ELECTRICAL CHARACTERISTICS**

Table 2

**CHARACTERISTICS**

Operating Temperature Range	-55°C to +155°C
Maximum Working Voltage	$\sqrt{(P * R)}$
Resistance Range	3mΩ ~300mΩ
Temperature Coefficient	±100ppm/°C ±75ppm/°C ±50ppm/°C

**PACKING STYLE AND PACKAGING QUANTITY**

Table 3

PRODUCT TYPE	PACKING STYLE	REEL DIMENSION	QUANTITY PER REEL
PE1206	Embossed taping reel	7" (178 mm)	4,000 Units

**FUNCTIONAL DESCRIPTION**

**POWER RATING**

PE1206 rated power at 70°C is 1/4W, 1/2W & 1W

**RATED VOLTAGE**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$U = \sqrt{(P * R)}$$

Where

U=Continuous rated DC

or AC (rms) working voltage (v)

P=Rated power

R=Resistance value (Ω)




Fig. 3 Maximum dissipation (P) in percentage of rated power as a function of the operating ambient temperature (T<sub>amb</sub>)

**TAPING REEL**

Table 4

DIMENSION	1206
Tape Width(mm)	8
ØA (mm)	178.0±5
ØN (mm)	60.0±2
ØC (mm)	13.50±0.5
ØD (mm)	21.0±0.8
W1 (mm)	8.4 +1/-0
W2 (mm)	Max 12.4




Fig.4 Reel

**TAPE SPECIFICATION**

Table 5

DIMENSION	1206
A <sub>0</sub> (mm)	1.82±0.15
B <sub>0</sub> (mm)	3.53±0.15
W (mm)	8.00±0.30
E (mm)	1.75±0.10
F (mm)	3.50±0.10
P <sub>0</sub> (mm)	4.00±0.10
P <sub>1</sub> (mm)	4.00±0.10
P <sub>2</sub> (mm)	2.00±0.10
D <sub>0</sub> (mm)	1.50±0.10
D <sub>1</sub> (mm)	1.50±0.10
T (mm)	0.85±0.15





Fig.5 Embossed tapping reel

**PACKING METHOD**

**LEADER/TRAILER TAPE SPECIFICATION**




CCB325

Fig.6 Leader/trailer tape

**RECOMMENDED FOOTPRINT DIMENSIONS**

FOOTPRINT DIMENSION

Size Footprint	Dimensions		Code	unit :mm
PE1206	A	B	C	D
3mR	6.2	0.4	2.9	1.84
4mR	6.2	0.5	2.85	1.84
5mR~8mR	6.2	0.6	2.8	1.84
≥9mR	6.2	1.2	2.5	1.84



**Fig.7 RECOMMENDED FOOTPRINT DIMENSIONS**

## TESTS AND REQUIREMENTS

TEST	TEST METHOD	PROCEDURE	REQUIREMENT
Life/ Endurance	IEC 60115-1 4.25.1	1,000 hours at 70±5 °C applied RCWV 1.5 hours on, 0.5 hour off, still air required	± (1.0 % + 0.0005 Ω)
High Temperature Exposure/ Endurance at upper category temperature	IEC 60068-2-2	1,000 hours at 155±5 °C,unpowered	± (1.0 % + 0.0005 Ω)
Moisture Resistance	MIL-STD-202 Method 106G	Each temperature / humidity cycle is defined at 8 hours (Method 106G), 3 cycles / 24 hours for 10d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, un-powered Parts mounted on test-boards, without condensation on parts Measurement at 24±2 hours after test conclusion.	± ( 0.5% + 0.0005 Ω)
Thermal Shock	MIL-STD-202 Method 107G	-55/+125 °C Note: Number of cycles required is 300. Devices unmounted Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	± ( 1.0% + 0.0005 Ω)
Short time overload	IEC 60115-1 4.13	Applied 5 times of rating power 5 seconds at room temperature	± (0.5% + 0.0005 Ω) No visible damage
Board Flex/ Bending	IEC 60068-2-21	Chips mounted on a 90mm glass epoxy resin PCB(FR4) 2 mm bending Bending time: 60±1 seconds	± (1.0 % + 0.0005 Ω)
Solderability - Wetting	IPC/JEDEC J-STD-002B test B	Electrical Test not required Magnification 50X SMD conditions: 1st step: Method B, aging 4 hours at 155 °C dry heat 2nd step: leadfree solder bath at 245±3 °C Dipping time: 3±0.5 seconds	Well tinned (≥95% covered) No visible damage
- Leaching	IPC/JEDEC J-STD-002B test D	Leadfree solder, 260 °C, 30 seconds immersion time	No visible damage
- Resistance to Soldering Heat	IEC 60068-2-58	Condition B, no pre-heat of samples Leadfree solder, 260±5 °C, 10±1seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	± ( 0.5% + 0.0005 Ω) No visible damage

**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 0	2010-08-18		- First issue of this specification
Version 1	2010-11-11		- Change Quantity Per Reel from 5Kpcs to 4Kpcs
Version 2	2011-09-01		- Range extension to 300m $\Omega$