




B16WS

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

Reverse Voltage - 60 Volts Forward Current - 1.0 Ampere

SOD-323



Dimensions in millimeters and (inches)

FEATURES

- Low forward voltage drop
- Guard ring construction for transient protection
- For use in low voltage, high frequency inverters
- High surge current capability

MECHANICAL DATA

Case: JEDEC SOD-323 molded plastic body

Terminals: Solderable per MIL-STD-750, Method 2026

Approx: Weight: 5.48mg/0.00019oz

Mark: SM

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

MDD Catalog Number	SYMBOLS	B16WS	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	60	VOLTS
Maximum RMS voltage	V _{RMS}	42	VOLTS
Maximum DC blocking voltage	V _{DC}	60	VOLTS
Maximum average forward rectified current	I _(AV)	1.0	Amp
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	10.0	Amps
Maximum instantaneous forward voltage at 1.0A	V _F	0.7	Volts
Total powerdissipation	P _{tot}	250	mW
Thermal Resistance, Junction to AmbientAir	R _{θJA}	400	°C/W
Maximum DC reverse current at rated DC blocking voltage at VR=60V	I _R	0.1	mA
Typical junction capacitance (NOTE 1)	C _J	120	pF
Operating junction temperature range	T _J	125	°C
Storage temperature range	T _{STG}	-55 to +150	°C

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.



RATINGS AND CHARACTERISTIC CURVES B16WS

Fig.1 Power Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 TYPICAL FORWARD VOLTAGE





Fig.4 Typical Junction Capacitance



The curve graph is for reference only, can't be the basis for judgment(曲线图仅供参考)!

