


TRANSISTOR(NPN)

FEATURES

- Complementary Type The PNP Transistor MMBT3906 is Recommended
- Epitaxial Planar Die Construction



1. Base 2. Emitter 3. Collector
SOT-23 Plastic Package

MARKING:1AM

Absolute Maximum Ratings ($T_a = 25\text{ }^\circ\text{C}$)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	60	V
V_{CEO}	Collector-Emitter Voltage	40	V
V_{EBO}	Emitter-Base Voltage	6	V
I_C	Collector Current	200	mA
P_C	Collector Power Dissipation	200	mW
$R_{\theta JA}$	Thermal Resistance From Junction To Ambient	625	$^\circ\text{C}/\text{W}$
T_j	Junction Temperature	150	$^\circ\text{C}$
T_{stg}	Storage Temperature	-55 ~ +150	$^\circ\text{C}$

Characteristics at $T_a = 25\text{ }^\circ\text{C}$









Parameter	Symbol	Test conditions	Min	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = 10\mu\text{A}, I_E = 0$	60		V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = 1\text{mA}, I_B = 0$	40		V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = 10\mu\text{A}, I_C = 0$	6		V
Collector cut-off current	I_{CBO}	$V_{CB} = 60\text{V}, I_E = 0$		0.1	μA
Collector cut-off current	I_{CEX}	$V_{CE} = 30\text{V}, V_{BE(off)} = 3\text{V}$		50	nA
Emitter cut-off current	I_{EBO}	$V_{EB} = 5\text{V}, I_C = 0$		0.1	μA
DC current gain	$h_{FE(1)}$	$V_{CE} = 1\text{V}, I_C = 10\text{mA}$	100	300	
	$h_{FE(2)}$	$V_{CE} = 1\text{V}, I_C = 50\text{mA}$	60		
	$h_{FE(3)}$	$V_{CE} = 1\text{V}, I_C = 100\text{mA}$	30		
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = 50\text{mA}, I_B = 5\text{mA}$		0.3	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C = 50\text{mA}, I_B = 5\text{mA}$		0.95	V
Transition frequency	f_T	$V_{CE} = 20\text{V}, I_C = 10\text{mA}, f = 100\text{MHz}$	300		MHz
Delay Time	t_d	$V_{CC} = 3\text{V}, V_{BE} = -0.5\text{V}$		35	nS
Rise Time	t_r	$I_C = 10\text{mA}, I_{B1} = -I_{B2} = 1.0\text{mA}$		35	nS
Storage Time	t_s	$V_{CC} = 3\text{V}, I_C = 10\text{mA},$		200	nS
Fall Time	t_f	$I_{B1} = -I_{B2} = 1\text{mA}$		50	nS

CLASSIFICATION OF $h_{FE(1)}$

Rank	O	Y	
Range	100-200	200-300	





Typical Characteristics



PACKAGE OUTLINE

Plastic surface mounted package

SOT-23


SOLDERING FOOTPRINT


Unit : mm

