### 乾坤科技股份有限公司

DOCUMENT : SR990000NH

REVISION : A0
PAGE : 1 OF 7

### 2W, 2512, L Type Low Resistance Chip Resistor (Lead free / Halogen Free)

1. Scope

This specification applies to 3.2mm x 6.4mm size 2W, fixed metal foil current sensing resistors used in electronic equipment.

2. Type Designation

$$RL-3264-9 - \square \square \square - \square \underline{NH}$$
 (1) (2) (3) (4)

Where

- (1) Series No.
- (2) Resistance value:

For example:

Four digits of number

$$R002 = 2m\Omega$$


$$3R25m = 3.25m\Omega$$

(3) Tolerance:

Refer to paragraph 4-1

(4) NH = Sn plating (Lead free / Halogen free)

#### 3. Dimensions and schematic



Code	Dimensions (mm)		
Letter	3264		
L	$6.35 \pm 0.25$		
W	$3.20 \pm 0.20$		
a	$(1 \text{m}\Omega)$ $2.50 \pm 0.15$		
	$(2m\Omega)$ 1.90 ± 0.15		
	$(3.25 \text{m}\Omega)$ $2.0 \pm 0.15$		
t	$(1 \text{m}\Omega)$ $0.70 \pm 0.15$		
	$(2m\Omega)$ 0.65 ± 0.15		
	$(3.25 \text{m}\Omega)  0.50 \pm 0.15$		

Figure 1. Construction and Dimensions

REVISION : A0 乾坤科技股份有限公司

: 2 OF 7 **PAGE** 

DOCUMENT : SR990000NH

### 4. Specification:

Characteristics	Feature 2W	
Power Ratings*		
Resistance Value	$1\sim 2m\Omega, 3.25m\Omega$	
Temperature Coefficient of Resistance	$(1m\Omega)$ $\pm 200$ ppm/°C $(2m\Omega)$ $\pm 100$ ppm/°C $(3.25m\Omega)$ $\pm 50$ ppm/°C	
Operation Temperature Range	-55°C ~+170°C	
Resistance Tolerance	$\pm 1\%(F)$ , $\pm 2\%(G)$ , $\pm 5\%(J)$	
Insulation Resistance	Over 100MΩ	
Maximum Working Voltage (V)	$(P*R)^{1/2}$	

#### Note \*:

Power ratings is based on continuous full load operation at rated ambient temperature of 70°C. For resistors operated at ambient temperature in excess of 70°C, the maximum load shall be derated in accordance with the following curve.




Figure 2. : Power Temperature Derating Curve

## CYNTEC CO., LTD. 乾坤科技股份有限公司

DOCUMENT : SR990000NH

REVISION : A0
PAGE : 3 OF 7

### 5. Reliability Performance

Renability Ferrormance		
Test Item	Condition of Test	Requirements
Short Time Overload	2.5 x Rated power for 5 seconds Refer to JIS C 5201-1 4.13	$\Delta R: \pm (0.5\% + 0.0005\Omega)$ Without significant damage by flashover ( spark, arching ), burning or breakdown etc.
Thermal Shock	-55 ~150°C 1,000 cycles, 15 min at each extreme condition Refer to JIS C 5201-1 4.19	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without distinct damage in appearance
Low Temperature Storage	Kept at -55°C, 1,000 hours Refer to JIS C 5201-1 4.23.4	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without distinct damage in appearance
Resistance to Soldering Heat	Dipped into solder at $270 \pm 5^{\circ}$ C for $20 \pm 1$ seconds Refer to JIS C 5201-1 4.18	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without distinct damage in appearance
Load Life	Rated voltage for 1.5hours followed by a pause 0.5hour at $70 \pm 3^{\circ}$ C Cycle repeated 1,000 hours Refer to JIS C 5201-1 4.25	$\Delta R$ : $\pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Damp Heat with Load	40 ± 2°C with relative humidity 90% to 95%.  D.C. rated voltage for 1.5 hours ON 30 minutes OFF.  Cycle repeated 1,000 hours  Refer to JIS C 5201-1 4.24	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without distinct damage in appearance
High Temperature Exposure	Kept at 170°C for 1,000 hours Refer to JIS C 5201-1 4.23.2	$\Delta R$ : $\pm (1.0\% + 0.0005\Omega)$ Without distinct damage in appearance
Solderability	Temperature of Solder: $245 \pm 5^{\circ}$ C Immersion Duration: $3 \pm 0.5$ second Refer to JIS C 5201-1 4.17	Uniform coating of solder cover minimum of 95% surface being immersed

## CYNTEC CO., LTD. 乾坤科技股份有限公司

DOCUMENT : SR990000NH

REVISION : A0
PAGE : 4 OF 7

Test Item	Condition of Test	Requirements
Mechanical Shock	Refer to JIS C 5201-1 4.21	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without mechanical damage such as break
Substrate Bending	Bending width : 2mm	$\Delta R$ : $\pm (0.5\% + 0.0005\Omega)$ Without mechanical damage such as break


### 乾坤科技股份有限公司

DOCUMENT : SR990000NH

REVISION : A0
PAGE : 5 OF 7

### 6. Recommended Solder Pad Dimensions

	W	L	D
3264	4.00	8.00	3.35



Note: We recommend there is no circuit design between pads to avoid circuit short

### 乾坤科技股份有限公司

DOCUMENT : SR990000NH

: 6 OF 7


REVISION : A0

**PAGE** 


### 7. Packaging

#### 7-1 Dimensions

#### 7-1-1 Tape packaging dimensions



#### 7-1-2 Reel dimensions



### 乾坤科技股份有限公司


DOCUMENT : SR990000NH

REVISION : A0
PAGE : 7 OF 7

#### 7-2 Peel Strength of Top Cover Tape

The peel speed shall be about 300mm/min.

The peel force of top cover tape shall between 0.1 to 0.7N



#### 7-3 Number of Taping

2,000 pieces / reel

#### 7-4 Label marking

The following items shall be marked on the reel.

- (1) Type designation
- (2) Quantity
- (3) Manufacturing date code
- (4) Manufacturer's name
- (5) The country of origin