



Recommended P.C.B Layout

MATERIAL

Contact Pin : Brass
 Insulator: NY6T UL94-V0

SPECIFICATION

Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin. at DC 500V
 Contact Resistance : 20mΩMax. at DC 100mA
 Dielectric Voltage : AC 500V for one minute
 Operation Temperature : -40°C to + 105°C
 適用波峰焊製程溫度: 260°C ± 5°C 3~5S

210-9 1- 04 G B 01
 1 2 3 4 5 6

- 1. 7: Green Product
- 9: Green Product High Temp
- 2. 1: Single row
- 2: Dual rows
- 3. No. of contacts per row
- 4. G: Gold flash
- 5. B: Black Insulator
- 6. Pinrex internal code.



| | | | | | | | | | | | |
|------|-------------------|------------|--|--|--------------|------------|--|---------------------------------------|----------|----------------------------|----------------------------|
| E | 增加材質 | 2018/05/23 | TOLERANCE .0 =±.30 .00 =±.20 .000 =±.XXX .0000=±. ANG.=±3° | | OLD PART NO. | | TITLE PIN HEADER 2.54*2.54mm STRAIGHT TYPE, SINGLE ROW | 频锐科技股份有限公司 PINREX TECHNOLOGY CORP. | | | |
| D | 增加製程溫度 | 2017/09/01 | | | UNITS : mm | DRAWER 杨海琴 | | | CHECK 李劍 | | |
| C | REVISE SIZE | 2011/06/08 | | | SCALE NONE | SIZE A4 | SHEET 1 OF 1 | REV. E | APP'D 李劍 | NEW PART NO. 210-91-04GB01 | DRAW NO. 210-91-04GB01(E版) |
| B | REVISE DIMENSIONS | 2007/09/01 | | | | | | | | | |
| A | RELEASE | 2005/01/26 | | | | | | | | | |
| REV. | DESCRIPTION | DATE | | | | | | | | | |