



| REVISION DATA | | | |
|---------------|-----|-------------|------|
| S/N | ECN | DESCRIPTION | DATE |
| | | | |
| | | | |
| | | | |

Technical Data

Material:
 Pin(outer sleeve): Brass,machined CuZn38Pb2
 Plating(outer sleeve):
 Tin plated:2µm/80µ"Ni, 5µm/200µ"Sn
 Gold Plated:2µm/80µ"Ni,Full gold
 Insulator(black): Glass filled thermoplastic polyester
 UL94V-0

Electrical:
 Current rating: 3Amps/contact max.
 Contact resistance: ≤4mΩ/contact
 Insulation resistance: ≥1000MΩ at V=100V
 Operating voltage: 60VAC/DC

Mechanical:
 Operating temperatures: Gold Plated:-55°C to+125°C
 Tin plated:-40°C to+105°C

Ordering information

JRK - NNN X - B P 1276A

| No. of Positions | Insulator Type code | Pin Plating code |
|------------------|---------------------|------------------|
| 1 | Single row | 1 Tin150µ" |
| 2 | Double row | 2 Tin200µ" |
| | | 3 GF |
| | | 4 Gold2µ" |
| | | 5 Gold3µ" |
| | | 6 Gold10µ" |
| | | 7 Gold15µ" |
| | | S Special |

| TOLERANCE: | PROJECTION | TITLE: |
|-------------|------------|--|
| ANGLE ±5° | | 2.54mmPitch SIP Adapters 90° Pin Length 12.76mm |
| X.XXX ±0.05 | DATE | 2013-6-3 |
| X.XX ±0.15 | DRAWN | sean ma |
| X.X ±0.20 | CHECKED | PART NO: JRK-NNN1-BP1276A |
| X. ±0.35 | APPROVED | DRAWING NO: JRK-NNN1-B1276A |
| | | REV: A UNIT: mm SCALE: 3:1 SIZE: A4 |

A

B

4

3

2

1

A

B

C

D