




Circuit diagram



- Notes:
1. Rating: 12V DC 50mA
 2. Contact resistance: 100mΩ max
 3. Insulation resistance: 100MΩ 250V AC for 1min
 4. Dielectric strength: 250V AC(50/60hz) for 1min
 5. Life test: 100,000 Cycles
 6. Travel: 0.15±0.05mm

NO.1	
PART NO	Material/Qty
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

NO.2	
PART NO	MATERIAL/Qty
S	SUS/1PC
D	SUS/2PCS

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	---	3	Phosphor Bronze	Plating silver	---
④	Contact	---	1	SUS	Plating silver	---
③	Base	---	1	Nylon	Black	---
②	Cover	---	1	SUS	Natural	---
①	Keystroke	---	1	Nylon	Black	---

APPROVALS		DATE	TITLE:	
DRAWN	JKUN.LU	2016/6/30	Tact Switch	
CHECKED			ELECTRONICS CO.,LTD	

APPROVALS		DATE	TITLE:			
APPROVALS			Tact Switch			
CHECKED			ELECTRONICS CO.,LTD			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE		30~以上 ±0.30	ANGLE	±2°	DRAWING NO.	
		10~30 ±0.20	UNIT:	mm	SCALE: 1:1	
		5~10 ±0.15	PROJ:		SHEET 1 OF 1	
		~5 ±0.10				