



General Description

The 18N10. combines advanced trench MOSFET technology with a low resistance package to provide extremely low RDS(ON). This device is ideal for power switching application.

Features

V _{DSS}	R _{D(S)(ON)} @ 10V (typ)	I _D
100V	35mΩ	18A

**Schematic Diagram****TO-252****Application**

- Power switching application
- LED backlighting
- RoHS Compliant

Ordering Information

Part Number	Marking	Case	Packaging
18N10.	18N10.	TO-252	2500pcs/Reel

Table 1. Absolute Maximum Ratings (TA=25°C)

Symbol	Parameter	Value	Unit
V _{DS}	Drain-Source Voltage (V _{GS} =0V)	100	V
V _{GS}	Gate-Source Voltage (V _{DS} =0V)	±20	V
I _D (DC)	Drain Current (DC) at T _c =25°C	18	A
I _{DM} (pulse)	Drain Current-Continuous@ Current-Pulsed (Note 1)	72	A
P _D	Maximum Power Dissipation(T _c =25°C)	47	W
E _{AS}	Single Pulse Avalanche Energy (Note 2)	20	mJ
T _J , T _{STG}	Operating Junction and Storage Temperature Range	-55 To 175	°C

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2.E_{AS} condition:T_J=25°C, V_{DD}=50V, V_G=10V, R_G=25Ω

Table 2. Thermal Characteristic

Symbol	Parameter	Value	Max	Unit
R _{θJC}	Thermal Resistance,Junction-to-Case	---	3.2	°C/W


Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V I _D =250μA	100			V
I _{DSS}	Zero Gate Voltage Drain Current(Tc=25°C)	V _{DS} =100V, V _{GS} =0V			1	μA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	1.0	2.0	3.0	V
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V			±100	nA
R _{DS(ON)}	Drain-Source On-State Resistance	V _{GS} =4.5V, I _D = 1 A		38	55	mΩ
		V _{GS} =10V, I _D = 1 A		35	45	mΩ
Dynamic Characteristics						
g _{FS}	Forward Transconductance	V _{DS} =5V, I _D =4.5A	5			S
C _{iss}	Input Capacitance	V _{DS} =50V, V _{GS} =0V f=1.0MHz		1380		PF
C _{oss}	Output Capacitance			88		PF
C _{rss}	Reverse Transfer Capacitance			60		PF
Q _g	Total Gate Charge	V _{DS} =50V, I _D =4.5A V _{GS} =10V		26.8		nC
Q _{gs}	Gate-Source Charge			6.4		nC
Q _{gd}	Gate-Drain Charge			12.4		nC
Switching Times						
t _{d(on)}	Turn-on Delay Time	V _{DS} =50V, R _L =8.6Ω V _{GS} =10V, R _G =3Ω		7		nS
t _r	Turn-on Rise Time			12		nS
t _{d(off)}	Turn-Off Delay Time			24		nS
t _f	Turn-Off Fall Time			11		nS
Source-Drain Diode Characteristics						
I _{SD}	Source-Drain Current(Body Diode)			18		A
I _{SDM}	Pulsed Source-Drain Current(Body Diode)			72		A
V _{SD}	Forward On Voltage ^(Note 1)	T _J =25°C, I _{SD} =1A, V _{GS} =0V		0.75	1	V
t _{rr}	Reverse Recovery Time ^(Note 1)	T _J =25°C, I _F =4.5A di/dt=500A/μs		22		nS
Q _{rr}	Reverse Recovery Charge ^(Note 1)			28		nC
t _{on}	Forward Turn-on Time	Intrinsic turn-on time is negligible(turn-on is dominated by L _S +L _D)				


Notes 1.Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 1.5%, Starting T_J=25°C

Test Circuit


1) E_{AS} Test Circuits



2) Gate Charge Test Circuit:



3) Switch Time Test Circuit:



TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (Curves)

Figure1. On-Region Characteristics




Figure 2: Transfer Characteristics




Figure3. ID vs Junction Temperature




Figure4. On-Resistance vs. Junction Temperature




Figure5. On-Resistance vs. Gate-Source Voltage




Figure6. Body-Diode Characteristics




Figure7. Gate-Charge Characteristics




Figure 8. Capacitance Characteristics




Figure 9. Maximum Forward Biased Safe Operating Area




Figure10. Single Pulse Power Rating Junction-to-Case






Figure11. Normalized Maximum Transient Thermal Impedance



TO-252 Package information



COMMON DIMENSIONS

SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.40
A1	0.00	-	0.20
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.50
c	0.43	0.53	0.63
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.80
E1	4.63	-	-
e	2.286BSC		
H	9.40	10.10	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L2	0.51BSC		
L3	0.88	-	1.28
L4	0.50	-	1.00
L5	1.65	1.80	1.95
θ	0°	-	8°