

SE60210GA  
**N-Channel Enhancement-Mode MOSFET**

Revision: A

**General Description**

This type used advanced trench technology and design to provide excellent  $R_{DS(ON)}$  with low gate charge.

- | High density cell design for ultra low  $R_{DS(ON)}$
- | Excellent package for good heat dissipation

**Features**

For a single MOSFET

- |  $V_{DS} = 60V$
- |  $R_{DS(ON)} = 2.2m\Omega$  @  $V_{GS}=10V$
- |

**Pin configurations**

See Diagram below



**Absolute Maximum Ratings**

Parameter	Symbol	Rating	Units
Drain-Source Voltage	$V_{DS}$	60	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Drain Current	Continuous	210	A
	Pulsed	800	
Total Power Dissipation @ $TA=25^\circ C$	$P_D$	300	W
Operating Junction Temperature Range	$T_J$	-55 to 175	$^\circ C$

# SE60210GA

Electrical Characteristics (TJ=25°C unless otherwise noted)						
Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
<b>OFF CHARACTERISTICS (Note 2)</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	I <sub>D</sub> =250µA, V <sub>GS</sub> =0 V	60			V
I <sub>DSS</sub>	Drain to Source Leakage Current	V <sub>DS</sub> = 48V, V <sub>GS</sub> =0V			1	µA
I <sub>GSS</sub>	Gate-Body Leakage Current	V <sub>GS</sub> =20V			100	nA
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> =250µA	2.0	3.0	4.0	V
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance	V <sub>GS</sub> =10V, I <sub>D</sub> =20A		2.2	2.6	mΩ
<b>DYNAMIC PARAMETERS</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =30V, f=1MHz		7070		pF
C <sub>oss</sub>	Output Capacitance			2140		pF
C <sub>rss</sub>	Reverse Transfer Capacitance			63		pF
<b>SWITCHING PARAMETERS</b>						
Q <sub>g</sub>	Total Gate Charge <sup>2</sup>	V <sub>GS</sub> =10V, V <sub>DS</sub> =30V, I <sub>D</sub> =20A		85		nC
Q <sub>gs</sub>	Gate Source Charge			24		nC
Q <sub>gd</sub>	Gate Drain Charge			14		nC
t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>GS</sub> =10V, V <sub>DS</sub> =30V, R <sub>GEN</sub> =10Ω		36		ns
t <sub>d(off)</sub>	Turn-Off Delay Time			95		ns
t <sub>d(r)</sub>	Turn-On Rise Time			62		ns
t <sub>d(f)</sub>	Turn-Off Fall Time			34		ns
<b>Thermal Resistance</b>						
Symbol	Parameter				Typ	Units
R <sub>θJC</sub>	Junction to Case				0.5	°C/W

# SE60210GA

## Typical Characteristics

Fig 1. Typical Output Characteristics




Figure 2. On-Resistance vs. Gate-Source Voltage




Figure 3. On-Resistance vs. Drain Current and Gate Voltage




Figure 4. Normalized On-Resistance vs. Junction Temperature




Figure 5. Typical Transfer Characteristics





Figure 6. Typical Source-Drain Diode Forward Voltage



# SE60210GA

## Typical Characteristics

Figure 7. Typical Gate-Charge vs. Gate-to-Source Voltage




Figure 8. Typical Capacitance vs. Drain-to-Source Voltage




Figure 9. Maximum Safe Operating Area




Figure 10. Maximum Drain Current vs. Case Temperature






Figure 11. Normalized Maximum Transient Thermal Impedance, Junction-to-Case



# SE60210GA

## Package Outline Dimension

TO-220



DIM.	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	4.24	4.65	0.167	0.183
b	0.69	1.02	0.027	0.040
b(1)	1.14	1.78	0.045	0.070
c	0.36	0.61	0.014	0.024
D	14.33	15.85	0.564	0.624
E	9.96	10.52	0.392	0.414
e	2.41	2.67	0.095	0.105
e(1)	4.88	5.28	0.192	0.208
F	1.14	1.40	0.045	0.055
H(1)	6.10	6.71	0.240	0.264
J(1)	2.41	2.92	0.095	0.115
L	13.36	14.40	0.526	0.567
L(1)	3.33	4.04	0.131	0.159
Ø P	3.53	3.94	0.139	0.155
Q	2.54	3.00	0.100	0.118