






ROHS



B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME

NOTES:

1. MATERIAL:
  - MOLDING: LCP U94 V-0
  - CONTACT: COPPER ALLOY.
  - GOLD PLATED Min ON CONTACT AREA, 100u"
  - Min TIN (LEAD FREE) ON SOLDER AREA,
  - SHELL: SUS304-H1T=0.30±0.03mm
  - 50u" NICKEL PLATING OVER ALL.
2. MECHANICAL:
  - INSERTION: 5~20N.
  - EXTRACTION: 8~20N AFTER TEST.
  - DURABILITY: 10000 CYCLES
3. ELECTRICAL:
  - CURRENT: 5A FOR VBUS;
  - 1.25A FOR GND PIN.
  - 0.25A FOR OTHER.
  - VOLTAGE: 20 V MAX
  - WITHSTANDING VOLTAGE: 100V AC R.M.S.
  - CONTACT RESISTANCE: 40mΩ MAX.
  - INSULATION RESISTANCE: 100MΩ MIN.
4. ENVIRONMENTAL
  - TEMPERATURE RANGE -25°C ~ +85°C
5. 尺寸标注事项:
  - \* 者为首样全检, 重点管控尺寸.
  - 图例有标注
6. 产品符合RoHS标准

Table:

成品料号	零件名称	零件料号	材料 / 电镀
TX	端子	SUS 304 R-H	NO PLATING
TX	注塑材料	SUS 301 R-H	Sn 80~200u"
TX	外壳	SUS 301 R-H	电镀切割前压.

产品图

公差一览表

公差一览表	公差
X	±0.25
X	±0.20
XX	±0.15
XXX	±0.10
X	±5°
X	±2°
XX	±1°
XXX	±0.5°

深圳市精拓金电子有限公司

Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位	MM	制图	许榕强	制图料号
比例	1:1	审核	郭志富	产品名称
日期	2016-09-09	核准	黄国荣	产品图号
DATE		APPD		角法
				版本
				VER
				A0