

TSF60R190S2/TSP60R190S2 600V N-Channel Super-Junction MOSFET Gen-II


Description

SJ-FET is new generation of high voltage MOSFET family that is utilizing an advanced charge balance mechanism for outstanding low on-resistance and lower gate charge performance. This advanced technology has been tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate and higher avalanche energy. SJ-FET is suitable for various AC/DC power conversion in switching mode operation for higher efficiency.



Features

- Multi-Epi process SJ-FET
- 650V @T_J = 150 °C
- Typ. R_{D(S)} = 0.16Ω
- Ultra Low Gate Charge (typ. Q_G = 36.5nC)
- 100% avalanche tested

TSF60R190S2



TSP60R190S2



Absolute Maximum Ratings

Symbol	Parameter	TSP60R190S2	TSF60R190S2	Unit
V _{DSS}	Drain-Source Voltage	600		V
I _D	Drain Current - Continuous (T _C = 25°C) - Continuous (T _C = 100°C)	20*	12.6*	A
I _{DM}	Drain Current - Pulsed (Note 1)	65		A
V _{GSS}	Gate-Source voltage	±30		V
E _{AS}	Single Pulsed Avalanche Energy (Note 2)	485		mJ
I _{AS}	Avalanche current, repetitive or not-repetitive (pulse width limited by T _j max)	3.5		A
dv/dt	Peak Diode Recovery dv/dt (Note 3)	15		V/ns
dV _{ds} /dt	Drain Source voltage slope (V _{ds} =480V)	50		V/ns
P _D	Power Dissipation (T _C = 25°C)	150	34	W
T _J , T _{STG}	Operating and Storage Temperature Range	-55 to +150		°C
T _L	Maximum Lead Temperature for Soldering Purpose, 1/16" from Case for 10 Seconds	260		°C

* Drain current limited by maximum junction temperature. Maximum duty cycle D=0.75.

Thermal Characteristics


Symbol	Parameter	TSP60R190S2	TSF60R190S2	Unit
R _{θJC}	Thermal Resistance, Junction-to-Case	0.83	3.7	°C/W
R _{θCS}	Thermal Resistance, Case-to-Sink Typ.	0.5	-	°C/W
R _{θJA}	Thermal Resistance, Junction-to-Ambient	62	80	°C/W

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Off Characteristics						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = 250µA, T _J = 25°C	600	-	-	V
		V _{GS} = 0V, I _D = 250µA, T _J = 150°C	-	650	-	V
ΔBV _{DSS} /ΔT _J	Breakdown Voltage Temperature Coefficient	I _D = 250µA, Referenced to 25°C	-	0.6	-	V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _D S = 600V, V _G S = 0V -T _C = 125°C	-	-	100	µA
I _{GSSF}	Gate-Body Leakage Current, Forward	V _G S = 30V, V _D S = 0V	-	-	100	nA
I _{GSSR}	Gate-Body Leakage Current, Reverse	V _G S = -30V, V _D S = 0V	-	-	-100	nA
On Characteristics						
V _G S(th)	Gate Threshold Voltage	V _D S = V _G S, I _D = 250µA	2.0	3.0	4.0	V
R _D S(on)	Static Drain-Source On-Resistance	V _G S = 10V, I _D = 10A	-	0.16	0.19	Ω
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _D S = 100V, V _G S = 0V, f = 1.0MHz	-	1805	-	pF
C _{oss}	Output Capacitance		-	68	-	pF
C _{rss}	Reverse Transfer Capacitance		-	2.1	-	pF
Q _g	Total Gate Charge	V _D S = 480V, I _D = 10A, V _G S = 10V (Note 4)	-	36.5	-	nC
Q _{gs}	Gate-Source Charge		-	8.7	-	nC
Q _{gd}	Gate-Drain Charge		-	12.5	-	nC
R _g	Gate resistance	f=1 MHz, open drain	-	9.8	-	Ω
Switching Characteristics						
t _d (on)	Turn-On Delay Time	V _D S = 400V, I _D = 10A R _G = 3.3Ω, V _G S = 10V (Note 4)	-	38	-	ns
t _r	Turn-On Rise Time		-	39	-	ns
t _d (off)	Turn-Off Delay Time		-	170	-	ns
t _f	Turn-Off Fall Time		-	47	-	ns
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Maximum Continuous Drain-Source Diode Forward Current	V _G S = 0V, I _S = 20A	-	-	20	A
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current		-	-	65	A
V _S D	Drain-Source Diode Forward Voltage	V _G S = 0V, I _S = 20A	-	0.9	1.4	V
t _{rr}	Reverse Recovery Time	V _G S = 0V, V _D S = 400V, I _S = 10A, dI _F /dt = 100A/µs	-	318	-	ns
Q _{rr}	Reverse Recovery Charge		-	5.5	-	µC
I _{rrm}	Peak Reverse Recovery Current		-	24.9	-	A


NOTES:

- Repetitive Rating: Pulse width limited by maximum junction temperature
- I_D=I_{AS}, V_DD=50V, Starting T_J=25 °C
- I_{SD}≤I_D, d_i/d_t ≤ 200A/µs, V_DD ≤ BV_{DSS}, Starting T_J = 25 °C
- Essentially Independent of Operating Temperature Typical Characteristics


Safe operating area TC=25 °C
parameter: tp; TO-220




Safe operating area TC=25 °C
parameter: tp; TO-220FullPAK




Typ. output characteristics $T_f=25$ °C
parameter: V_{GS}




Typ. transfer characteristics




Typ. drain-source on-state resistance
parameter : V_{GS}




Typ. gate charge characteristics




Typ. capacitances




Normalized $V_{GS(th)}$ characteristics




Normalized on resistance vs temperature




Forward characteristics of reverse diode




Drain-source breakdown voltage




Power dissipation




Max. transient thermal impedance parameter: D=tp/T; TO-220







Max. transient thermal impedance parameter: D=tp/T; TO-220FullPAK




Avalanche energy




Switching times test circuit and waveform for inductive load
Switching times test circuit for inductive load

Switching time waveform

Unclamped inductive load test circuit and waveform
Unclamped inductive load test circuit

Unclamped inductive waveform


Test circuit and waveform for diode characteristics

Test circuit for diode characteristics



Diode recovery waveform





DISCLAIMER

Truesemi Semiconductor reserves the right to make changes WITHOUT further notice to any products herein to improve reliability, function, or design.

For documents and material available from this datasheet, Truesemi Semiconductor does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Truesemi Semiconductor hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

The products shown herein are not designed for use as critical components in medical, life-saving, or life-sustaining applications, whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness. Customers using or selling Truesemi Semiconductor products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Truesemi Semiconductor for any damages arising or resulting from such use or sale.

INFORMATION

For further information on technology, delivery terms and conditions and prices, please contact Truesemi Semiconductor office or website (www.truesemi.com).