

*SESDFBPxxV Series*  
*Single Line ESD Protection Diode*

Revision:B

**General Description**

The SESDFBPxxV ESD protection diode is designed to replace multilayer varistors (MLVs) in portable applications such as cell phones, notebook computers, and PDA's. They feature large cross-sectional area junctions for conducting high transient currents, offer desirable electrical characteristics for board level protection, such as fast response time, lower operating voltage, lower clamping voltage and no device degradation when compared to MLVs.

**Applications**

- Cellular phones handsets and Accessories
- PDA's
- MP3 players
- Digital cameras
- Portable applications
- mobile telephone

**Features**

- 60W peak pulse power
- Small package for use in portable electronics
- Low leakage current
- These are Pb-Free Devices

**Complies with the following standards**

**IEC61000-4-2**


**Level 4 15 kV (air discharge)**

**8 kV(contact discharge)**

**MIL STD 883E - Method 3015-7 Class 3**

**25 kV HBM (Human Body Model)**

**Functional diagram**




**WBFBP-02C**

**Maximum Ratings**

Symbol	Parameter	Value	Unit
V <sub>PP</sub>	IEC 61000-4-2 (ESD) Contact	±15	kV
P <sub>PK</sub>	Peak Pulse Power	60	W
I <sub>PP</sub>	Peak Pulse Power	12	A
T <sub>J</sub> , T <sub>STG</sub>	Junction and Storage Temperature Range	-55 to 150	°C
T <sub>L</sub>	Lead Solder Temperature – Maximum (10 Second Duration)	260	°C

**Electrical Parameter**

Symbol	Parameter
$I_{PP}$	Maximum Reverse Peak Pulse Current
$V_C$	Clamping Voltage @ $I_{PP}$
$V_{RWM}$	Working Peak Reverse Voltage
$I_R$	Maximum Reverse Leakage Current @ $V_{RWM}$
$I_T$	Test Current
$V_{BR}$	Breakdown Voltage @ $I_T$
$I_F$	Forward Current
$V_F$	Forward Voltage @ $I_F$




**Electrical Characteristics ( $T_A=25^{\circ}C$  unless otherwise noted,  $V_F=1.25V$  Max. @  $I_F=10mA$  for all types)**


Part Numbers	$V_{BR}$			$I_T$	$V_{RWM}$	$I_R$	$C$
	Min.	Typ.	Max.				Max. 1MHz, 0V Bias (note 1)
	V	V	V				pF
SESDFBP3V3	5.0	5.7	6.4	1	3.3	1	35
SESDFBP05V	6.0	6.8	7.2	1	5.0	1	30
SESDFBP07V	7.5	8.1	8.6	1	7.0	1	25
SESDFBP12V	13.5	14.2	15.0	1	12.0	1	15

1. Capacitance of one diode at  $f=1MHz, V_{RW}=0V, T_A=25^{\circ}C$

**Typical Characteristics**



**Figure 1. Non-Repetitive Peak Pulse Power versus Pulse Time**



**Fig 2. Power Derating Curve**




Figure 3. Clamping Voltage vs. Peak Pulse Current




Figure 4. Forward Voltage vs. Forward Current




Figure 5. Junction Capacitance vs. Reverse Voltage





Fig 6. ESD Clamping (8kV Contact per IEC 61000-4-2)

WBFBP-02C Mechanical Data



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.450	0.550	0.018	0.022
A1	0.010	0.070	0.000	0.003
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
D1	0.450REF.		0.018REF.	
E1	0.400REF.		0.016REF.	
b	0.275	0.325	0.011	0.013
e	0.675	0.725	0.027	0.029
L	0.275	0.325	0.011	0.013
L1	0.010REF.		0.000REF.	

The SINO-IC logo is a registered trademark of ShangHai Sino-IC Microelectronics Co., Ltd.

© 2005 SINO-IC – Printed in China – All rights reserved.

**SHANGHAI SINO-IC MICROELECTRONICS CO., LTD**

**Add:** Building 3, Room 3401-03, No.200 Zhangheng Road, ZhangJiang Hi-Tech Park, Pudong, Shanghai 201203, China

**Phone:** +86-21-33932402 33932403 33932405 33933508 33933608

**Fax:** +86-21-33932401

**Email:** [webmaster@sino-ic.com](mailto:webmaster@sino-ic.com)

**Website:** <http://www.sino-ic.com>