



Micro Commercial Components

Micro Commercial Components 20736 Marilla Street Chatsworth

CA 91311

Phone: (818) 701-4933 Fax: (818) 701-4939 SI2301A


Features


- Halogen free available upon request by adding suffix "-HF"
- -20V,-2.8A, $R_{DS(ON)}$ =120m Ω @ V_{GS} =-4.5V $R_{DS(ON)}$ =150m Ω @V_{GS}=-2.5V
- High dense cell design for extremely low R_{DS(ON)}
- Rugged and reliable
- High Speed Switching
- SOT-23 Package
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1

Maximum Ratings @ 25°C Unless Otherwise Specified

Symbol	Parameter	Rating	Unit	
V_{DS}	Drain-source Voltage	-20	V	
I _D	Drain Current-Continuous	-2.8	Α	
I _{DM}	Drain Current-Pulsed ^a	-10	Α	
V_{GS}	Gate-source Voltage	±8	V	
P_{D}	Total Power Dissipation	1.0	W	
R⊕JA	Thermal Resistance Junction to Ambient ^b	125	°C/W	
TJ	Operating Junction Temperature	-55 to +150	$^{\circ}\mathbb{C}$	
T _{STG}	Storage Temperature	-55 to +150	$^{\circ}\mathbb{C}$	

P-Channel Enhancement Mode Field Effect Transistor






DIMENSIONS					
	INCHES		MM		
DIM	MIN	MAX	MIN	MAX	NOTE
Α	.110	.120	2.80	3.04	
В	.083	.104	2.10	2.64	
С	.047	.055	1.20	1.40	
D	.035	.041	.89	1.03	
Е	.070	.081	1.78	2.05	
F	.018	.024	.45	.60	
G	.0005	.0039	.013	.100	
Н	.035	.044	.89	1.12	
J	.003	.007	.085	.180	
K	015	020	37	51	

Suggested Solder

Pad Layout inches mm

Internal Block Diagram





SI2301A

Electrical Characteristics T_A = 25°C unless otherwise noted

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
Off Characteristics				•		•
Drain-Source Breakdown Voltage	BV _{DSS}	$V_{GS} = 0V, I_{D} = -250\mu A$	-20			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = -20V, V _{GS} = 0V			-1	μΑ
Gate Body Leakage Current, Forward	I _{GSSF}	V _{GS} = 8V, V _{DS} = 0V			100	nA
Gate Body Leakage Current, Reverse	Igssr	V_{GS} = -8V, V_{DS} = 0V			-100	nA
On Characteristics °						
Gate Threshold Voltage	V _{GS(th)}	$V_{GS} = V_{DS}, I_{D} = -250 \mu A$	-0.5	-0.7	-0.9	V
Static Drain-Source		$V_{GS} = -4.5V, I_{D} = -2.8A$		80	120	mΩ
On-Resistance	R _{DS(on)}	$V_{GS} = -2.5V, I_{D} = -2.0A$		110	150	mΩ
Forward Transconductance	9 _{FS}	$V_{DS} = -5V, I_{D} = -2.8A$		8		S
Dynamic Characteristics d						
Input Capacitance	C _{iss}), O),), O),		880		pF
Output Capacitance	C _{oss}	$V_{DS} = -6V, V_{GS} = 0V,$ f = 1.0 MHz		270		pF
Reverse Transfer Capacitance	C _{rss}]		175		pF
Switching Characteristics d						
Turn-On Delay Time	t _{d(on)}			11	20	ns
Turn-On Rise Time	t _r	$V_{DD} = -6V, I_{D} = -1A,$		5	10	ns
Turn-Off Delay Time	t _{d(off)}	$V_{GS} = -4.5V$, $R_{GEN} = 6\Omega$		32	65	ns
Turn-Off Fall Time	t _f			23	45	ns
Total Gate Charge	Qg	\/ O\/ O O A		11	14.5	nC
Gate-Source Charge	Q _{gs}	$V_{DS} = -6V, I_{D} = -2.8A, V_{GS} = -4.5V$		1.5		nC
Gate-Drain Charge	Q _{gd}	- VGS 1.0V		2.1		nC
Drain-Source Diode Characteristics an	d Maximun F	Ratings				
Drain-Source Diode Forward Current b	Is				-0.75	Α
Drain-Source Diode Forward Voltage °	V _{SD}	$V_{GS} = 0V, I_{S} = -0.75A$			-1.2	V

Notes:
a.Repetitive Rating: Pulse width limited by maximum junction temperature.b.Surface Mounted on FR4 Board, t < 5 sec.
c.Pulse Test: Pulse Width ≤ 300µs, Duty Cycle ≤ 2%.
d.Guaranteed by design, not subject to production testing.



SI2301A




Figure 1. Output Characteristics




Figure 3. Capacitance




Figure 5. Gate Threshold Variation with Temperature




Figure 2. Transfer Characteristics




Figure 4. On-Resistance Variation with Temperature




Figure 6. Body Diode Forward Voltage Variation with Source Current

3 of 5



SI2301A




Figure 7. Gate Charge




Figure 8. Maximum Safe Operating Area




Figure 9. Switching Test Circuit




Figure 10. Switching Waveforms




Figure 11. Normalized Thermal Transient Impedance Curve

4 of 5



Ordering Information:

Device	Packing
Part Number-TP	Tape&Reel: 3Kpcs/Reel

Note: Adding "-HF" suffix for halogen free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.